

# TABLE OF CONTENTS

---



## Chapter 1 - Getting Started!

<b>Introduction</b> .....	1-2
Purpose of this Manual.....	1-2
About Getting Started .....	1-2
Online Help Files and Other Documentation .....	1-2
Technical Support .....	1-2
<b>Conventions Used</b> .....	1-3
Key Topics for Each Chapter.....	1-3
<b>Before you begin</b> ... ..	1-4
<b>Productivity Suite System Requirements</b> .....	1-5
<b>Step 1: Install Programming Software</b> .....	1-6
<b>Step 2: Launch Programming Software</b> .....	1-11
Online Help.....	1-12
<b>Step 3: Install Hardware</b> .....	1-13
<b>Step 4: Apply Power to CPU</b> .....	1-16
<b>Step 5: Establish PC to CPU Communications</b> .....	1-17
<b>Step 6: Open/Read Hardware Configuration</b> .....	1-18
<b>Step 7: Create a Project</b> .....	1-20
<b>Step 8: Save Project</b> .....	1-26
<b>Step 9: Write Project to CPU</b> .....	1-27
<b>Step 10: Place CPU in RUN Mode</b> .....	1-28
<b>Step 11: Test the Project Using Monitor Mode</b> .....	1-29

## Chapter 2 - Specifications

<b>Overview .....</b>	<b>2-2</b>
CPU System.....	2-2
<b>P3-03B, P3-05B, P3-08B, P3-11B Bases .....</b>	<b>2-3</b>
Base Configuration .....	2-3
<b>P3-01AC and P3-01DC Power Supplies.....</b>	<b>2-5</b>
No Power Budgeting.....	2-5
P3-01AC Specifications.....	2-6
P3-01DC Specifications .....	2-7
Power Connections .....	2-8
Grounding .....	2-8
<b>Productivity3000 CPU Modules.....</b>	<b>2-9</b>
<b>Productivity3000 CPU Modules.....</b>	<b>2-10</b>
P3-550 Specifications .....	2-11
LCD Message Display (P3-550) .....	2-13
Front Panel LCD Monitoring and Configuration (P3-550).....	2-14
P3-550E Specifications.....	2-15
LCD Message Display (P3-550E).....	2-17
Front Panel LCD Monitoring and Configuration (P3-550E).....	2-18
P3-530 Specifications .....	2-19
Battery (Optional) .....	2-21
Port Specifications .....	2-22
USB IN Port P3-550.....	2-22
USB Type B Slave Input Specifications .....	2-22
Ethernet Port.....	2-23
Remote I/O Port P3-550(E).....	2-23
Ethernet Specifications .....	2-23
USB OUT Port .....	2-24
EXP I/O OUT Port.....	2-24
RS-232 Port.....	2-25
RS-485 Port.....	2-26
<b>P3-EX Expansion Module.....</b>	<b>2-27</b>
P3-EX Expansion Module Example .....	2-28
Port Specifications .....	2-30

**Remote Slave Modules** ..... 2-31

    P3-RS/P3-RX Remote Slave Module Example (P3-550(E) only) ..... 2-32

    P3-RS Remote Slave Module Specifications..... 2-33

    P3-RS Remote Slave Module Front Panel ..... 2-34

    Status Indicators..... 2-34

    LCD Message Display (P3-RS only) ..... 2-35

    P3-RX Remote Slave Module Specifications ..... 2-36

    P3-RX Remote Slave Module Front Panel..... 2-37

    Status Indicators..... 2-37

    Setting the Remote Slave Address ..... 2-38

    Port Specifications ..... 2-40

    USB IN Port (P3-RS only)..... 2-40

    USB IN Specifications ..... 2-40

    Remote I/O Port..... 2-41

    EXP I/O OUT Port..... 2-42

    RS-232 Serial Port..... 2-43

    RS-485 Serial Port..... 2-44

**I/O Modules Overview** ..... 2-45

**Discrete I/O Modules** ..... 2-46

    Discrete Input Modules ..... 2-46

    Discrete Output Modules ..... 2-46

**P3-16SIM Input Simulator** ..... 2-47

**P3-08ND3S Isolated Sinking/Sourcing Input**..... 2-48

    Wiring Diagrams ..... 2-50

**P3-16ND3 Sinking/Sourcing Input**..... 2-51

    Wiring Diagrams ..... 2-53

**P3-32ND3 Sinking/Sourcing Input**..... 2-54

    Wiring Diagrams ..... 2-55

**P3-64ND3 Sinking/Sourcing Input**..... 2-56

    Wiring Diagrams ..... 2-57

**P3-08NAS AC Isolated Input** ..... 2-58

    Wiring Diagrams ..... 2-60

**P3-16NA AC Input** ..... 2-61

    Wiring Diagrams ..... 2-63

## Table of Contents

---

<b>P3-08TD1S Sinking Output</b> .....	<b>2-64</b>
Wiring Diagrams .....	2-66
<b>P3-08TD2S Sourcing Output</b> .....	<b>2-67</b>
Wiring Diagrams .....	2-69
<b>P3-16TD1 Sinking Output</b> .....	<b>2-70</b>
Wiring Diagrams .....	2-72
<b>P3-16TD2 Sourcing Output</b> .....	<b>2-73</b>
Wiring Diagrams .....	2-75
<b>P3-32TD1 Sinking Output</b> .....	<b>2-76</b>
Wiring Diagrams .....	2-78
<b>P3-32TD2 Sourcing Output</b> .....	<b>2-79</b>
Wiring Diagrams .....	2-81
<b>P3-64TD1 Sinking Output</b> .....	<b>2-82</b>
Wiring Diagrams .....	2-84
<b>P3-64TD2 Sourcing Output</b> .....	<b>2-85</b>
Wiring Diagrams .....	2-87
<b>P3-08TAS Isolated AC Output</b> .....	<b>2-88</b>
Wiring Diagrams .....	2-90
Replaceable Fuses.....	2-90
<b>P3-16TA AC Output</b> .....	<b>2-91</b>
Wiring Diagrams .....	2-93
Replaceable Fuses.....	2-93
<b>P3-08TRS Isolated Relay Output</b> .....	<b>2-94</b>
Wiring Diagrams .....	2-96
Replaceable Fuses.....	2-96
<b>P3-16TR Relay Output</b> .....	<b>2-97</b>
Wiring Diagrams .....	2-99
Replaceable Fuses.....	2-99
<b>P3-08TRS-1 Isolated Relay Output</b> .....	<b>2-100</b>
Wiring Diagrams .....	2-102
Replaceable Fuses.....	2-102
<b>P3-16TD3P Sinking/Sourcing Protected Output</b> .....	<b>2-103</b>
Wiring Diagrams .....	2-105

## Chapter 3 - Analog I/O Specifications

<b>Analog I/O Modules Overview</b> .....	3-2
<b>Analog I/O Modules</b> .....	3-3
Analog Input Modules.....	3-3
Analog Output Modules.....	3-3
Analog Input/Output Modules.....	3-3
<b>P3-04ADS Isolated Analog Input</b> .....	3-4
Wiring Diagrams.....	3-6
Module Configuration.....	3-8
LCD Panel Display.....	3-9
<b>P3-08AD Analog Input</b> .....	3-10
Wiring Diagrams.....	3-12
Module Configuration.....	3-13
LCD Panel Display.....	3-14
<b>P3-16AD-1 Analog Input</b> .....	3-15
Wiring Diagrams.....	3-17
Module Configuration.....	3-18
LCD Panel Display.....	3-19
<b>P3-16AD-2 Analog Input</b> .....	3-20
Wiring Diagrams.....	3-22
Module Configuration.....	3-23
LCD Panel Display.....	3-24
<b>P3-08RTD Analog Input</b> .....	3-25
Wiring Diagrams.....	3-27
Module Configuration.....	3-28
LCD Panel Display.....	3-29
<b>P3-08THM Analog Input</b> .....	3-30
Wiring Diagrams.....	3-32
Module Configuration.....	3-33
LCD Panel Display.....	3-34
<b>P3-04DA Analog Output</b> .....	3-35
Wiring Diagrams.....	3-37
Configuration Settings.....	3-39
LCD Panel Display.....	3-40

## Table of Contents

---

<b>P3-08DA-1 Analog Output</b> .....	<b>3-41</b>
Wiring Diagrams .....	3-43
Module Configuration .....	3-44
LCD Panel Display .....	3-45
<b>P3-08DA-2 Analog Output</b> .....	<b>3-46</b>
Wiring Diagrams .....	3-48
Module Configuration .....	3-49
LCD Panel Display .....	3-50
<b>P3-06DAS-1 Isolated Analog Output</b> .....	<b>3-51</b>
Wiring Diagrams .....	3-53
Module Configuration .....	3-54
LCD Panel Display .....	3-55
<b>P3-06DAS-2 Isolated Analog Output</b> .....	<b>3-56</b>
Wiring Diagrams .....	3-58
Module Configuration .....	3-59
LCD Panel Display .....	3-60
<b>P3-16DA-1 Analog Output</b> .....	<b>3-61</b>
Wiring Diagrams .....	3-63
Module Configuration .....	3-64
LCD Panel Display .....	3-65
<b>P3-16DA-2 Analog Output</b> .....	<b>3-66</b>
Wiring Diagrams .....	3-68
Module Configuration .....	3-69
LCD Panel Display .....	3-70
<b>P3-8AD4DA-1 Analog Input/Output</b> .....	<b>3-71</b>
Wiring Diagrams .....	3-74
Module Configuration .....	3-75
LCD Panel Display .....	3-76
<b>P3-8AD4DA-2 Analog Input/Output</b> .....	<b>3-77</b>
Wiring Diagrams .....	3-80
Module Configuration .....	3-81
LCD Panel Display .....	3-82

## Chapter 4 - Speciality Modules Specifications

<b>High-Speed Input (HSI) Module Overview</b> .....	4-2
HSI Specifications .....	4-2
HSI LED Indicators.....	4-5
HSI Wiring Examples .....	4-6
<b>High-Speed Output (HSO) Module Overview</b> .....	4-9
HSO Specifications .....	4-9
HSO LED Indicators.....	4-12
HSO Wiring Examples .....	4-12
<b>High-Speed Module Tester Utility</b> .....	4-16
<b>P3-SCM Serial Communications Module</b> .....	4-17
P3-SCM Specifications.....	4-17
P3-SCM LED Indicators.....	4-21

## Chapter 5 - Installation and Wiring

<b>Safety Guidelines</b> .....	5-2
Plan for Safety .....	5-2
Three Levels of Protection .....	5-3
Orderly System Shutdown.....	5-3
System Power Disconnect .....	5-3
Emergency Stop Circuits .....	5-4
<b>Introduction to the Productivity3000 Mechanical Design</b> .....	5-5
Typical Productivity3000 System.....	5-5
<b>Dimensions and Installation</b> .....	5-6
Base Dimensions .....	5-6
<b>Mounting Guidelines</b> .....	5-7
Enclosures .....	5-7
Mounting Position.....	5-7
Mounting Clearances .....	5-7
Grounding .....	5-7
Temperature Considerations.....	5-7
Power Considerations.....	5-7

## Table of Contents

---

Class 1, Division 2 Approval .....	5-9
Agency Approvals.....	5-9
Using Mounting Rails .....	5-10
Installing the Power Supply .....	5-11
Installing the CPU.....	5-12
Installing the I/O Modules.....	5-13
<b>Wiring Guidelines .....</b>	<b>5-14</b>
Wiring to the Power Supply .....	5-14
Grounding .....	5-14
Fuse Protection.....	5-15
<b>I/O Module Wiring Options .....</b>	<b>5-16</b>
<b>ZIPLink</b> Wiring System .....	5-16
Terminal Block With Pigtail Cable.....	5-16
Removable Terminal Blocks (Optional) .....	5-18
Terminal Block Removal .....	5-18
Planning the I/O Wiring Routes.....	5-19
<b>System Wiring Strategies .....</b>	<b>5-20</b>
CPU Isolation Boundaries .....	5-20
Sinking/Sourcing Concepts .....	5-21
I/O “Common Terminal” Concepts.....	5-22
DC Input Wiring Methods.....	5-23
DC Output Wiring Methods.....	5-23
Relay Outputs - Wiring Methods .....	5-25
Relay Outputs – Transient Suppression for Inductive Loads in a Control System.....	5-26

## Chapter 6 - Communications

<b>Communications: Capabilities .....</b>	<b>6-3</b>
Communication Ports.....	6-3
<b>Communications: Connectivity .....</b>	<b>6-11</b>
Communication Ports.....	6-11
<b>Communications ASCII and Custom Protocol Functionality .....</b>	<b>6-17</b>
ASCII Instructions .....	6-17
Custom Protocol Instructions .....	6-18



**Communications: Ethernet**..... 6-20

- TCP and UDP Port Numbers ..... 6-20
- IP Addressing and Subnetting ..... 6-20
- PC Setup ..... 6-21
- CPU Setup..... 6-22
- TCP Connection Behavior with Modbus TCP and Network Instructions ..... 6-23

**Communications Modbus Functionality** ..... 6-24

- Master/Client Function Code and Data Type Support ..... 6-24
- Slave/Server Function Code and Data Type Support ..... 6-26
- Assigning Modbus Addresses to Tags ..... 6-27
- Modbus Options ..... 6-30
- Modbus Instructions..... 6-33
- Network Instructions ..... 6-35
- Automatic Poll versus Manual Polling and Interlocking..... 6-36
- Message Queue..... 6-38

**EtherNet/IP for the Productivity Series** ..... 6-39

- Terminology Definitions ..... 6-39
- Network Layer Chart ..... 6-40
- EtherNet/IP Data ..... 6-40
- Class 1 and Class 3 Connections ..... 6-41
- Example Setup: Productivity3000 as EtherNet/IP Adapter ..... 6-41
- Troubleshooting Tips:..... 6-47
- Ethernet IP I/O Message Troubleshooting: ..... 6-49
- Ethernet IP Explicit Message Troubleshooting: ..... 6-49
- ProNET ..... 6-50
- Custom Protocol over Ethernet Functionality..... 6-51
- Hardware Configuration ..... 6-52
- Custom Protocol Ethernet Instruction..... 6-53

**Communications: Remote I/O and GS-Drives** ..... 6-54

- Things To Consider for the design of Remote I/O and GS-Drives ..... 6-54
- Configuration of Remote Slaves..... 6-55
- Configuration of GS-Drive Connections..... 6-58

**Communications: Port Configuration** ..... 6-62

- Ethernet Configuration ..... 6-62
- External Ethernet Port Settings ..... 6-63

## Table of Contents

---

Local Ethernet Port Settings.....	6-64
Remote Access Configuration .....	6-64
Serial Configuration.....	6-65
RS-232 and RS-485 Port Settings.....	6-65
<b>Communications: Error Codes .....</b>	<b>6-68</b>
<b>P3000 EtherNet/IP Error Codes .....</b>	<b>6-69</b>

## Chapter 7 - Maintenance and Troubleshooting

<b>Hardware Maintenance .....</b>	<b>7-2</b>
Standard Maintenance .....	7-2
Air Quality Maintenance.....	7-2
CPU Battery Replacement.....	7-2
<b>Diagnostics.....</b>	<b>7-3</b>
Diagnostics. ....	7-3
Critical Errors.....	7-3
Non-Critical Errors.....	7-3
Finding Diagnostic Information .....	7-3
Error Codes .....	7-3
<b>CPU Indicators .....</b>	<b>7-4</b>
<b>PWR Indicator .....</b>	<b>7-5</b>
Incorrect Base Power.....	7-5
Faulty CPU .....	7-5
Device or Module Causing the Power Supply to Shutdown .....	7-6
<b>Run Indicator .....</b>	<b>7-7</b>
<b>CPU Indicator.....</b>	<b>7-7</b>
<b>Communications Problems .....</b>	<b>7-7</b>
<b>I/O Module Troubleshooting .....</b>	<b>7-8</b>
Things to Check .....	7-8
Error Codes .....	7-8
Some Quick Steps .....	7-8
Testing Output Points .....	7-9
<b>Noise Troubleshooting .....</b>	<b>7-10</b>
Electrical Noise Problems.....	7-10
Reducing Electrical Noise.....	7-10

**Run Time vs. Stop Mode Transfer Instruction**..... 7-11

    Run Time Transfers..... 7-12

    Stop Mode Transfers ..... 7-12

**Forcing I/O Points** ..... 7-14

    Advantages of Forces..... 7-14

    Enabling Forces ..... 7-14

    Forcing Tags in Your System ..... 7-15

    Identifying Forced Values ..... 7-17

    Force Value Timing Chart..... 7-18

## Appendix A - European Union Directives (CE)

**In This Appendix**.....A-1

**European Union (EU) Directives** .....A-2

    Member Countries .....A-2

    Applicable Directives .....A-2

    Compliance.....A-2

    General Safety .....A-3

    Special Installation Manual .....A-4

**Basic EMC Installation Guidelines**.....A-4

    Enclosures .....A-4

    Mains Filters .....A-5

    Suppression and Fusing.....A-5

    Internal Enclosure Grounding.....A-5

    Equipotential Grounding .....A-5

    Communications and Shielded Cables .....A-6

    Analog and RS232 Cables .....A-7

    Multidrop Cables.....A-7

    Shielded Cables Within Enclosures.....A-7

    Analog Modules and RF Interference .....A-7

    Network Isolation .....A-8

    Items Specific to the Productivity3000 .....A-9

## Appendix B - Productivity3000 Error Codes

In This Appendix:.....	B-1
Communications Error Codes.....	B-2
Module Error Codes .....	B-3
CPU Error Codes .....	B-5
Project Error Codes.....	B-6
Project Error Messages .....	B-8