



TABLE OF CONTENTS

Chapter 1: Getting Started

Introduction	1-2
The Purpose of This Manual	1-2
Supplemental Manuals	1-2
Technical Support	1-2
Conventions Used	1-3
Key Topics for Each Chapter.....	1-3
Product Overview	1-4
Quick Start Steps	1-5
Step 1 – Unpack and Inspect.....	1-5
Step 2 – Install Optional Hardware Accessories.....	1-6
Step 3 – Become Familiar with Available Communication Ports.....	1-7
Step 4 – Install the Programming Software and Develop a Project	1-8
Step 5 – Connect HMI to Computer	1-9
Step 6 – Provide Power to the HMI	1-10
Step 7 – Access the EA9-RHMI Setup Screens	1-13
Step 8 – Choose HMI to Device Cable.....	1-14
Step 9 – Connect HMI to PLC	1-17

Chapter 2: Specifications

Specifications	2-2
Dimensions	2-4
Inches [mm].....	2-4
Communication Ports and Memory Expansion	2-5
Compatible Touch Screen Monitors	2-7
Handling External Memory Devices	2-8
Writing to External Memory Devices	2-8

Table of Contents

1

Memory Device Formatting.....	2-8
Minimizing Data Errors.....	2-9
Monitoring Available Memory	2-9
File Name Limitations.....	2-10
Power Loss Retention	2-10

Chapter 3: Accessories

Accessories Overview.....	3-2
EA-ECOM Ethernet Communication Module.....	3-3
D-SUB 15-pin to Terminal Block Adapter	3-4
SD Card	3-5
USB FLASH Drive	3-5

Chapter 4: Installation and Wiring

Safety Guidelines	4-2
Introduction.....	4-3
Mounting	4-4
DIN Rail Mounting	4-4
Panel Mounting.....	4-4
Mounting Clearances	4-5
Wiring Guidelines	4-6
Agency Approvals.....	4-6
Providing Power to the HMI.....	4-7
C-more LED Status Indicators.....	4-8
Reset Button.....	4-9
RUN/STOP switch.....	4-9

Chapter 5: System Setup Screens

Introduction.....	5-2
Accessing the System Setup Screens	5-3
With no project loaded	5-3
With project loaded.....	5-4
Using RHMI USB Remote.....	5-5

System Setup Screens – Enable Password in Software	5-8
System Setup Screens Flowchart	5-14
Main Menu.....	5-15
Information Menu	5-16
Setting Menu	5-20
Test Menu	5-26
Memory Menu	5-36

Chapter 6: PLC Communications

Introduction.....	6-2
<i>Direct</i> LOGIC PLCs Password Protection	6-2
PLC Protocols	6-3
PLC Communication Cables & Wiring Diagrams.....	6-5
AutomationDirect PLCs RS-232C Serial.....	6-7
AutomationDirect PLCs RS-422A/RS-485A.....	6-10
<i>Direct</i> LOGIC Universal Isolated Network Adapter, p/n FA-ISOCAN:	6-16
<i>Direct</i> LOGIC Universal Converter, p/n F2-UNICON:	6-17
RS-422A/RS-485A Multi-Drop Wiring Diagram Examples	6-18
Allen-Bradley	6-22
GE.....	6-27
GE VersaMax Micro	6-27
Mitsubishi.....	6-28
Omron	6-30
Modicon Modbus RS-232.....	6-31
Modicon Micro Series.....	6-31
Modicon Modbus with RJ45.....	6-31
Siemens.....	6-32

Chapter 7: Maintenance

Project Backup	7-2
Check Operating Environment	7-2
Check Operating Voltage	7-2
Check Status Indicators	7-2
Check Physical Conditions.....	7-3

Run Tests under System Setup Screens.....	7-3
Check Memory Usage	7-3
Check Error Log	7-4
Check Project Functionality	7-4
Checks from <i>C-more</i> Programming Software.....	7-5
Notes:	7-6

Chapter 8: Troubleshooting

Common Problems	8-2
Troubleshooting Flow Chart.....	8-3
HMI Does Not Power Up.....	8-4
<i>C-more</i> LED Status Indicators.....	8-5
General Errors and Warnings	8-6
Display is Blank	8-7
No User Program	8-8
Touch Screen Does Not Work	8-9
Touch Screen Calibration is Inverted	8-9
Firmware Recovery Tool	8-10
No System Found.....	8-11
No Communications Between Panel and PC (Personal Computer) via USB	8-12
USB Driver Troubleshooting	8-14
No Communications Between Panel and PC (Personal Computer) via Ethernet	8-16
No Communications Between Panel and PLC	8-21
IP Address in System Setup Screens Displays 0.0.0.0	8-24
Difficulty Connecting to the Panel over the Internet (Web Server and Remote Access Features)	8-25
PLC Protocol Error Codes	8-26
HMI Runtime Errors.....	8-27
Panel Constantly Displays “Initializing” when Powering Up.....	8-28
Data Not Logging Problems.....	8-28
Electrical Noise Problems.....	8-29
Touch Screen Not Working	8-29

Chapter 9: Replacement Parts

Replacement Parts Overview	9-2
3-wire Communications Terminal Block – EA9-3TB.....	9-3
DC Power Connector Replacement – C0-4TB.....	9-3

Appendix A: HMI and PLC Error Code Tables

Introduction.....	A-2
<i>C-more</i> HMI Error Code Table	A-3
<i>Direct</i> LOGIC – Panel Error Code PLC-499 Explanation	A-5
<i>Direct</i> LOGIC K-Sequence Protocol – PLC Error Code Table.....	A-5
<i>Direct</i> LOGIC <i>Direct</i> NET Protocol – PLC Error Codes.....	A-5
Modbus Protocols Error Code P499 Explanation	A-6
AutomationDirect CLICK	A-6
AutomationDirect <i>Direct</i> LOGIC - Modbus (Koyo).....	A-6
Modicon Modbus RTU	A-6
Entivity Modbus RTU.....	A-6
<i>Direct</i> LOGIC ECOM Protocol – PLC Error Codes.....	A-6
Productivity Error Code P499.....	A-7
AutomationDirect Do-More Error Codes.....	A-8
Allen-Bradley – Panel Error Code PLC-499 Explanation	A-9
Allen-Bradley DF1 & DH485 Protocols – PLC Error Code Tables	A-10
Allen-Bradley EtherNet/IP Protocol – Panel Error Code PLC-496, 497 and 498 Explanation	A-12
Allen-Bradley – EtherNet/IP Protocol – PLC Error Code Tables ControlLogix, CompactLogix, and FlexLogix	A-13
Allen-Bradley – Micro800 Serial and EtherNet/IP Tag Based PLC Error Code Tables	A-17
Allen-Bradley – EtherNet/IP Protocol – PLC Error Code Tables SLC, MicroLogix and ENI.....	A-21
Generic EtherNet IP Protocol – PLC Error Codes	A-26
GE 90-30 – Panel Error Code PLC-499 Explanation.....	A-27
GE 90-30 SNPX Protocol – PLC Error Code Tables.....	A-28

Mitsubishi FX Protocol – PLC Error Codes.....	A-37
Omron – Panel Error Code PLC-499 Explanation	A-37
Omron Host Link Protocol – PLC Error Code Table	A-38
Omron FINS Protocol – PLC Error Code Table	A-39
Omron – Panel Error Code P495 Explanation	A-42
Omron CS/CJ FINS Ethernet Protocol – PLC Error Code Table.....	A-43
Siemens – Panel Error Code P499 Explanation.....	A-44
Siemens PPI Protocol – PLC Error Code Table.....	A-45
Siemens ISO over TCP Protocol – PLC Error Code Table	A-46

Appendix B: HMI Runtime Errors

Introduction.....	B-2
Runtime Errors.....	B-3
Log File Naming.....	B-4

Appendix C: Security Considerations for Control Systems Networks

Security Considerations for Control Systems Networks.....	C-2
-----------------------------------------------------------	-----