




# Electronic Remote Reset Module Product Installation

**Figure 1.****Figure 2.****Figure 3.****Table 1. Modbus Settings**

Pin #	Description	
	ZEB-XRR-24	ZEB-XRR-120
1	L	L
2	N	N

**Table 2. Environmental Ratings of the Module**

Transportation and Storage	Temperature	-40°C to 85°C (-40°F to 185°F)
	Humidity	5-95% non-condensing
	Shock IEC 60068-2-27	15G
Operating	Temperature	-25°C to 65°C (-13°F to 149°F)
	Humidity	5-95% non-condensing
	Altitude	Above 2000 meters (6600 feet) Consult FACTORY
	Vibration IEC-60068-2-6	3G
	Polution Degree	3

**Table 3. Approvals/Certifications**

Agency Certifications	UL508 CUL (CSA C22.2 No. 14) CE (Low Voltage Directive)	RoHS
-----------------------	---	------

**Table 4. Module Electrical Requirements**

	24V ac	120V ac
Voltage Range	19.2 - 28.8	96 - 148
Transformer		50VA for 1 second

**Notes:**

Use any UL Listed Control Transformer 50VA or Greater.



PowerChain Management is a registered trademark of Eaton Corporation.

All other trademarks are property of their respective owners.