



Instruktion-Instruction-Instruktionen-Instructions SC3/SRC/SMCDOL

Montering - Mounting Montage - Montage




DK: Hvis enheden er monteret vandret, skal driftsstrømmen reduceres med 50%





UK: If the unit is mounted horizontally the current must be derated by 50%

DE: Falls Einheit horizontal montiert wird, muss der Strom um 50% reduziert werden

FR: En cas montage horizontal, réduire le courant de 50%



Dimensioner - Dimensions Dimensionen - Dimensions



DK: Køleplade skal holdes ren. Luftstrømmen må ikke blokeres

UK: Keep heatsink clean. Airflow must not be blocked

DE: Kühlflächen freihalten. Luftstrom muss ungehindert fließen

FR: Maintenir les plaques de refroidissement libres, l'air doit pouvoir circuler




Forbindelse - Wiring - Verdrahtung - Cablage

75°C Cu Wire/Kabel	mm ²	mm ²
*	1 x 0.75 - 4	1 x 0.5 - 1.5
	2 x 1.0	2 x 0.5 - 0.75
*	1 x 0.75 - 6	1 x 0.5 - 1.5
	2 x 0.75 - 4.5	2 x 0.5 - 1.5
*	1 x 0.75 - 6	1 x 0.5 - 1.5
	2 x 0.75 - 1.5	2 x 0.5 - 1.5
	Pozidrive 1 0.5 Nm max.	
	4 mm 0.5 Nm max.	3 mm 0.5 Nm max.


* UL Tested

- Vigtigt (Overhold max skruedrejningsmomenter)
 - Important: (Observe the maximum screw torque limits)
 - Wichtig: (Max. Drehmoment beachten)
- Do not connect power factor correction capacitors to the output.


SC 3 DX



SRC 3 DX



SMC 3 DA ..15 DOL



11&12 for UP 62 (termisk beskyttelse) eller andre tilslutninger. Ingen forbindelse til det øvrige kredsløb.

11&12 for UP 62 (thermal overload) or other wiring purposes. Have no internal connection.

11&12 für UP 62 (Thermischer Schutz) oder andere Anschluss Möglichkeiten. Keine interne Verbindung.

UL: Use thermal overload protection as required by the National Electric Code.
UL: SMC.. DOL / SRC. When protected by a non-time delay K5 or H Class fuse, rated 266 % of motor FLA, this device is rated for use on a circuit capable of delivering not more than 5,000 rms. symmetrical amperes, 600 V maximum.
Maximum surrounding temperature 40°C.
DK: Se specifikationer i datablad UK: See recommendation in datasheet DE: Empfehlungen im Datenblatt beachten