



WIEGMANN

FREEBURG, ILLINOIS, USA

HUBBELL ELECTRICAL PRODUCTS
A Division of HUBBELL
INCORPORATED (Delaware)
501 West Apple
Freeburg, IL 62243 USA
For Customer Service: 618-539-3193

DWG. NO. HWIHF330104

FORM NO. HFW330104

DATE 08/03/2016

AFFECTED P.N. PMKSML, PMKSMLSS, PMKLRG, PMKLRGSS

INSTALLATION, OPERATION, & MAINTENANCE DATA SHEET

CAUTION: Before installing, make sure you are compliant with area classifications - as failure to do so may result in bodily injury, death and property damage. Do not attempt installation until you are familiar with the following procedures. All installation must comply with the applicable Electrical Code(s). Make sure that all supply circuits are de-energized before starting installation or maintenance. Verify that the installation is grounded. Failure to ground will create electrical shock hazards, which can cause serious injury and or death.

Important: Please read these instructions carefully before installing or maintaining this equipment. Safe electrical practices should be followed at all times and this data should be used as a guide only. Maintain the environmental integrity of this enclosure by closing all openings w/UL listed or recognized components that have the same environmental rating as the enclosure.

INSTALLATION OF POLE MOUNTING KIT

TOOLS NEEDED:

5/16" NUT DRIVER
7/16 WRENCH
9/16 WRENCH

UL RATINGS:

UL RECOGNIZED COMPONENT

MAX/ MIN MOUNTING HOLE SPACING

PMKSML & PMKSMLSS - 21.6" MAX / 6.7" MIN
PMKLRG & PMKLRGSS - 35.3" MAX / 21.3" MIN

POLE MOUNTING KIT INSTALLATION INSTRUCTIONS:

STEP 1: FASTEN TOP POLE MOUNTING BRACKET TO POLE USING SUPPLIED SLOTS IN BRACKET AND 9/16 HOSE CLAMP. (MOUNT MUST BE LEVEL)


STEP 2: PLACE THE CENTER BRACKET ON THE BACKSIDE OF THE ENCLOSURE. LAY THE ADJUSTABLE ARMS SO THAT THE OUTSIDE MOUNTING HOLES ALIGN WITH THE MOUNTING HOLES ON THE ENCLOSURE. SLIDE THE 3/8-16 X 1" BOLTS INTO THE MOUNTING HOLES TO HOLD THE ARM IN LOCATION. ONCE THE ARMS ARE CENTERED (LEFT TO RIGHT) ON THE CENTER MOUNTING BRACKET STUDS INSTALL THE (4) 1/4" FLAT WASHER AND (4) 1/4" LOCKING NUTS. ONE PER EACH STUD.

STEP 3: INSTALL (2) SEALING WASHER WITH 3/8 LOCK NUT ON INSIDE OF THE ENCLOSURE.


STEP 4: INSTALL 9/16" HOSE CLAMP IN THE BOTTOM POLE MOUNTING BRACKET USING THE SUPPLIED SLOTS IN BRACKET.

STEP 5: REPEAT STEPS 2 AND 3 FOR BOTTOM BRACKETS.


STEP 6: TAKE THE COMPLETED ASSEMBLY AND ALIGN THE TOP CENTER BRACKET WITH THE OPENING IN THE TOP POLE MOUNTED BRACKET. LOWER THE ASSEMBLY SO THAT THE TOP MOUNTED CENTER BRACKET PASSES THROUGH THE OPENING IN THE TOP POLE MOUNTED BRACKET (ENCLOSURE ASSEMBLY MAY NEED TO BE TILTED). ENSURE THAT THE CENTER MOUNTED BRACKET PASSES THROUGH EACH OPENING ON THE POLE MOUNTED BRACKET (TOP AND BOTTOM SLOTS). TIGHTEN BOTTOM HOSE CLAMP UNTIL TIGHT ON POLE.



STEP 1



STEP 2



STEP 3



WIEGMANN®

FREEBURG, ILLINOIS, USA


HUBBELL ELECTRICAL PRODUCTS
A Division of HUBBELL
INCORPORATED (Delaware)
501 West Apple
Freeburg, IL 62243 USA
For Customer Service: 618-539-3193

DWG. NO. HWIHF330104


FORM NO. HFW330104

DATE 08/03/2016



AFFECTED P.N. PMKSML, PMKSMLSS, PMKLRG, PMKLRGSS



STEP 4



STEP 5



STEP 6