

Index

Symbols

15-pin D-Sub, 28
 6-inch Slim Bezel models, 27
 DIN Clip Mounting, 27
 62-Pin Socket, 33, 35
 9-pin D-Sub Connector, 28

A

accessories, 9
 adjustable features, 15
 Allen-Bradley
 A-B DH+ option cards
 PLC Port, 30
 PLC Cable Wiring Diagrams
 Micrologix 1000/1200/1500 RS-232, A-3
 PLC5 DF1 RS-232, A-3
 SLC DF1 RS-232 (P/N EZ-SLC-232-CBL), A-3
 SLC500, 5/01, /02, /03 DH-485/AIC, A-2
 SLC500 DH-485/AIC (Multi-drop), A-2
 PLC Wiring Diagrams
 RS-422A, A-12
 alphanumeric entry, 7
 Analog Clock, 7
 application, 2
 AS-MBKT-085 Modicon line connector, 38
 AS-MBKT-185 Modicon terminating connector, 38

B

Back View, 28
 BACKPLANE
 EZEthernet Installation, 34
 Backplane connector, 33
 backup, 7
 Battery
 1/2 AA, 3.6 V Lithium Battery, 47
 low battery, 45
 replace, 47
 Belden 9729 cabl, A-11
 bitmaps, 7
 Boot program, 41
 Bottom View, 28
 brackets, 27

C

cable, 55
 calendar, 7
 captive washers, 22, 23, 24, 25, 26
 CARD CONNECTOR, 34
 card slot, 50
 CAUTION
 battery removal, 26, 47
 DIN Clips, 27
 removing RAM or Flash card, 48, 50
 thread locking compound, 15, 16
 CD ROM, 3
 CE mark, vi
 chassis ground, 28
 chemical barrier, 54
 Chemical Compatibility, 52
 Cleaning, vi, 54
 clearance, 16
 Clock, 7, 15, 41
 COM1 Port, 15, 28, 31, 42
 communication settings, 15
 Communications
 cable, 55
 from EZ Touch to Computer, 55
 ports, 7
 Setup, 15, 41
 Communications Setup, 15
 compatible/incompatible chemicals and compounds,
 vi
 Computer, 42
 connections, 15
 Connections and Wiring, 15, 29
 Connector
 EZ-S6C-FH, EZ-S6C-FSH, 32
 EZ-S6M-FH, EZ-S6M-FSH, 32, 36, 37, 38, 39
 EZ-S8C-FH, 32
 connector
 Allen-Bradley DH+ Option Card, 33
 EZEthernet, 34
 EZEthernet option card, 35
 Generic DeviceNet I/O Option Card, 36
 Generic Ethernet/IP Option Card, 37
 Generic Profibus-DP Option Card, 39
 Modicon Modbus Plus, 38
 context sensitive onscreen help, 3
 Contrast, 15, 43
 contrast adjustment feature, 43

contrast range, 43
 cooling, 16
 cutout, 16
 cutout dimensions — See Dimension Drawings

D

Data Highway Plus Models, 6
 Day, 42
 DC powered, 15
 design screens, 2
 Dimension Drawings, 17
 Cutout
 EZ-S8C-FS and EZ-S8C-FSH, 31
 EZ-T10C-FS, EZ-T10C-FSH, EZ-T10C-FSD,
 EZ-T15-FSE, 24
 EZ-T10C-FSM, EZ-T10C-FSP, 24
 EZ-T15C-FS, EZ-T15C-FSH, EZ-T15C-FSD,
 EZ-T15C-FSE, 26
 EZ-T15C-FSM, EZ-T15C-FSP, 26
 Dimensions (Outline)
 EZ-S8C-FS and EZ-S8C-FSH, 20
 EZ-T10C-FS, EZ-T10C-FSH, EZ-T10C-FSD,
 EZ-T10C-FSE, 23
 EZ-T15C-FS, EZ-T15C-FSH, EZ-T15C-FSD,
 EZ-T15C-FSE, 25
 EZ-T15C-FSM, EZ-T15C-FSP, 25
 Outline & Cutout
 EZ-S6C-K, EZ-S6C-F, EZ-S6C-FH, 17
 EZ-S6C-KS, EZ-S6C-FS, EZ-S6C-FSH, 18
 EZ-S6M-R, EZ-S7M-F, EZ-S6M-FH, 17
 EZ-S6M-RS, EZ-S6M-FS, EZ-S6M-FSH, 18
 EZ-S8C-F and EZ-S8C-FH, 19
 EZ-T10C-F and EZ-T10C-FH, 22
 EZ-T10C-FSM, EZ-T10C-FSP, 23
 DIN Clip Slot Location, 27, 28
 EZ-S6C-F, 27
 EZ-S6C-FH, 27
 EZ-S6C-FS, 28
 EZ-S6C-FSH, 28
 EZ-S6C-K, 27
 EZ-S6C-KS, 28
 EZ-S6M-F, 27
 EZ-S6M-FH, 27
 EZ-S6M-FS, 28
 EZ-S6M-FSH, 28
 EZ-S6M-R, 27
 EZ-S6M-RS, 28
 Slim Bezel Models, 28
 DIN Clip tab, 26, 29

DIN Clips, 15, 16, 27
 DIP Switches
 EZ Ethernet, 35
 EZ Ethernet Option Card, 35
 Generic DeviceNet I/O Option Card, 36
 Generic Ethernet/IP Option Card, 37
 Modicon Modbus Plus Option Card, 38
 DirectLogic PLC Cable Wiring Diagrams
 15-pin D-SUB (P/N EZ-4CBL-1), DL40, A-5
 25-pin D-SUB (P/N EZ-4CBL-2), A-5
 RJ-11 (P/N EZ-3CBL), A-4
 RJ-12 (P/N EZ-2-CBL), A-4
 VGA 15-pin (P/N EZ-2CBL-1), 250 RS, A-4
 DirectLogic PLC Wiring Diagrams
 RS-422A and RS-485A, A-11
 Display Blank, 56
 Display Test, 44

E

electrical circuits, vi
 Environmental Specifications, vi
 ETHERNET, 34
 EU Information, vi
 European Union (EU) Directives, vi
 Exit, 44
 EZ-BAT, 47
 EZ-BRK-1, 27
 EZ-ETHERNET, 34
 EZ-ETHERNET-M, 35
 EZ-FLASH-1, 50
 EZ-FLASH-2, 50
 EZ-S8C-FS and EZ-S8C-FSH Dimensions & Cutout,
 20, 21
 EZ-T10C-FS and EZ-T10C-FSH Dimensions &
 Cutout, 23, 24
 EZ-T15C-FS and EZ-T15C-FSH Dimensions &
 Cutout, 25, 26
 EZ-TOUCHEDIT-M, 2
 EZEthernet Option Card, 34
 Installation Instructions, 34
 Outline Drawing, 35
 EZEthernet Option Card Installation Instructions, 34
 EZEthernet Option Card Manual, 35
 EZTouch Panel, 5
 install, 2
 models, 5
 Programming Cable, 31
 Programming Software, 2
 Software Manual, 2

EZTOUCH-PGMCBL, 28
EZTOUCH10-GSK, 48
EZTOUCH6-GSK and EZTOUCH6S-GSK, 48
EZTOUCH8-GSK, 48

F

F1 function key, 3
factory default values, 15
Features, 7
Field expandable user RAM, 7
Firmware, 41
firmware upgrade, 7
Flash, 7
FLASH Card, 50
Flash memory, 41
Flash option card, 45
FLASH Program Backup, 50
Fluorescent Backlight Bulb Replacement, 51
Fly-Over HELP, 3
Front Bezel, 29
front bezel, 27
front-panel mount, 15
fuse, 50
Fuse Reset, 50

G

Gasket Replacement, 48
 6-inch Slim Bezel Models, 48
gasket slot, 48
General Electric PLC Wiring Diagram, A-6
Generic DeviceNet I/O, 36
Generic Ethernet/IP, 37
Generic Profibus-DP, 39
get started, 3
GND, 28
graphical data, 5

H

Hardware, 3, 41
Hardware Specifications, 11
Help, 3, 57
 windows, 3
Hr, 42

I

IBM, 3
ideal conditions, 52

Install

installing EZTouch Programming Software, 2
Installing the EZTouch Panel, 15
 program, 2
interface boards, 30
internal fuse, 50
Introduction, 5

L

languages, 7
LED, 28, 48, 55
 Configuration ERROR, 33
 Transmit Enable, 33
LEDs
 Allen-Bradley DH+ Option Card, 33
 DeviceNet I/O Option Card, 36
 DH+, 33, 36, 37, 39
 EZ Ethernet option card, 35
 EZEthernet option card, 35
 Generic Ethernet/IP Option Card, 37
 Generic Profibus-DP Option Card, 39
 Modicon Modbus Plus Option Card, 38
line connector, 38
Lithium Battery Replacement, 47

M

Maintenance, 2
Manual
 organization, 1
 Revisions, v
MBP, 38
Memory Card, 56
metal brackets, 27
Meters, 7
Min, 42
Mitsubishi FX Series
 8-pin MINI-DIN RS-422, A-7
Mitsubishi FX Series PLC Wiring Diagram
 25-pin RS-422A, A-6
Modbus Plus, 38
Models, 5
Modicon
 PLC Wiring Diagram
 984 CPU, Quantum 113 CPU, A-7
 AEG Modicon MICRO Series, A-8
 Modicon ModBus with RJ45, A-8
Modicon Modbus Plus, 38
Mon, 42
Mounting, 2, 15, 16, 27

Dimensions, 17
 Hardware, 17, 18
 Mounting Panel, 26, 29
 mouse, 3
 mouse cursor, 3

N

node address, 38
 Nonvolatile flash card, 7
 nonvolatile storage, 45
 numeric, 7

O

offline, 2
 Omron PLC Wiring Diagram
 C200, C500 RS-232C, A-9
 CQM1 and CPM1, A-9
 online, 2
 Onscreen HELP, 3
 onscreen prompts, 2
 Operating Temperature, vi
 operator interfaces, 2
 Option Card
 Allen-Bradley Data Highway Plus, 33
 EZ Ethernet, 34
 Generic Devicenet I/O, 36
 Generic Ethernet/IP, 37
 Generic Profibus-DP, 39
 Installation, 32
 Modicon Modbus Plus, 38
 Optional Equipment, 9
 outline, 16
 outline dimensions — See Dimension Drawings

P

palette, 7
 Panel Status Indicator Light, 48
 panel tests, 15
 PC, 3
 PID Faceplates, 7
 pinout, 30
 pixel, 44
 PLC, 5, 8, 15
 addresses, 7
 Cable, 28
 Cable Part Numbers, 10, 30
 connector, 28, 30
 memory locations, 7

Port, 15, 28, 30
 Wiring Diagrams, 2
 PLC Cable Part Numbers
 CBL-UTICW-012, A-10
 P/N EZ-2-CBL, A-4
 P/N EZ-2CBL-1, A-4
 P/N EZ-3CBL, A-4
 P/N EZ-4CBL-1, A-5
 P/N EZ-4CBL-2, A-5
 P/N EZ-90-30-CBL, A-6
 P/N EZ-DH485-CBL, A-2
 P/N EZ-MITSU-CBL, A-6
 P/N EZ-MITSU-CBL-1, A-7
 P/N EZ-MLOGIX-CBL, A-3
 P/N EZ-OMRON-CBL, A-9
 P/N EZ-S7MPI-CBL, A-10
 P/N EZ-SLC-232-CBL, A-3
 P/N EZPLC5-232-CBL, A-3

PLC connector
 Allen-Bradley Data Highway Plus, 33
 polyester surface, 52
 Power
 Connector, 28, 30
 source, 15, 28
 Supply, 55
 Terminal, 28, 30
 Precautions, 51
 PreventativeMaintenance, vi
 PreventativeMaintenanceand Cleaning, vi
 Printer, 7, 15, 28, 42
 programmable graphic operator interface devices, 2
 programmable graphics interface, 5
 Programming
 Cable Part Number, 10
 computer, 15
 PC Cable, 28

Q

questions, 57

R

RAM, 7
 card slot, 49
 memory, 41, 49
 Upgrade, 49
 reboot, 44
 redo, 7
 Regulated power source, 30
 Remote I/O, 6, 32

Removing

- Battery, 47
- memory card, 48
- power, 45

Replacement Equipment, 9**Rotary Address Switches, 39****RS-232 EZTouch Panel Programming Cable, 31****RS-232C, 15, 28****RS-232C or RS-422A/485A PLC Interface Cable, 3****RS-232C Programming Cable, 3****RS-422A, 15, 28****RS-422A connections, A-11****RS-422A Wiring Connections for DirectLogic PLCs,
A-1, A-11****RS-422A Wiring for A-B SLC 503/504 RS-232 Port,
A-12****RS-422A/RS-485A Wiring Connections, A-11****RS-485A, 15, 28****RXD, 38****S****Safety Extra Low Voltage (SELV), vi****scratch resistant coating, 54****Screen Saver, 51****screens, 7****Sec, 42****Selector Switch, 7****SELV Circuits, vi****serial port, 3****Setup, 15****Setup Mode, 15, 41****Shutting Off Power, 45****Siemens S7 MPI Adaptor****RS-232C Wiring Diagram, A-10****Siemens S7 MPI Adaptor, RS-232C (P/N EZ-S7MPI-
CBL), A-10****Slide Switch, 7****Slim Bezel Model, 11****Slim Bezel Models EZ-S6M-RS, EZ-S6M-FS, EZ-
S6M-FSH, 28****Software, 3****special interface boards, 28****SPECIFICATIONS, 11, 13****Specifications****6-inch Models (Slim and Standard), 11****8-inch, 10-inch, 15-inch Slim Bezel, 13****8-inch and 10-inch Standard Bezel, 12****all 6-inch Models, 11****Status LED, 28****Storage Temperature, vi****Stud Mounting, 16****Studs, 16****Switches****Generic Profibus-DP Option Card, 39****T****tag, 7****Technical Support, 4, 57****Termination Switch, 39****Test screen, 43****tests, 15****TFT Color units, 43****thread locking compounds, 15****Throw Switch, 7****Thumbwheel Object, 7****time and date, 41****Toggle Switch, 7****top slot, 56****topics, 1****Touchpad Test, 15, 43****Touchscreen Cleaning, 54****Touchscreen/Chemical Compatibility, 52****Troubleshooting, 2, 55****TXD, 38****U****undo, 7****upgrade, 9****user program backup, 7****V****VGA display, 3****W****Windows-based, 2****Wiring, 2, 15, 29****Diagram, 28****diagram, 31****RS-422, A-1, A-11****Y****Yr, 42**



This page intentionally left blank.