


Monitor Holder Part# 162894 Assembly Procedure



Copyright 2023, Automationdirect.com Incorporated/
All Rights Reserved Worldwide

Hardware Included

2X – Button Head
Socket Cap Screw
M6-1.0 x 16mm

2X – Button Head
Socket Cap Screw
M6-1.0 x 12mm

2X – Button Head
Socket Cap Screw
1/4-20 x 1/2"

2X – Concrete Anchor
M8 x 50mm

2X – Cable-Tie 200mm long

4X – Button Head
Socket Cap Screw
M4-0.7 x 12mm

4X – Button Head
Socket Cap Screw
M4-0.7 x 20mm

1X – Allen Wrench,
5mm

4X – Spacer, OD=9mm,
ID=5mm, Length=8mm


2X – Cross Head Screw
M6 x 60mm

2X – Roll-in T-Nut,
Slot size 10, 45 series
M6-1.0 thread

2X – Roll-in T-Nut,
Slot size 8, 30 series,
M6-1.0 thread

2X – Roll-in T-Nut,
Slot size 8, 15/40 series
M6-1.0 thread

2X – Roll-in T-Nut,
Slot size 6, 10 series
1/4-20 thread



2X Button Head
Socket Cap Screw
and Roll-in T-Nut to
fit required slot size

4X M4-0.7 x 12mm
or M4-0.7 x 20mm and
9mm spacer if needed

