

DURAPULSE GS4 AC DRIVE USER MANUAL TABLE OF CONTENTS



CONTENTS

GS4 USER MANUAL TOC

<i>WARNINGS AND TRADEMARKS</i>	W-1
<i>WARNING</i>	W-1
<i>Trademarks.</i>	W-1
<i>AVERTISSEMENT.</i>	W-2
<i>Marques de commerce</i>	W-2
<i>Warnings.</i>	W-3
<i>DURAPULSE GS4 USER MANUAL REVISION HISTORY</i>	H-1
<i>DURAPULSE GS4 AC DRIVE USER MANUAL TABLE OF CONTENTS</i>	TOC-1
<i>CHAPTER 1: GETTING STARTED</i>	1-1
<i>User Manual Overview</i>	1-2
<i>Overview of this Publication</i>	1-2
<i>Who Should Read This Manual.</i>	1-2
<i>Supplemental Publications</i>	1-2
<i>Technical Support</i>	1-2
<i>Special Symbols</i>	1-2
<i>Purpose of AC Drives</i>	1-3
<i>Selecting the Proper Drive Rating</i>	1-3
<i>Determine Motor Full-Load Amperage (FLA)</i>	1-3
<i>Determine Motor Overload Requirements</i>	1-3
<i>Determine Application Type; Constant Torque or Variable Torque</i>	1-3
<i>Installation Altitude</i>	1-4
<i>Determine Maximum Enclosure Internal Temperature</i>	1-5
<i>Derate Output Current Based on Carrier Frequency (if necessary)</i>	1-6
<i>DURApulse GS4 AC Drive Environmental Information</i>	1-9
<i>Storage and Transportation.</i>	1-9
<i>Environmental Conditions</i>	1-9
<i>DURApulse GS4 AC Drive Specifications</i>	1-10
<i>230V Class – Constant Torque – (Model-Specific Specifications)</i>	1-10
<i>230V Class – Variable Torque – (Model-Specific Specifications)</i>	1-11
<i>460V Class – Constant & Variable Torque – (Model-Specific Specifications)</i>	1-12
<i>Specifications Applicable to All GS4 Models</i>	1-14
<i>Receiving and Inspection</i>	1-15
<i>Drive Package Contents.</i>	1-15
<i>Model Number Explanation</i>	1-16
<i>Nameplate Information.</i>	1-16
<i>Unpacking Your GS4 DURApulse AC Drive</i>	1-17
<i>Lifting Eye Locations and Instructions</i>	1-17
<i>Unpacking the Drive.</i>	1-19

CHAPTER 2: INSTALLATION AND WIRING.	2-1
<i>Drive Models by Frame Size</i>	2-2
<i>Installation</i>	2-2
<i>Minimum Clearances and Air Flow.</i>	2-3
<i>Minimum Clearance Distances</i>	2-3
<i>Airflow and Power Dissipation</i>	2-6
<i>Dimensions</i>	2-7
<i>Circuit Connections – RFI Jumper</i>	2-14
<i>RFI Jumper Removal.</i>	2-14
<i>Isolating Main Power from Ground</i>	2-15
<i>Floating Ground System (IT Systems)</i>	2-16
<i>Asymmetric Ground System (Corner Grounded TN Systems)</i>	2-16
<i>Circuit Connections – Warnings and Notes</i>	2-17
<i>Danger!</i>	2-17
<i>Wiring Terminal Access</i>	2-20
<i>Control Terminal Access.</i>	2-20
<i>Removing the Control Terminal Block</i>	2-21
<i>Main Circuit Wiring Terminals</i>	2-22
<i>Main Terminal Specifications</i>	2-22
<i>Wiring Terminal Connector Dimensions – Main-Circuit Terminals.</i>	2-24
<i>Main Terminal Diagrams</i>	2-28
<i>Main Circuit Wiring Diagrams</i>	2-30
<i>Control Circuit Wiring Terminals</i>	2-31
<i>Control Terminal Specifications.</i>	2-31
<i>Control Terminal Block Diagram & Wiring Specifications</i>	2-34
<i>Control Terminal Wiring Instructions.</i>	2-34
<i>Control Circuit Wiring Diagrams</i>	2-35
<i>Digital Inputs.</i>	2-35
<i>Full I/O with Sinking Inputs.</i>	2-36
<i>Full I/O with Sourcing Inputs</i>	2-37
CHAPTER 3: KEYPAD OPERATION AND QUICKSTART.	3-1
<i>The DURApulse GS4 Digital Keypad</i>	3-2
<i>GS4 Start-Up Display</i>	3-4
<i>Status Page.</i>	3-4
<i>Menu Page.</i>	3-5
<i>Quick-Start – Quick-Start Page.</i>	3-6
<i>Keypad Fault Codes</i>	3-16

CHAPTER 4: AC DRIVE PARAMETERS	4-1
DURApulse GS4 Parameter Summary	4-2
Motor Parameters Summary (P0.xx)	4-2
Ramps Parameters Summary (P1.xx)	4-3
V/Hz Parameters Summary (P2.xx)	4-4
Digital Parameters Summary (P3.xx)	4-6
Analog Parameters Summary (P4.xx)	4-10
Presets Parameters Summary (P5.xx)	4-13
Protection Parameters Summary (P6.xx)	4-14
PID Parameters Summary (P7.xx)	4-18
Display Parameters Summary (P8.xx)	4-19
Serial Communication Parameters Summary (P9.xx)	4-22
Pump Parameters Summary (P10.xx)	4-26
Fault Parameters Summary (P11.xx)	4-27
DURApulse GS4 Parameter Details	4-30
Explanation of Parameter Details format	4-30
Group P0.xx Details – Motor Parameters	4-30
Group P1.xx Details – Ramps Parameters	4-36
Group P2.xx Details – V/Hz Parameters	4-46
Group P3.xx Details – Digital Parameters	4-60
Group P4.xx Details – Analog Parameters	4-89
Analog Input Parameter Examples	4-108
Group P5.xx Details – Presets Parameters	4-119
Group P6.xx Details – Protection Parameters	4-121
Group P7.xx Details – PID Parameters	4-160
Group P8.xx Details – Display Parameters	4-171
Group P9.xx Details – Serial Communication Parameters	4-178
Block Transfer Explanation	4-189
Group P10.xx Details – Pump Parameters	4-190
Pump Parameters Details	4-191
Timing Charts for Circulative Control Modes P10.01 through P10.08	4-194
Terminal Specifications for GS4-06TR (Optional Six-Relay Output Card)	4-200
Wiring Diagrams for Cyclical Pump Control	4-200
Group P11.xx Details – Fault Parameters	4-203

CHAPTER 5: SERIAL COMMUNICATIONS	5-1
<i>Communications Parameters Summary</i>	5-2
<i>Summary – Serial Communication Parameters</i>	5-2
<i>Summary – Block Transfer Parameters</i>	5-5
<i>Serial Modbus Status Addresses</i>	5-6
<i>Status Addresses (Read Only)</i>	5-6
<i>Serial Communications Overview</i>	5-8
<i>Serial Communications Connectivity</i>	5-8
<i>Minimum AC Drive Parameter Settings For Serial Communication</i>	5-8
<i>Common Third-Party Modbus RTU Masters</i>	5-9
<i>AutomationDirect PLCs as Modbus Master</i>	5-9
<i>Connecting Communication Cables</i>	5-10
<i>Detailed Serial Modbus Communication Information</i>	5-12
<i>Data Format</i>	5-12
<i>Communication Protocol</i>	5-13
<i>CMD (command code) and DATA (data characters)</i>	5-14
<i>BACnet Serial Communication</i>	5-18
<i>About BACnet</i>	5-18
<i>Parameter Summary for BACnet</i>	5-18
<i>GS4 BACnet Object and Property</i>	5-19
<i>Steps to Setup the GS4 Parameters for BACnet</i>	5-23
<i>BACnet Protocol Implementation Conformance Statement</i>	5-24
CHAPTER 6: MAINTENANCE AND TROUBLESHOOTING	6-1
<i>Maintenance and Inspections</i>	6-2
<i>Monthly Inspection</i>	6-2
<i>Annual Inspection</i>	6-2
<i>Recharge Capacitors (for drives not in service)</i>	6-3
<i>Recommended Inspection Schedules</i>	6-4
<i>Troubleshooting</i>	6-8
<i>Warning Codes</i>	6-8
<i>Fault Codes</i>	6-16
<i>Typical AC Drive Problems and Solutions</i>	6-26
<i>Grease and Dirt Problems</i>	6-26
<i>Fiber Dust Problem</i>	6-27
<i>Corrosion Problem</i>	6-28
<i>Industrial Dust Problem</i>	6-29
<i>Wiring and Installation Problem</i>	6-30
<i>Digital Input/Output Terminal Problems</i>	6-31
CHAPTER 7: GSOFT2 – GETTING STARTED	7-1
<i>GS4 Drive Configuration Software</i>	7-2
<i>System Requirements</i>	7-2
<i>Installation Guide</i>	7-3
<i>System Requirement Configuration</i>	7-3
<i>Software Installation</i>	7-4
<i>Opening GSoft2 Software Program</i>	7-6
<i>Software Functions</i>	7-7
<i>Firmware Upgrade Notes</i>	7-10
<i>GSoft2 Help File Note</i>	7-10

CHAPTER 8: GSLOGIC INTRODUCTION.	8-1
Purpose of This Chapter	8-2
For More Detailed Information.	8-2
GSLogic Introduction	8-2
GS4 PLC Summary.	8-3
Introduction	8-3
Notes on Using GSLogic, the GS4 PLC, and the GS4 Drive.	8-4
Getting Started	8-6
Connect to PLC.	8-6
Installation of GSLogic Programming Software.	8-9
System Requirements	8-9
About Getting Started.	8-9
Software and Online Help Files.	8-9
Technical Support	8-9
Installing GSLogic Programming Software	8-10
Program Writing.	8-12
Connecting GSLogic PC to GS4 PLC	8-12
Basic Ladder Program Example.	8-17
Program Download	8-19
Program Monitoring.	8-20
GS4 GSLogic Program Examples	8-21

APPENDIX A: ACCESSORIES	A-1
EMI Input Filters	A-2
EMI Filter Dimensions	A-3
EMI Filter Installation	A-5
Reflective Wave Phenomenon	A-6
Recommended Motor Cable Length.	A-6
Motor Cable Length Charts.	A-7
Fuses	A-8
Line/Load Reactors	A-9
Line/Load Reactors Selection Charts.	A-9
DC Reactors (Choke) Specification Charts	A-11
Line/Load Reactor Specification Charts	A-12
Line Reactor Dimensions	A-13
Line Reactor Applications and Wiring Connections.	A-19
Dynamic Braking	A-22
Braking Units.	A-22
USB to RS-485 PC Adapter	A-23
USB-485M to GS4 Wiring and Pin-out.	A-23
Conduit Box Kit	A-24
Conduit Box Installation – Frames D0 and D	A-25
Conduit Box Installation – Frame E.	A-26
Conduit Box Installation – Frame F.	A-27
Conduit Box Installation – Frame G	A-28
Flange Mounting Kits (Frames A, B, C).	A-30
Flange Mounting Kits – Frame A	A-30
Flange Mounting Kits – Frame B	A-33
Flange Mounting Kits – Frame C	A-35
Instructions for Built-in Flange Mounting (Frames D0, D, E, F).	A-37
Cutout Dimensions	A-37
Flange Mounting Instructions – Frames D0, D, E	A-38
Flange Mounting Instructions – Frame F	A-39
Spare Keypad	A-40
GS4-KPD	A-40
Keypad Panel Mounting Kit GS4-BZL	A-42
Spare Fan Kits	A-44
Fan Removal	A-47

APPENDIX B: OPTIONAL I/O AND COMMUNICATION CARDS	B-1
Introduction	B-2
Removing the Card Slot Cover	B-2
Option Card Installation and Removal.	B-4
Installation	B-4
Removal	B-4
Optional I/O Cards	B-5
GS4-06CDD Combo I/O card	B-5
GS4-06NA Input card	B-7
GS4-06TR Output card	B-7
Optional Communications Cards.	B-8
GS4-MODTCP and GS4-CM-ENETIP IP Address and Network Configuration.	B-9
GS4-CM-MODTCP Specifications.	B-10
GS4-CM-MODTCP LED Indicators and Troubleshooting	B-12
GS4-CM-MODTCP Common Communication Parameters	B-13
GS4-CM-MODTCP Control Words	B-14
GS4-CM-MODTCP Status Words	B-15
GS4-CM-ENETIP Specifications.	B-16
GS4-CM-ENETIP LED Indicators and Troubleshooting	B-17
GS4-CM-ENETIP Common Parameters	B-18
GS4-CM-ENETIP EtherNet/IP I/O Messaging (Implicit Messaging)	B-19
GS4-CM-ENETIP Explicit Messaging	B-22
EtherNet/IP Communication Card Register Settings	B-28
Using Speed Mode as a Control Method	B-28
APPENDIX C: ANALOG AND DIGITAL I/O PARAMETER MAPS	C-1
Introduction	C-2
GS4 Digital Inputs – Main Control Board	C-3
GS4 Digital Outputs – Main Control Board	C-4
GS4 Digital Inputs – Option Cards	C-5
GS4 Digital Outputs – Option Cards	C-6
GS4 Digital Outputs – Virtual.	C-7
GS4 Analog Common Parameters	C-8
GS4 Analog Input 1 Parameters	C-8
GS4 Analog Input 2 Parameters	C-9
GS4 Analog Input 3 Parameters	C-10
GS4 Analog Output 1 Parameters	C-11
GS4 Analog Output 2 Parameters	C-11
GS4 Frequency Output Parameters	C-11

APPENDIX D: USING GS4 AC DRIVES WITH AUTOMATIONDIRECT PLCs.	D-1
Appendix D Overview	D-2
Sinking/Sourcing Basics	D-2
GS4-to-PLC I/O Wiring Examples	D-4
Drive Wired with DC Sinking Inputs (PLC output card is sourcing)	D-4
Drive Wired with DC Sourcing Inputs (PLC output card is sinking)	D-4
Drive Wired with DC Sinking Outputs (PLC input card is sourcing)	D-5
Drive Wired with DC Sourcing Outputs (PLC input card is sinking)	D-5
Drive Relay Outputs Wired with Sinking PLC Modules	D-6
Drive Relay Outputs Wired with Sourcing PLC Modules	D-6
Drive Analog Inputs	D-7
Analog Input Wired for Voltage and Current	D-7
Drive Analog Outputs	D-8
Analog Output Wired for Voltage and Current	D-8
Drive Frequency Output (High-speed pulse output)	D-9
Communication with GS4 Drives	D-10
Getting Started	D-10
Serial Modbus Monitoring and Control	D-10
ModTCP (Ethernet) Monitor and Control	D-15
EtherNet/IP Monitor and Control	D-16
GS4-CM-ENETIP EtherNet/IP I/O Messaging (Implicit Messaging)	D-16
Program Examples Using AutomationDirect CLICK PLC	D-18
Modbus RTU CLICK Program Example	D-18
Modbus TCP CLICK Program Example	D-22
APPENDIX E: SAFE TORQUE OFF	E-1
Safe Function Failure Rate	E-2
Safe Torque Off Terminal Function Description	E-2
Wiring Diagrams	E-3
Internal STO Circuit	E-3
Control Loop Wiring Diagrams	E-3
STO Parameters	E-4
Operating Sequence Description	E-5
STO P6.71=0	E-5
STO P6.71=0, P6.29=1	E-5
STO P6.71=1	E-5
STL1 P6.71=1, P6.29=0	E-6
STL2 P6.71=1, P6.29=1	E-6
Error Codes for STO Function	E-6

<i>APPENDIX F: PID CONTROL</i>	F-1
<i>Function of PID Control</i>	F-2
<i>What Does PID Control Accomplish?</i>	F-2
<i>PID Control Analogy</i>	F-2
<i>Common Applications for PID Control</i>	F-3
<i>Definition of PID Loop "Directions"</i>	F-3
<i>Forward-Acting PID Loop (Heating Loop) (Negative-Feedback Loop)</i>	F-3
<i>Reverse-Acting PID Loop (Cooling Loop) (Positive-Feedback Loop)</i>	F-3
<i>PID Control Overview</i>	F-4
<i>Concept of GS4 PID Control & Tuning</i>	F-5
<i>Proportional Gain (P)</i>	F-5
<i>Integral Time (I)</i>	F-5
<i>Derivative Value (D)</i>	F-6
<i>Proportional Integral Control (PI)</i>	F-6
<i>Proportional Derivative Control (PD)</i>	F-6
<i>Proportional Integral Derivative Control (PID)</i>	F-6
<i>Tuning Example for PID Control</i>	F-7
<i>DURApulse GS4 and GS3 PID Parameter Comparisons</i>	F-9
<i>GS4 Parameters Involved in PID Control – Summary</i>	F-10
<i>GS4 Parameters Involved in PID Control – Details</i>	F-11
<i>GS4 Parameters Involved in PID Control – Details</i>	F-11

BLANK
PAGE