

# Table of Contents

---

## Chapter 1: Introduction

<b>Manual Overview</b> .....	<b>1-2</b>
Overview of this Manual .....	1-2
Other Reference Materials .....	1-2
Who Should Read This Manual .....	1-2
Technical Support .....	1-2
<b>Conventions Used</b> .....	<b>1-3</b>
Key Topics for Each Chapter .....	1-3
<b>Ethernet Base Controller Overview</b> .....	<b>1-4</b>
I/O Values Stored in Cache Memory .....	1-4
Industry Standard Ethernet .....	1-5
H2-EBC(100) and H2-EBC-F .....	1-5
H4-EBC and H4-EBC-F .....	1-5
RS232C Serial Port .....	1-5

## Chapter 2: Installing the H2-EBC(100), H2-EBC-F or H4-EBC(-F)

<b>EBC Network Identifiers</b> .....	<b>2-2</b>
<b>Setting the Module ID</b> .....	<b>2-2</b>
Several Methods for Setting Module ID .....	2-2
Setting Module ID with DIP Switches .....	2-2
Setting Module ID with Software Tool .....	2-2
<b>The H2 Series EBC DIP Switch</b> .....	<b>2-3</b>
The H2-EBC(100) & H2-EBC-F DIP Switch .....	2-3
<b>The H4 Series EBC DIP Switch</b> .....	<b>2-4</b>
The H4-EBC(-F) DIP Switch .....	2-4
<b>Inserting the H2 Series EBC into the Base</b> .....	<b>2-5</b>
<b>Intalling the H4 Series EBCs onto the Base</b> .....	<b>2-5</b>
<b>DL205 Power Wiring and Grounding</b> .....	<b>2-6</b>
Base Wiring .....	2-6
<b>H4 Series EBC Power Wiring and Grounding</b> .....	<b>2-7</b>
EBC Wiring .....	2-7
<b>10BaseT/100BaseT Network Cabling</b> .....	<b>2-8</b>
EBC Supports Two Standards .....	2-8
10/100BaseT Connections .....	2-8

---

<b>10BaseFL Network Cabling</b> .....	<b>2-9</b>
EBC Supports Two Standards .....	2-9
10BaseFL Connections .....	2-9
Fiber Optic Cable .....	2-9
Fiber Optic Module ST Connector .....	2-9
<b>Maximum Ethernet Cable Length</b> .....	<b>2-10</b>
<b>Calculating the Power Budget for the DL205 with H2 Series EBCs</b> .....	<b>2-11</b>
Managing your Power Resource .....	2-11
EBC Power Specifications .....	2-11
Module Power Requirements .....	2-11
<b>Power Consumption Chart (DL205 Modules)</b> .....	<b>2-12</b>
Power Budget Calculation Example .....	2-13
Power Budget Calculation Worksheet .....	2-14
<b>Calculating the Power Budget for the H4 Series EBCs</b> .....	<b>2-15</b>
Managing your Power Resource .....	2-15
EBC and Expansion Base Power Specifications .....	2-15
Module Power Requirements .....	2-15
<b>Power Consumption Chart (DL405 Modules)</b> .....	<b>2-16</b>
Power Budget Calculation Example .....	2-17
Power Budget Calculation Worksheet .....	2-18
<b>DL405 Local and Expansion I/O</b> .....	<b>2-19</b>
Local Base and I/O .....	2-19
Local Expansion Base and I/O .....	2-19

## Chapter 3: Configuring the EBCs Using NetEdit3

<b>NetEdit3 Software</b> .....	<b>3-2</b>
Installing NetEdit3 .....	3-2
Launching NetEdit3 .....	3-3
The NetEdit3 Screen .....	3-3
Adding Network Protocol Support to the NetEdit3 PC .....	3-4
<b>Using NetEdit3</b> .....	<b>3-5</b>
Ethernet Communication Protocol .....	3-5
Ethernet Address .....	3-6
Module Type, IP Address and ID .....	3-6
Module Info> General Information .....	3-7
Module Info> Ethernet Stats .....	3-7
EBC Settings .....	3-7
EBC Settings>Configuration>General .....	3-8
<b>IP Address</b> .....	<b>3-8</b>
EBC Settings>Configuration>Serial Port .....	3-9
EBC Settings>Utils>Show Base Contents .....	3-10
EBC Settings>Firmware .....	3-10
FileMenu>Live Update .....	3-11
F / B / C Columns .....	3-11

<b>Using NetEdit3 to Configure the H4–EBC(–F) Base</b> .....	<b>3–12</b>
EBC Settings> Configuration>I/O Base .....	3–12
Configuring Analog Modules .....	3–12
Configuring the High Speed Counter Module .....	3–12
<b>Locating the Ethernet Address Label</b> .....	<b>3–13</b>
Ethernet Address .....	3–13

## Chapter 4: MODBUS TCP/IP for H2–EBC100

<b>MODBUS TCP/IP</b> .....	<b>4–2</b>
Client / Server Model .....	4–2
Protocol Description .....	4–2
<b>Supported MODBUS Function Codes</b> .....	<b>4–4</b>
<b>MODBUS 584/984 Addressing</b> .....	<b>4–5</b>
<b>MODBUS 584/984 Addressing for Function Code 3 Clients</b> .....	<b>4–6</b>
<b>H2–EBC100 System Memory</b> .....	<b>4–7</b>
<b>H2–EBC100 System Memory (continued)</b> .....	<b>4–8</b>
<b>H2–EBC100 System Memory (continued)</b> .....	<b>4–9</b>
<b>Current / Last State Error Codes</b> .....	<b>4–9</b>

## Chapter 5: H2–EBC100 DHCP & HTML Configuration

<b>H2–EBC100 DHCP</b> .....	<b>5–2</b>
DHCP Issues .....	5–2
<b>Disabling DHCP and Assigning a Static IP Address</b> .....	<b>5–2</b>
<b>Using HTML Configuration</b> .....	<b>5–3</b>
Connecting to the H2–EBC100 .....	5–3

## Chapter 6: Troubleshooting Guidelines

<b>Isolating a Communication Problem</b> .....	<b>6–2</b>
Diagnostic Tools and Techniques .....	6–2
<b>Troubleshooting Chart</b> .....	<b>6–2</b>
<b>EBC Module Diagnostic LEDs</b> .....	<b>6–4</b>
EBC LEDs .....	6–4
<b>Using NetEdit3 for Troubleshooting</b> .....	<b>6–6</b>
Select a Module .....	6–5
Module Info> General Information .....	6–5
Change Protocol .....	6–6
Ethernet Stats .....	6–6
Replacing the EBC Module .....	6–6
<b>Diagnosing Network Cable Problems</b> .....	<b>6–8</b>

## Appendix A: General Specifications

H2 Series and H4 Series EBC Specifications .....	A-2
Serial Port Specifications .....	A-2
Ethernet Standards .....	A-3

## Appendix B: Using the H2 Series EBC with Think & Do

Configuring the DL205 I/O Base .....	B-2
Mapping H2-EBC I/O Points .....	B-2
Launching Connectivity Center Tool .....	B-2
Connecting to the EBC .....	B-2
Mapping I/O Points to Data Items .....	B-2
I/O Module Status Word / Bits .....	B-3
Using EZTouch/EZText Panel with the RJ-12 Serial Port .....	B-4
Adding Operator Interface Device .....	B-4
Using Monitor I/O to Verify Panel Operation .....	B-5

## Appendix C: Using the H4 Series EBC with Think & Do

Configuring the DL405 I/O Base with H4 Series EBCs .....	C-2
Starting I/O View .....	C-3
Starting a New Screen in I/O View .....	C-3
Selecting a Driver .....	C-4
H4-EBC Base Configuration Screen .....	C-5
Identifying Analog Modules .....	C-6

## Appendix D: Using the H2 Series EBC with KEPDirect OPC Server

Introduction to KEPDirect OPC Server .....	D-2
Introduction to OPC .....	D-2
DDE Support .....	D-2
KEPDirect .....	D-2
KEPDirect Project: Adding and Configuring a Channel .....	D-4
Running the Server .....	D-4
Adding a Channel .....	D-4
Selecting the Device Driver .....	D-5
Selecting the Network Adapter .....	D-5
Setting the Server Writes Optimizations .....	D-6
Saving the New Channel Settings .....	D-7
Using Multiple Channels in a Project .....	D-7
KEPDirect Project: Adding and Configuring a Device .....	D-8
Adding a Device .....	D-8

---

Selecting the Device Model .....	D-8
Setting the Device Timeout Properties .....	D-9
Automatic OPC Tag Database Generation .....	D-10
Saving the New Device Settings .....	D-10
<b>KEPDirect Project: Adding Tags to the Project .....</b>	<b>D-11</b>
User Defined Tags .....	D-11
<b>H2 Series EBC I/O Addressing .....</b>	<b>D-14</b>
H2-EBC I/O Addressing Example .....	D-14

## **Appendix E: Using the KEPDirect OPC Quick Client**

<b>Creating a KEPDirect Quick Client Project .....</b>	<b>E-2</b>
Connecting the Client to the OPC Server .....	E-2
Creating a Client Group .....	E-2
Selecting a Group Item .....	E-3
Item Operations .....	E-4
<b>Using the RJ12 Serial Port in ASCII Mode .....</b>	<b>E-5</b>

---