

Table of Contents

Chapter 1: Introduction

Manual Overview	1-2
Overview of this Manual	1-2
Other Reference Materials	1-2
Who Should Read This Manual	1-2
Technical Support	1-2
Conventions Used	1-3
Key Topics for Each Chapter	1-3
Ethernet Base Controller Overview	1-4
I/O Values Stored in Cache Memory	1-4
Industry Standard Ethernet	1-5
H2-EBC(100) and H2-EBC-F	1-5
H4-EBC and H4-EBC-F	1-5
RS232C Serial Port	1-5

Chapter 2: Installing the H2-EBC(100), H2-EBC-F or H4-EBC(-F)

EBC Network Identifiers	2-2
Setting the Module ID	2-2
Several Methods for Setting Module ID	2-2
Setting Module ID with DIP Switches	2-2
Setting Module ID with Software Tool	2-2
The H2 Series EBC DIP Switch	2-3
The H2-EBC(100) & H2-EBC-F DIP Switch	2-3
The H4 Series EBC DIP Switch	2-4
The H4-EBC(-F) DIP Switch	2-4
Inserting the H2 Series EBC into the Base	2-5
Intalling the H4 Series EBCs onto the Base	2-5
DL205 Power Wiring and Grounding	2-6
Base Wiring	2-6
H4 Series EBC Power Wiring and Grounding	2-7
EBC Wiring	2-7
10BaseT/100BaseT Network Cabling	2-8
EBC Supports Two Standards	2-8
10/100BaseT Connections	2-8

10BaseFL Network Cabling	2-9
EBC Supports Two Standards	2-9
10BaseFL Connections	2-9
Fiber Optic Cable	2-9
Fiber Optic Module ST Connector	2-9
Maximum Ethernet Cable Length	2-10
Calculating the Power Budget for the DL205 with H2 Series EBCs	2-11
Managing your Power Resource	2-11
EBC Power Specifications	2-11
Module Power Requirements	2-11
Power Consumption Chart (DL205 Modules)	2-12
Power Budget Calculation Example	2-13
Power Budget Calculation Worksheet	2-14
Calculating the Power Budget for the H4 Series EBCs	2-15
Managing your Power Resource	2-15
EBC and Expansion Base Power Specifications	2-15
Module Power Requirements	2-15
Power Consumption Chart (DL405 Modules)	2-16
Power Budget Calculation Example	2-17
Power Budget Calculation Worksheet	2-18
DL405 Local and Expansion I/O	2-19
Local Base and I/O	2-19
Local Expansion Base and I/O	2-19

Chapter 3: Configuring the EBCs Using NetEdit3

NetEdit3 Software	3-2
Installing NetEdit3	3-2
Launching NetEdit3	3-3
The NetEdit3 Screen	3-3
Adding Network Protocol Support to the NetEdit3 PC	3-4
Using NetEdit3	3-5
Ethernet Communication Protocol	3-5
Ethernet Address	3-6
Module Type, IP Address and ID	3-6
Module Info> General Information	3-7
Module Info> Ethernet Stats	3-7
EBC Settings	3-7
EBC Settings>Configuration>General	3-8
IP Address	3-8
EBC Settings>Configuration>Serial Port	3-9
EBC Settings>Utils>Show Base Contents	3-10
EBC Settings>Firmware	3-10
FileMenu>Live Update	3-11
F / B / C Columns	3-11

Using NetEdit3 to Configure the H4-EBC(-F) Base	3-12
EBC Settings> Configuration>I/O Base	3-12
Configuring Analog Modules	3-12
Configuring the High Speed Counter Module	3-12
Locating the Ethernet Address Label	3-13
Ethernet Address	3-13

Chapter 4: MODBUS TCP/IP for H2-EBC100

MODBUS TCP/IP	4-2
Client / Server Model	4-2
Protocol Description	4-2
Supported MODBUS Function Codes	4-4
MODBUS 584/984 Addressing	4-5
MODBUS 584/984 Addressing for Function Code 3 Clients	4-6
H2-EBC100 System Memory	4-7
H2-EBC100 System Memory (continued)	4-8
H2-EBC100 System Memory (continued)	4-9
Current / Last State Error Codes	4-9

Chapter 5: H2-EBC100 DHCP & HTML Configuration

H2-EBC100 DHCP	5-2
DHCP Issues	5-2
Disabling DHCP and Assigning a Static IP Address	5-2
Using HTML Configuration	5-3
Connecting to the H2-EBC100	5-3

Chapter 6: Troubleshooting Guidelines

Isolating a Communication Problem	6-2
Diagnostic Tools and Techniques	6-2
Troubleshooting Chart	6-2
EBC Module Diagnostic LEDs	6-4
EBC LEDs	6-4
Using NetEdit3 for Troubleshooting	6-6
Select a Module	6-5
Module Info> General Information	6-5
Change Protocol	6-6
Ethernet Stats	6-6
Replacing the EBC Module	6-6
Diagnosing Network Cable Problems	6-8

Appendix A: General Specifications

H2 Series and H4 Series EBC Specifications	A-2
Serial Port Specifications	A-2
Ethernet Standards	A-3

Appendix B: Using the H2 Series EBC with Think & Do

Configuring the DL205 I/O Base	B-2
Mapping H2-EBC I/O Points	B-2
Launching Connectivity Center Tool	B-2
Connecting to the EBC	B-2
Mapping I/O Points to Data Items	B-2
I/O Module Status Word / Bits	B-3
Using EZTouch/EZText Panel with the RJ-12 Serial Port	B-4
Adding Operator Interface Device	B-4
Using Monitor I/O to Verify Panel Operation	B-5

Appendix C: Using the H4 Series EBC with Think & Do

Configuring the DL405 I/O Base with H4 Series EBCs	C-2
Starting I/O View	C-3
Starting a New Screen in I/O View	C-3
Selecting a Driver	C-4
H4-EBC Base Configuration Screen	C-5
Identifying Analog Modules	C-6

Appendix D: Using the H2 Series EBC with KEPDirect OPC Server

Introduction to KEPDirect OPC Server	D-2
Introduction to OPC	D-2
DDE Support	D-2
KEPDirect	D-2
KEPDirect Project: Adding and Configuring a Channel	D-4
Running the Server	D-4
Adding a Channel	D-4
Selecting the Device Driver	D-5
Selecting the Network Adapter	D-5
Setting the Server Writes Optimizations	D-6
Saving the New Channel Settings	D-7
Using Multiple Channels in a Project	D-7
KEPDirect Project: Adding and Configuring a Device	D-8
Adding a Device	D-8

Selecting the Device Model	D-8
Setting the Device Timeout Properties	D-9
Automatic OPC Tag Database Generation	D-10
Saving the New Device Settings	D-10
KEPDirect Project: Adding Tags to the Project	D-11
User Defined Tags	D-11
H2 Series EBC I/O Addressing	D-14
H2-EBC I/O Addressing Example	D-14

Appendix E: Using the KEPDirect OPC Quick Client

Creating a KEPDirect Quick Client Project	E-2
Connecting the Client to the OPC Server	E-2
Creating a Client Group	E-2
Selecting a Group Item	E-3
Item Operations	E-4
Using the RJ12 Serial Port in ASCII Mode	E-5

Appendix F: H2-EBC(100) Analog Module Addressing

H2-EBC(100) Analog Module Addressing - Modbus TCP	E-2
H2-EBC(100) Analog Module Addressing - H2/4-ERM(100)	E-5