

C3SCGY/C4XSCSS - SERIES


BUL88195
REV. A

MOUNTING INSTRUCTIONS FOR C3SCGY AND C4XSCSS

NOTES:

- 1) To mount enclosure drill (4) x 0.500" holes as shown in Fig 1.2.
- 2) Make sure surface is flat or shim to suit. Use hex head bolts and sealing washers (rubber side against enclosure). Fig 1.3.
- 3) Install 3/8-16 mounting hardware as per sketch below. Torque to 180 IN-LBS. Washer should remain flat against enclosure surface see Fig 1.1.

FIG 1.1



Mounting kits are required to maintain marked Type rating.

Part No.	Material
EZPMFHD	Zinc Plated Mild Steel (Type 3, 12 and 4)
ESSMFHD	Type 304 Stainless Steel (Type 3, 12 and 4X)
ES16MFHD	Type 316 Stainless Steel (Type 3, 12 and 4X)

