

TABLE OF CONTENTS



Chapter 1: Introduction to the CTRIO & CTRIO2 Modules

CTRIO and CTRIO2 Module Overview	1-2
CTRIO Workbench	1-2
CTRIO Configuration	1-2
CTRIO Functions	1-3
Typical Counter Applications:	1-4
Support Systems for the CTRIO Modules	1-4
H0-CTRIO(2)	1-4
H2-CTRIO(2)	1-4
H4-CTRIO	1-4
T1H-CTRIO	1-4
CTRIO Specifications	1-5
H0-CTRIO(2) LED Indicators	1-7
H2-CTRIO(2) LED Indicators	1-8
H4-CTRIO LED Indicators	1-9
T1H-CTRIO LED Indicators	1-10
CTRIO Module Workflow Diagram	1-11

Chapter 2: Installation and Field Wiring

Installing the H0-CTRIO(2) Module	2-2
CPU and CTRIO Compatibility Chart	2-2
Setting H0-CTRIO(2) Jumpers	2-3
Wiring the H0-CTRIO(2) Module	2-4
H0-CTRIO(2) Quadrature Encoder Wiring Example	2-5
H0-CTRIO(2) TTL Quadrature Encoder Field Wiring	2-6

H0-CTRIO(2) TTL Input Wiring	2-7
H0- CTRIO(2) Output Wiring Schematic	2-8
H0-CTRIO(2) Stepper/Servo Drive Wiring Example	2-9
Solid State Input Device Wiring to the H0-CTRIO(2) Module	2-10
Installing the H2-CTRIO(2) Module	2-11
CPU and CTRIO Compatibility Chart	2-11
Setting H2-CTRIO(2) Jumpers	2-12
Wiring the H2-CTRIO(2) Module	2-13
H2- CTRIO(2) Quadrature Encoder Wiring Example	2-14
H2-CTRIO(2) TTL Quadrature Encoder Field Wiring	2-15
H2-CTRIO(2) TTL Input Wiring	2-16
H2- CTRIO(2) Output Wiring Schematic	2-17
H2-CTRIO(2) Stepper/Servo Drive Wiring Example	2-18
Solid State Input Device Wiring to the H2-CTRIO(2) Module	2-19
Installing the H4-CTRIO	2-20
CPU and CTRIO Compatibility Chart	2-20
Wiring the H4-CTRIO Module	2-21
H4-CTRIO Quadrature Encoder Wiring Example	2-22
H4-CTRIO TTL Quadrature Encoder Field Wiring	2-23
H4-CTRIO TTL Input Wiring	2-24
H4-CTRIO Output Wiring Schematic	2-25
H4-CTRIO Stepper/Servo Drive Wiring Example	2-26
Solid State Input Device Wiring to the H4-CTRIO Module	2-27
Installing the T1H-CTRIO	2-28
CPU and CTRIO Compatibility Chart	2-28
Wiring the T1H-CTRIO Module	2-29
T1H-CTRIO Output Field Wiring	2-30
T1H-CTRIO Input Field Wiring	2-30
T1H-CTRIO Quadrature Encoder Wiring Example	2-31
T1H-CTRIO TTL Quadrature Encoder Field Wiring	2-32

T1H-CTRIO TTL Input Wiring	2-33
T1H-CTRIO Output Wiring Schematic	2-34
T1H-CTRIO Stepper/Servo Drive Wiring Example	2-35
Solid State Input Device Wiring to T1H-CTRIO Module	2-36

Chapter 3: Introduction to CTRIO Workbench

Configuring a CTRIO Module for Do-more CPUs	3-2
What is CTRIO Workbench?	3-2
Installing CTRIO Workbench	3-3
Getting Started with CTRIO Workbench	3-3
Offline CTRIO Configuration	3-3
Online CTRIO Configuration	3-4
Successful On-line Connection	3-5
Module Modes of Operation	3-6
Program Mode - Configuring the CTRIO Module	3-6
Run Mode - Start Processing I/O Pulses with the CTRIO Module	3-6

Chapter 4: Configuring the Inputs

Configure I/O Dialog Overview	4-2
Input Function Selections	4-5
Supported Functions	4-5
Discrete Outputs Pre-Assigned to Input Functions	4-5
Counter Function	4-6
Quad Counter	4-7
Pulse Catch	4-8
Edge Timer	4-9
Dual Edge Timer	4-10
Reset 1 and Reset 2 (Hard Resets for Counters Only)	4-11
Soft Resets	4-11
Capture 1	4-12
Inhibit 1	4-12
Introduction to the Scaling Wizard	4-13

Scaling Wizard Examples for Counter Functions	4-13
Position Scaling (Counter)	4-14
Rate Scaling (Counter)	4-15
Using the Scaling Wizard with Timer Functions	4-16
Interval Scaling (Timer)	4-16

Chapter 5: Configuring the Outputs

Configure I/O Dialog Overview	5-2
Output Function Selections	5-5
Supported Functions	5-5
CTRIO Memory Usage: Pulse Profiles and Preset Tables	5-5
Raw Output	5-6
Discrete Outputs	5-7
Creating and Using the Programmable Limit Switch (CTRIO2 only)	5-8
Creating and Using the Output Preset Tables	5-10
Using the Discrete Outputs in Level Mode	5-11
Pulse Outputs	5-12
Creating Pulse Output Profile Tables	5-12
Trapezoid Profile	5-13
Trapezoid Plus Profile	5-14
S-Curve Profile	5-15
Symmetrical S-Curve Profile	5-16
Dynamic Positioning Profile	5-17
Dynamic Positioning Plus Profile	5-18
Dynamic Velocity Profile	5-19
Home Search Profile	5-20
Home Search Routines	5-21
Trapezoid with Limits Profile	5-22
Free Form Profile	5-25
Additional Pulse Profiles	5-26
Hx-CTRIO2 with Do-more	5-26

Chapter 6: Program Control

Do-more and Program Control	6-2
Input Memory Map for Data Transfers from CTRIO to DL CPUs	6-4
Input (n) Parameter Definitions	6-4
Input Function Status Bit Definitions	6-5
Output Status Bit Definitions (for Preset Table Control)	6-5
Output Status Bit Definitions (Pulse Output)	6-5
Output Memory Map for Data Transfers from DL CPUs to CTRIO	6-6
Output (n) Parameter Definitions	6-6
Input Function Control Bit Definitions	6-7
Output Control Bit Definitions (for Preset Table Control)	6-7
Output Control Bit Definitions (Pulse Output)	6-7
Output Control Bit Definitions (Raw Mode)	6-8
System Functions Status Bit Definitions	6-8
System Functions Control Bit Definitions	6-8
I/O Map Dialog	6-9
I/O Map with <i>Direct</i> LOGIC PLC (2 ranges mode)	6-9
I/O Map with <i>Direct</i> LOGIC PLC (4 ranges mode)	6-10
I/O Map with <i>Direct</i> LOGIC PLC with CTRIO in ERM/EBC Network	6-11
I/O Map with EBC/WinPLC	6-11
I/O Map with an H2-PBC or T1H-PBC Profibus DP Controller	6-12
Printing a Memory Map Report	6-13
Exporting to <i>Direct</i> SOFT	6-13
Addressing Conventions(with V-memory Examples for <i>Direct</i>LOGIC PLCs)	6-14
Example for Bit-accessed Data in PLC CPUs	6-14
Addressing High and Low Byte of Word Parameters	6-14
Addressing High and Low Word of DWord Parameters	6-14
Input Function Status/Control Bits and Parameters	6-15
Input Function Status Bit Definitions	6-15
Input Function Control Bit Definitions	6-15
Input Function Status DWord Parameters	6-15
Status Registers	6-16
Control Registers	6-16
Memory Mapping Example for D2-240 CPU	6-17

Input Functions	6-18
Counter & Quadrature Counter	6-18
Edge Timer and Dual Edge Timer	6-19
Edge and Dual Edge Timer Timeout Function	6-20
Pulse Catch Input Function	6-21
Runtime Changes to CTRIO Configured Preset Tables (DL PLCs)	6-22
Entry Number for Edit Table Entry Commands	6-23
Entry Type for Edit Table Entry Commands	6-23
Discrete Outputs Driven from a Scaled level	6-24
Load Preset Table Flowchart	6-25
Pulse Output Status/Control Bits and Command Codes (DL PLCs)	6-26
Output Status Bit Definitions (Pulse Output)	6-26
Output Control Bit Definitions (Pulse Output)	6-26
Output Control (D) Words (Pulse Output)	6-26
Command Code and Parameter Definitions	6-27
Status and Control Bits/Registers	6-28
Memory Mapping Example for D2-240 CPU	6-29
Pulse Output Profiles (DL PLCs)	6-30
Trapezoid, S-Curve, Symmetrical S-Curve, Home Search, Free Form Profiles	6-31
Trapezoid, S-Curve, Symmetrical S-Curve, Home Search, Free Form Flowchart	6-32
Running a Trapezoid, S-Curve, Symm. S-Curve, Home Search, Free Form Profile	6-33
Dynamic Positioning and Dynamic Positioning Plus	6-34
Dynamic Positioning and Dynamic Positioning Plus Flowchart	6-35
Dynamic Positioning and Dynamic Positioning Plus using the CTRIO Y0 and Y1	6-36
Dynamic Velocity	6-37
Dynamic Velocity using the CTRIO Y0 and Y1	6-37
Dynamic Velocity Mode Flowchart	6-38
Velocity Mode	6-39
Velocity Mode control on CTRIO Y0 & Y1	6-39
Velocity Mode Flowchart	6-40
Run to Limit Mode	6-41
Run to Limit Mode Flowchart	6-42
Run at Velocity on CTRIO Y0 & Y1 until Discrete Input Limit	6-43
Run to Position Mode	6-44
Run to Position Mode Flowchart	6-45

Run at Velocity on CTRIO until Input Function Value Position	6-46
System Functions	6-47
Reading All CTRIO's Internal Registers Flowchart	6-48
Writing to All CTRIO's Internal Registers Flowchart	6-49
Writing to One CTRIO Internal Register Flowchart	6-50

Chapter 7: Using Monitor I/O

Do-more and Monitor CTRIO	7-2
Using the Monitor I/O Dialog	7-2
I/O Status & Input Functions	7-3
Output Functions	7-4
System Functions	7-6
Monitor I/O Error Codes	7-7

Chapter 8: DirectLOGIC Programming Examples

DirectLOGIC Programming Examples Overview	8-2
Load and Run a Pulse Profile	8-3
Dynamic Positioning/Positioning Plus	8-4
Dynamic Velocity	8-5
Velocity Mode	8-6
Run to Limit Mode	8-7
Run to Position Mode	8-8
Run to Position Mode with DirectSOFT IBox Instructions	8-9
System Functions Examples Overview	8-10
Simulating Retentive Counter	8-11
Reading CTRIO Internal Registers	8-12

Chapter 9: Do-more Programming Examples

Do-more Programming Examples Overview	9-2
Load and Run a Pulse Profile	9-3
Dynamic Positioning/Positioning Plus	9-4
Dynamic Velocity	9-5

Velocity Mode9-6

Run to Limit Mode9-7

Run to Position Mode9-8

System Functions Examples Overview9-9

Simulating Retentive Counter9-9

Reading CTRIO Internal Registers9-10