

Index

Numbers

10BaseFL, 2–19
10BaseT, 2–19
62.5/125 MMF, 2–19

A

ACT LED, 4–4
Advanced Settings, 2–13
Aliases, 3–6, 3–8

B

Bulletin Board Service, 1–3

C

Cables, 2–19
 10BaseFL, 2–20
 10BaseT, 2–19
 crossover, 2–19
 distance limitations, 2–20
 fiber optic, 2–20
 length, 2–21
 patch, 2–19
 recommended 10BaseT, 2–20
 straight-through, 2–19
Communication status bits
 busy, 3–11
 error, 3–11
Configuration box, 2–13

Connectors

 10BaseFL, 2–19
 10BaseT, 2–19
 RJ45, 2–19
 ST bayonet, 2–19
CPU, use with ECOM, 2–13, 2–15, 2–16, 2–22

D

Data types, 3–7
DDE Server, 1–6
DIP switch
 H2-ECOM (-F), 2–5, 2–19
 H4-ECOM (-F), 2–6
DirectSOFT32
 for setting Network Identifiers, 2–14
 programming software, 1–4

E

ECOM Module, inserting in PLC base, 2–15
ERROR LED, 4–4
Ethernet, 1–6
 (MAC) address, 2–2, 2–9, 2–11, 2–13
 standards, A–3
Expansion bases, 2–16

F

Fiber Optic, cables, 2–20
Flash memory, 2–12

H

Hubs, 2–18

I

Interlocks, for RX/WX instructions, 3–17

IP Address, 2–2, 2–13

L

LEDs, for troubleshooting, 4–2

Link, 2–2

LINKGD LED, 4–4

Load Address instruction, 3–3

Load instruction, 3–3

Local expansion bases, 2–16

M

Memory types, 3–6, 3–8

Module ID, 2–2, 2–13

Multimode Fiber Optic, 2–19, 2–20

Multiple Read/Write Instructions, 3–17

N

Name identifier, 2–2

NetEdit

features, 2–8, 2–10, 2–12

running, 2–7

troubleshooting, 4–5

Network, 2–2, 2–17

cabling, 2–19

identifiers, 2–2

layouts, 2–13, 2–17

table of identifiers, 2–13

O

Octal numbering system, 3–6, 3–8

P

Patch cable, 2–19

PLC-to-PLC communications, 3–2

Power budget, 2–15

Programming Examples

multiple Read/Write instructions, 3–17

one Read instruction, 3–13

one Write instruction, 3–15

Protocols, 1–6

adding in your PC, 2–9, 2–11

IPX, 2–8, 2–10, 2–12

UDP/IP, 2–8, 2–10, 2–12

Q

Query Network, 2–9, 2–11

R

Read/Write instructions, 3–2, 3–3

References, 1–2

Repeaters, 2–18

RJ45, 2–19

RLL, 3–2

S

Sequencing

RX/WX instructions, 3–17

using control relays, 3–17

using shift register, 3–17, 3–20

Slot 0, 2–15

Slot table

H2-ECOM, 2–15

H4-ECOM, 2–16

Special Relays, 3–11

Specifications, A–2, A–4

ST, connectors, 2–19

T

Tables

- data types, 3–7
- network identifiers, 2–13
- special relays, 3–11
- usable slots, 2–15, 2–16

Technical support, 1–2

Topology, 2–17

- star, 2–17

Troubleshooting

- chart, 4–2
- using diagnostic LEDs, 4–2, 4–4
- using NetEdit, 4–6
- diagnosing network cable problems, 4–10

Truth table, 3–17

W

Web site, 1–2