

# Index

---

## A

Address, assignment, 3–12, 4–5  
Application  
  planning, 1–4  
  worksheets, 4–3, Appendix A

## B

BCD Numbers, displaying 3–8, 5–6  
BCD Double Numbers, displaying 3–8, 5–7  
Back-panel, layout, 1–5  
Baud Rate, 4–5  
Binary Numbers, displaying, 5–5, 5–11

## C

Communications Cable, recommended, 2–6  
Communications, problems, 5–12  
Computer Requirements, 4–3  
Configuration  
  preparation, 4–2  
  software, 4–2  
Configuration Cable, 2–5  
Configuring  
  base register address, 4–5  
  communications, 4–4  
  overview, 4–3  
  panel functions, 4–6  
Connecting Cables  
  pinouts, 2–7  
  selecting, 2–6

## D

Decimal point, placement, 3–9  
Dynamic Message  
  third line display, 3–8  
  display, 3–7  
  operation, 3–7  
  top line display, 3–8

## F

Floating Point Numbers, displaying, 3–11, 5–7, 5–10  
Frequently Asked Questions, 1–6

## L

LCD Screen, 1–4

## M

Memory Mapping  
  DL05/105/205/405, 3–12  
  DL305, 3–13  
  Allen–Bradley, 3–14  
Message Display  
  examples, 5–3, 5–9  
  operations, 3–2  
  types, 3–5

## N

NEMA Rating, 2–6

---

## O

### OP–WINEDIT

- configuration cable, 2–5
- configuration software, 4–2
- documentation, 4–2
- installation, 4–3
- overview, 1–6
- system requirements, 4–3
- user steps, 4–3

## P

PLC Timeout, 4–4

### Panel

- cutout dimensions, 2–2
- mounting dimensions, 2–2

Panel Configuration, problems, 5–12

Power Receptacle, 1–5

### Power Supply

- connections, 2–4
- requirements, 1–6, 2–3

## S

Serial Port, 1–5

### Specifications, 2–3

- communication link, 2–3
- environmental, 2–3
- NEMA rating, 2–3
- power connector, 2–3
- temperatures, 2–3

### Static Message

- display, 3–6
- operation, 3–6

## T

Troubleshooting, 5–12

## U

User Memory, overview, 3–15

## W

Web site, 1–2

---