

PRODUCT INFORMATION PACKET



Model No: 112529.00

Catalog No: 112529.00

White Duck™ General Purpose Motor, 1 HP, 1 Ph, 60 Hz, 115/230 V, 1800 RPM, 56C Frame, TEFC

Operational at 115/208-230 V @60HZ



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Phase	1	Output HP	1 Hp
Output KW	0.75 kW	Voltage	115/230 V
Speed	1725 rpm	Service Factor	1.15
Frame	56C	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	75 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	12.8/6.4 A	Power Factor	68
Duty	Continuous	Insulation Class	F
Design Code	N	KVA Code	K
Drive End Bearing Size	6205	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	N	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	NEMA 56	Overall Length	12.12 in
Frame Length	6.25 in	Shaft Diameter	0.625 in
Shaft Extension	1.88 in	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005278.07	Outline Drawing	607-0008-675A





WASHGUARD MOTOR

- SPECIAL FEATURES:
- 1. SHAFT SEALS & V-RING.
 - 2. PLUGGED DRAIN HOLES IN ENDBELLS & CONDUIT BOX.
 - 3. BUNA-N GASKETS THROUGHOUT.
 - 4. STAINLESS STEEL SHAFT, HARDWARE & NAMEPLATE.
 - 5. SOLID STATE SITCH MOUNTED TO CONDUIT BOX.

DASH NO.	"C"	"AD"	"XO"	DASH NO.	"C"	"AD"	"XO"
500A	10.37	2.00	2.00	500B	10.37	2.00	2.25
525A	10.62	2.25	2.00	525B	10.62	2.25	2.25
550A	10.87	2.50	2.00	550B	10.87	2.50	2.25
575A	11.12	2.75	2.00	575B	11.12	2.75	2.25
600A	11.37	3.00	2.00	600B	11.37	3.00	2.25
625A	11.62	3.25	2.00	625B	11.62	3.25	2.25
650A	11.87	3.50	2.00	650B	11.87	3.50	2.25
675A	12.12	3.75	2.00	675B	12.12	3.75	2.25
700A	12.37	4.00	2.00	700B	12.37	4.00	2.25


DRAWING REVISION D		REVISION BY GKB		REV DATE/É DATE 03/13/2026		TOLERANCES (EXCEPT AS NOTED): <table><tr><td>DEC.</td><td>INCH</td><td>mm</td><td>ANGLE</td></tr><tr><td>.X</td><td>±0.1</td><td>[±3]</td><td>±0.5°</td></tr><tr><td>.XX</td><td>±0.03</td><td>[±0.8]</td><td></td></tr><tr><td>.XXX</td><td>±0.005</td><td>[±0.13]</td><td></td></tr><tr><td>.XXXX</td><td>±0.0005</td><td>[±0.013]</td><td></td></tr></table> REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45° CORNER FILLETS: R.02 [.5] MACHINED SURFACES: <table><tr><td>125</td><td>INCH</td><td>3.2</td><td>mm</td></tr></table> mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY				DEC.	INCH	mm	ANGLE	.X	±0.1	[±3]	±0.5°	.XX	±0.03	[±0.8]		.XXX	±0.005	[±0.13]		.XXXX	±0.0005	[±0.013]		125	INCH	3.2	mm
DEC.	INCH	mm	ANGLE																														
.X	±0.1	[±3]	±0.5°																														
.XX	±0.03	[±0.8]																															
.XXX	±0.005	[±0.13]																															
.XXXX	±0.0005	[±0.013]																															
125	INCH	3.2	mm																														
REQUEST NUMBER ECR-0249863		APPROVED BY BAN		DATE 03/13/2026																													
REQUEST NUMBER DESCRIPTION UPDTED DASH NO AS PER ECR																																	
COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.																																	

DRAWN BY PG 02/08/11		Regal Beloit America, Inc.			
DATE		DESCRIPTION OUTLINE TEFC - RICID "C" FACE			
APPROVED BY					
DATE					
REFERENCE 028881		MATERIAL WASHGUARD		PROCESS/FINISH	
THIRD ANGLE PROJECTION 		SIZE B	DRAWING NUMBER 607-0008		SHEET 1 OF 1



VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.

LINE LEADS



	ROTATION FACING LEAD END	L1	L2	JOIN & INSULATE
HIGH VOLT	C.C.W.	T1	T4 T5	T2,T3 T8
	C.W.	T1	T4 T8	T2,T3 T5
LOW VOLT	C.C.W.	T1,T3 T8	T2,T4 T5	
	C.W.	T1,T3 T5	T2,T4 T8	

TOLERANCES UNLESS
OTHERWISE SPECIFIED

DECIMALS

.00 ± .01

.000 ± .005

.0000 ± .0005

FRACTIONS ± 1/64

ANGLES ± 1/2°

INCH/MM

LEESON ELECTRIC CORPORATION

DRAWN RSK 07/21/98

CH'K'D.

APPR.

SCALE 1=1

REF. 005278-01

FMF 131571

TITLE
EXTERNAL WIRING DIAGRAM
TYPE "C" W/O PROTECTOR

MAT'L.
DECAL - 004012
STOCK MOTORS TO USE DECAL 214-0122-001

FINISH

STANDARD

SIZE

A

DRAWING NO.

005278-07

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY
AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK
ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED



CERTIFICATION DATA SHEET

1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810

CATALOG #: 112529.00

CONN. DIAGRAM: 005278.07

OUTLINE: 607-0008-625A

MOUNTING: F1 ONLY

WINDING #: C634256 FR 3 G

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
1	0.75	1800	1725	56C	TEFC	K	N

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
1	60	115/208-230	12.8/6.4	ACROSS THE LINE	CONTINUOUS	F4	1.15	40

FULL LOAD EFF:	75	3/4 LOAD EFF:	72.8	1/2 LOAD EFF:	69.7	GTD. EFF		ELEC. TYPE
FULL LOAD PF:	68	3/4 LOAD PF:	58	1/2 LOAD PF:	45.6	70		CAP START IND RUN

F.L. TORQUE		LOCKED ROTOR AMPS		L.R. TORQUE		B.D. TORQUE		F.L. RISE°C
3 LB-FT		66 / 33		9 LB-FT 300 %		7 LB-FT 233 %		73

SOUND PRESSURE @ 3 FT.		SOUND POWER		ROTOR WK^2		MAX. WK^2		SAFE STALL TIME		STARTS / HOUR		APPROX. MOTOR WGT
64 dBA		74 dBA		0 LB-FT^2		0.1 LB-FT^2		10 SEC.		0		36 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAIN
C-FACE	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	WHITE - LEESON (EPOXY)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	STANDARD 56	NONE	NONE	1144 STRESSPROOF (C-223)	ROLLED STEEL
6205	6203						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE


ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz



LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE for AC MOTOR

Model No 112529.00Curve at 230
60
1Volts
HZ
HPHP 1.00PHASE 1VOLTS 115/208-230Catalog No 112529.00HZ 60RPM 1725

FL TORQUE 3 Lb.Ft
 BD TORQUE 7.0 Lb.Ft
 LR TORQUE 9 Lb.Ft

FL AMPS 12.8/6.4
 PU TORQUE 6.7 Lb.Ft
 LR AMPS 33

WINDING C634256-3

Date 3/14/2018