

Multi-Max Rails Kit: KIT-GMMR10

See Figure A

Included are four ea. of the following:

2424 Multi-Max Mounting Rail, #(24241035-WTI)
#10-32 x .38Lg. Flat Head Screw, #(9912636-87-10)

Included are eight ea. of the following:

Screw, #10 x .50Lg., Thread Cutting #(9912595-82-10)

See Figure B

Assemble Multi-Max Vertical Rail to Base using #10 thread cutting Screw and secure tightly as shown. Secure Stiffener to the Vertical Rail using #10-32 flat head Screw and secure tightly as shown. Actual Multi-Max Rail location is not specified. Factory suggested placement to be the furthest most corners of the base. Typical.

FIGURE A




FIGURE B

