



## SRB-E-402EM

- Plug-in screw terminals with coding
- Expander module for contact expansion
- 4 safety contacts, STOP 0
- 2 Signalling outputs

## Data

### Ordering data

Product type description	SRB-E-402EM
Article number (order number)	103041198
EAN (European Article Number)	4030661563411
eCl@ss number, version 12.0	27-37-18-19
eCl@ss number, version 11.0	27-37-18-19
eCl@ss number, version 9.0	27-37-18-19
ETIM number, version 7.0	EC001449
ETIM number, version 6.0	EC001449

### General data

Standards	EN IEC 62061 EN ISO 13849-1 EN IEC 60947-5-1 EN IEC 60947-5-3 EN IEC 60947-5-5 EN IEC 61508 EN IEC 60204-1 EN IEC 60947-1
Climatic stress	EN 60068-2-78
Housing material	Glass-fibre reinforced thermoplastic, ventilated
Gross weight	250 g

## General data - Features

Wire breakage detection	Yes
Removable Terminals	Yes
Feedback circuit	Yes
Automatic reset function	Yes
Earth connection detection	Yes
Integral system diagnostics, status	Yes
Number of auxiliary contacts	2
Number of LEDs	1
Number of normally closed (NC)	1
Number of safety contacts	4

## Safety classification

Standards	EN ISO 13849-1 EN IEC 61508
Stop-Category	0

## Safety classification - Relay outputs

Performance Level, stop 0, up to	e
Category, Stop 0	4
Diagnostic Coverage (DC) Level, Stop 0	≥ 99 %
PFH value, Stop 0	$2.00 \times 10^{-8}$ /h
Safety Integrity Level (SIL), Stop 0, suitable for applications in	3
Mission time	20 Year(s)
Common Cause Failure (CCF), minimum	65

## Mechanical data

Mechanical life, minimum	10,000,000 Operations
--------------------------	-----------------------

Mounting

Snaps onto standard DIN rail to EN 60715

### Mechanical data - Connection technique

Terminal designations	EN 60947-1
Termination	rigid or flexible Screw connection, plug-in
Cable section, minimum	0.25 mm <sup>2</sup>
Cable section, maximum	2.5 mm <sup>2</sup>
Tightening torque of Clips	0.5 Nm

### Mechanical data - Dimensions

Width	22.5 mm
Height	98 mm
Depth	115 mm

### Ambient conditions

Degree of protection of the enclosure	IP40
Degree of protection of the mounting space	IP54
Degree of protection of clips or terminals	IP20
Ambient temperature	-25 ... +60 °C
Storage and transport temperature	-40 ... +85 °C
Resistance to vibrations	10...55 Hz, Amplitude 0.35 mm, ± 15 %
Resistance to shock	10 g / 11 ms

### Ambient conditions - Insulation values

Rated impulse withstand voltage $U_{imp}$	4 kV
Overvoltage category	III
Degree of pollution	2

### Electrical data

Frequency range	50 Hz 60 Hz
Operating voltage	24 VAC -15 % / +10 % 24 VDC -15 % / +20 %
Ripple voltage	10 %
Rated operating voltage	24 VAC
Rated operating voltage	24 VDC
Rated AC voltage for controls, 50 Hz, minimum	20.4 VAC
Rated control voltage at AC 50 Hz, maximum	26.4 VAC
Rated AC voltage for controls, 60 Hz, minimum	20.4 VAC
Rated control voltage at AC 60 Hz, maximum	26.4 VAC
Rated AC voltage for controls at DC minimum	20.4 VDC
Rated control voltage at DC, maximum	28.8 VDC
Electrical power consumption	1.3 W
Electrical power consumption	2.2 VA
Contact resistance, maximum	0.1 $\Omega$
Note (Contact resistance)	in new state
Drop-out delay, maximum	35 ms
Pull-in delay at automatic start, maximum, typically	20 ms
Material of the contacts, electrical	Ag-Ni, self-cleaning, positive drive

### Electrical data - Safe relay outputs

Voltage, Utilisation category AC-15	230 VAC
Current, Utilisation category AC-15	4 A
Voltage, Utilisation category DC-13	24 VDC
Current, Utilisation category DC-13	4 A
Switching capacity, minimum	10 VDC
Switching capacity, minimum	10 mA
Switching capacity, maximum	250 VAC

Switching capacity, maximum 6 A

### Electrical data - Digital inputs

Conduction resistance, maximum 40  $\Omega$

### Electrical data - Relay outputs (auxiliary contacts)

Switching capacity, maximum 24 VDC

Switching capacity, maximum 2 A

### Electrical data - Electromagnetic compatibility (EMC)

EMC rating EMC-Directive

### Status indication

Indicated operating states Position relay K1/K2

### Note

Note (General) Inductive loads (e.g. contactors, relays, etc.) are to be suppressed by means of a suitable circuit.

## Pictures

### Product picture (catalogue individual photo)



ID: ksrb4f25  
| 887,8 kB | .jpg | 301.978 x 666.75 mm - 856 x 1890 px - 72 dpi  
| 95,4 kB | .png | 74.083 x 163.336 mm - 210 x 463 px - 72 dpi  
| 39,2 kB | .jpg | 56.092 x 123.472 mm - 159 x 350 px - 72 dpi

K.A. Schmersal GmbH & Co. KG, Möddinghofe 30, 42279 Wuppertal

The details and data referred to have been carefully checked. Images may diverge from original. Further technical data can be found in the manual. Technical amendments and errors possible.

Generated on: 19/06/2024, 10:10