



TABLE OF CONTENTS

Chapter 1: Hardware

Introduction.....	1-2
Conventions Used.....	1-2
General Information.....	1-3
Product Overview Stride SE2 Unmanaged Models	1-5
Product Overview Stride SE2 PoE Unmanaged Models.....	1-6
Product Overview Stride SE2 Managed Models.....	1-7
Switch Accessories.....	1-8
SFP Fiber Transceivers.....	1-8
Mounting Brackets	1-9
DIP Switch (Unmanaged DIN rail mounted switches).....	1-10
Reset (Managed Switches).....	1-11
LED Indicators.....	1-12
Installation, DIN Rail Mounting	1-14
Installation, Optional Panel Mounting	1-16
Installation, IP65 Switches Panel Mounting	1-17
Dimensional Drawings.....	1-18
Power Wiring.....	1-26
Communication Ports Wiring.....	1-29
Technical Specifications.....	1-32
Unmanaged Models.....	1-32
Unmanaged PoE Models	1-34
Unmanaged IP65 Rated Models	1-36
Managed Models	1-38

Chapter 2: Managed Switch Introduction

Connecting to the Switch the First Time.....	2-2
Why Do You Need a Managed Switch?.....	2-10
Enhanced Traffic Filtering	2-10
Troubleshooting	2-11
Redundancy	2-11
Security	2-12
Better Network Awareness.....	2-12

Chapter 3: Managed Switch Basic Features

Managed Switch Features	3-2
Switch Management Settings	3-3
Port Configuration.....	3-4
Change Password.....	3-5
Redundancy Settings.....	3-6
Spanning Tree Protocols.....	3-7
Recovery Time, Hops and Convergence	3-9
RSTP/STP Configuration	3-10
Port Priority	3-15
RSTP Examples	3-16
Multicast Filtering (IGMP).....	3-20
IGMP Protocol Settings	3-21
Static FDB Multicast	3-21
The Benefits of Enabling IGMP	3-22
Port Monitoring	3-23
Browser Access Protocol (HTTPS).....	3-24
Virtual LANs (VLANs).....	3-25
PVLAN – Private VLANs	3-27
VLAN with RSTP	3-30
VLAN Examples	3-32
Alarms	3-42

Chapter 4: Advanced Network Behavior Features

Traffic Priority (Priority Queuing QoS, Quality of Service)	4-2
802.1p Example	4-4
Port Trunk – Link Aggregation.....	4-7
Port Rate	4-9
AD-Ring	4-10
Concepts.....	4-10
Implementation of AD-Ring	4-11
Implementation of AD-Ring+.....	4-12
Implementation of AD-VLAN-Ring.....	4-13
AD-RP	4-18
Concept.....	4-18
Implementation.....	4-19
RSTP/STP Transparent Transmission	4-22
Link Check	4-23
Virtual Cable Check	4-23
Port Security	4-24
Port CRC Protect.....	4-24
Loop Detect	4-24
MAC Address Forwarding Database	4-24
DHCP Server	4-25
DHCP Snooping.....	4-27

Chapter 5: Switch Management and Network Information

LLDP	5-2
ARP	5-2
SNTP.....	5-2
SSH Server	5-3
SSH user with authentication type “Public Key”	5-7
RMON Statistics.....	5-12
RMON Group.....	5-12

Table of Contents

Syslog.....	5-13
SNMP	5-14
Implementation.....	5-14
Explanation	5-14
MIB Introduction.....	5-15
SNMPv3.....	5-16
Introduction	5-16
Implementation.....	5-16
Modbus TCP	5-17
EtherNet/IP	5-18
Firmware Update.....	5-18
Configuration Upload and Download	5-19
Load Default	5-19
Reboot.....	5-19

Appendix A: Default Settings

Default Settings.....	A-2
-----------------------	-----

Appendix B: Console Port Access

Console Port Access:.....	B-2
Serial Access	B-2
Telnet Access.....	B-6
View Types.....	B-8

Appendix C: CLI Commands

CLI Commands.....	C-2
Introduction	C-2
CLI Commands.....	C-3
Global Commands.....	C-3

Appendix D: Troubleshooting

Troubleshooting Fiber Connections.....	D-2
--	-----

Troubleshooting AD-Ring..... D-4
 Troubleshooting VLANs..... D-7
 Installing Switch Firmware D-8

Appendix E: Ethernet IP

EtherNet/IP Switch Management..... E-2
 Implicit (I/O) Messaging E-3
 Explicit Messaging E-6

Appendix F: Modbus TCP

MODBUS TCP Definition F-2
 Port Definition..... F-2
 Communication Process F-2
 Information Frame Definition F-3
 Function Code Definition F-4
 Switch MODBUS MAP F-5
 Register Information F-6
 Device Information..... F-6
 Information - Port 1 details F-7
 Port Status..... F-9



