

Basic ejector

SBP 10 S02 SDA

Part no.:10.02.01.00565

[Home](#) > [Vacuum Technology for Automation](#) > [Vacuum Components](#) > [Vacuum Generators](#) > [Basic Ejectors](#) > [Basic Ejectors SBP](#) > [SBP 10 S02 SDA](#)

Basic ejector for universal use



Nozzle diameter: 1 mm

Add. function: Axial silencer

Degree of evacuation: 85 %


Connection: Hose D6(1)-D8(2)

Pressure optimal: 4.5 bar

Suction rate (max.): 37.7 l/min

Air consumption suction: 48 l/min

Design Data



Attribute	Value
B	15 mm
d	4.20 mm
d1	6 mm
d2	8 mm
D	14 mm
H	34 mm
H1	40 mm
H2	5.20 mm
H3	14 mm
L	51.50 mm
L1	97 mm
L2	22 mm
L3	5.50 mm
L4	12.50 mm
X1	20 mm

Technical Data

Attribute	Value
Nozzle diameter	1 mm
Degree of evacuation	85 %
Suction rate (max.)	2.30 m³/h

Basic ejector

SBP 10 S02 SDA

Part no.:10.02.01.00565

Suction rate (max.)	37.70 l/min
Air consumption suction	2.90 m³/h
Air consumption suction	48 l/min
Sound level free	65 dB(A)
Sound level suction	59 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	4.50 bar
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	43.5 ... 87.0
Suction rate (max.)	1.33 cfm
Air consumption suction	1.70 cfm
Weight	22 g
Product family	SBP

Accessories



BEF-PL 110x44.5x3 SBP

Part no.:10.02.01.00511

Length L: 110 mm

Width B: 44.5 mm


Height H: 3 mm

Construction use: Basic ejector SBP

Basic ejector

SBP 10 S02 SDA

Part no.:10.02.01.00565



SET SBP M4-IG

Part no.:10.02.01.00769

Length L: 50 mm

Width B: 14 mm

Construction use: Basic ejector SBP

Type: M4-IG



VFI CN8/6 50

Part no.:10.07.01.00245

Connection: Hose 8/6 with Cap nut

Filter pore size: 50 µm



VFI 6/4 50

Part no.:10.07.01.00328

Connection: Hose 6/4

Filter pore size: 50 µm

Basic ejector

SBP 10 S02 SDA

Part no...:10.02.01.00565



VFT G1/8-IG 80

Part no...:10.07.01.00116

Connection: G1/8"-F

Shape: Short filter insert

Nominal flow rate: 2.7 m³/h

Filter pore size: 80 µm



SEG 10 HS

Part no...:10.02.01.00247

Nozzle diameter: 1 mm

Shape: For high vacuum

Suction rate (max.): 34 l/min

Air consumption suction: 49 l/min

Spare parts



SD G1/8-AG 14x40

Part no...:10.02.01.00540

Thread G1: G1/8"-M

External diameter D: 14 mm

Length L: 40 mm

Basic ejector

SBP 10 S02 SDA

Part no...:10.02.01.00565
