



EN 60947-5-1



Midi



© D

WERMA®

WERMA Signaltechnik GmbH + Co. KG
D-78604 Rietheim-Weilheim
Telefon +49 (0)7424 / 9557-0
Telefax +49 (0)7424 / 9557-44
info@werma.com
www.werma.com

DANGER

ⓓ Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.

ⓖⓑ Electrical connection is to be made by trained electrical specialists **only**.

ⓕ Le branchement doit **uniquement** être effectué par des professionnels.

Ⓛ Il collegamento deve essere eseguito **solo** da elettricisti specializzati.

ⓔ La conexión **sólo** debe ser realizada por electricistas debidamente formados.

ⓅⓉ A ligação deve ser feita **exclusivamente** por profissional elétrico especializado.

ⓃⓁ De aansluiting mag **enkel** gebeuren door erkende vakmensen.

ⒸⓏ Připojení smí **provádět** pouze kvalifikovaný personál.

ⓅⓁ Podłączenie **wyłącznie** przez specjalistów-elektryków.

ⓕⓁ Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.

ⓇⓊⓈ Подключение проводится только специа-листом-электриком.

ⓉⓇ Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.

ⒸⓃ 布线需由专业电工执行

161 / 461

DANGER

EVS

TwinFLASH

ⓓ Bei Epilepsie ungeeignet!

ⓖⓑ Unsuitable for epilepsy sufferers.

ⓕ Ne convient pas aux personnes souffrant d'épilepsie.

Ⓛ Inadatto per epilettici.

ⓔ Inadecuado para epilépticos.

ⓅⓉ Não aconselhave! a pessoas que sofram de Epilepsia.

ⓃⓁ Niet geschikt voor epileptici.

ⒸⓏ Nevhodné pro epileptiky.


ⓅⓁ Nie stosować przy zchorzeniu padaczk.

ⓕⓁ Ei sovellu epileptikoille.





ⓇⓊⓈ Не подходит для страдающих эпилепсией.


ⓉⓇ Epilepsi hastalığı olanların kullanmaması önerilir.

ⒸⓃ 不适用于癫痫病患者














TwinLIGHT	261 x10 70 261 x10 60	12V/24V≈ 115V/60Hz - 230V/50Hz	<185 mA < 30 mA < 65 mA
TwinFLASH	261 x20 70 261 x20 60	12V/24V≈ 115V/60Hz - 230V/50Hz	< 85 mA < 60 mA <110 mA
TriColour	261 430 70 261 430 60	12V/24V≈ 115V/60Hz - 230V/50Hz	<145 mA < 25 mA < 50 mA
LED Rotating	261 x40 70 261 x40 60	12V/24V≈ 115V/60Hz - 230V/50Hz	<130 mA < 65 mA <110 mA
TwinLIGHT	461 x10 70 461 x10 60	12V/24V≈ 115V/60Hz - 230V/50Hz	<345 mA <110 mA <170 mA
TwinFLASH	461 x20 70 461 x20 60	12V/24V≈ 115V/60Hz - 230V/50Hz	<100 mA <140 mA <215 mA
	161 700 70 161 700 60	12V/24V≈ 115V/60Hz - 230V/50Hz	<175 mA < 80 mA <105 mA





- 3**
- 3a - 261 700 01
 - 3b - 261 700 02
 - 3c - 261 700 06
 - 3d - 261 700 07
 - 3e - 261 700 03
 - 3f - 261 700 05




5

NOTICE

dB = dB A (SPL) 1m

Tone		[dB]	[dB]
0	110 Hz	107	99
1	3.3 kHz	106	101
2	1 Hz	110	101
3	20 Hz	110	101
4	1 Hz	95	94
5	7 Hz	99	92
6	1 Hz	101	93
7	1 Hz	100	92
8	0.5 Hz	110	101
9	700 Hz	97	92



150000000129_AB
310.261.002

WERMA