


TABLE A

PART NO	LENGTH
ZL-D0-CBL10	0.5m [1.6 ft]
ZL-D0-CBL10-1	1.0m [3.3 ft]
ZL-D0-CBL10-2	2.0m [6.6 ft]



NOTES:

- CABLE – 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT – 2A per conductor, 40A maximum cable current
- VOLTAGE –
240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE – 0–60°C (32–140°F)
- P1 CONNECTOR – 10 position terminal block for DL05/DL06 PLC Automation Direct Order # DO-ACC-4
- P2 CONNECTOR – 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025-2400
- MINIMUM BEND RADIUS – 65.6 mm [2.58 in]

PIN-OUT DIAGRAM



ZL-D0-CBL10-n	
Rev: original	Date: 07/2009
Units: mm [inches]	
Scale: .03970	
ZIPLINK DL05/DL06 Cable	