


TABLE A

PART NO	LENGTH
ZL-D0-CBL24	0.5m [1.6 ft]
ZL-D0-CBL24-1	1.0m [3.3 ft]
ZL-D0-CBL24-2	2.0m [6.6 ft]

PLC END

ZIPLINK END



PIN-OUT DIAGRAM

P1		P2	P1		P2
12	BLUE	2	24	ORANGE/BLACK	14
11	PINK	3	23	RED/BLACK	15
10	LIGHT BLUE	4	22	WHITE	16
9	LIGHT GREEN	5	21	GREEN/BLACK	17
8	GRAY	6	20	GRAY/BLACK	18
7	YELLOW	7	19	YELLOW/BLACK	19
6	PURPLE	8	18	PURPLE/WHITE	20
5	GREEN	9	17	GREEN/WHITE	21
4	ORANGE	10	16	ORANGE/WHITE	22
3	RED	11	15	RED/WHITE	23
2	BROWN	12	14	BROWN/WHITE	24
1	BLACK	1	13	BLACK/WHITE	13

NOTES:

- CABLE - 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT - 0.5A per conductor, 32A maximum cable current
- VOLTAGE -
240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE - 0-60°C (32-140°F)
- P1 and P2 CONNECTOR - 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025-2400
- MINIMUM BEND RADIUS - 80 mm [3.15 in]
- CONNECT P1 TO PLC, CONNECT P2 TO ZIPLINK MODULE

ZL-D0-CBL24-n	
Rev: A	Date: 09/2010
Units: mm [inches]	
Scale: .03940	
ZIPLINK DL05/DL06 Cable	