


TABLE A

PART NO	LENGTH
ZL-D05-CBL18	0.5m [1.6 ft]
ZL-D05-CBL18-1	1.0m [3.3 ft]
ZL-D05-CBL18-2	2.0m [6.6 ft]



PIN-OUT DIAGRAM

P1	P2	P1	P2
19	2	11	8
BROWN	14	GRAY	20
BROWN/WHITE	1	GRAY/BLACK	7
BLACK	13	YELLOW	19
BLACK/WHITE	3	YELLOW/BLACK	9
RED	4	LIGHT GREEN	10
ORANGE	5	LIGHT BLUE	11
GREEN	6	PINK	12
PURPLE	15	BLUE	21
RED/WHITE	16	GREEN/BLACK	22
ORANGE/WHITE	17	WHITE	23
GREEN/WHITE	18	RED/BLACK	24
PURPLE/WHITE		ORANGE/BLACK	

P1 1, 2, 12, 13 NOT CONNECTED

NOTES:

- CABLE - 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT - 2A per conductor, 32A maximum cable current
- VOLTAGE -
240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE - 0-60°C (32-140°F)
- P1 CONNECTOR - 22-pin terminal block for Direct Logic 05, AutomationDirect part # DO-ACC-1
- P2 CONNECTOR - 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025-2400
- MINIMUM BEND RADIUS - 65.6 mm [2.58 in]

ZL-D05-CBL18-n	
Rev: original	Date: 10/2009
Units: mm (inches)	
Scale: none	
ZIPLINK DL05 Cable	
