

Isolator Barriers

Switching repeater

Ex i field circuit

9270/21-17-14s Art. No. 261411



- Slim design – 12.5 mm wide – for one- and two-channel versions
- Can be used for functional safety levels up to SIL 2 (IEC/EN 61508)
- Offers line fault detection with signalization

WebCode 9270A



Series 9270 switching repeaters can be used for operating contacts, NAMUR proximity sensors or optocouplers. A relay output or electronic output transmits the signals to the control level. The intrinsically safe digital input is galvanically separated from the output and auxiliary power.

Technical Data

Explosion Protection

Application range (Zones)	2
Ex interface zone	0 1 2 20 21 22
IECEX gas certificate	IECEX IBE 17.0043 X
IECEX gas explosion protection	Ex nA nC [Ex ia Ga] IIC T4 Gc
IECEX dust certificate	IECEX IBE 17.0043 X
IECEX dust explosion protection	[Ex ia Da] IIIC
ATEX gas certificate	IBExU17ATEX1151 X
ATEX gas explosion protection	⊕ II 3 (1) G Ex nA nC [Ex ia Ga] IIC T4 Gc
ATEX dust certificate	IBExU17ATEX1151 X
ATEX dust explosion protection	⊕ II (1) D [Ex ia Da] IIIC
Certificate cULus	E81680
Marking cULus	Class I, Div. 2, Groups A,B,C,D; Class I, Zone 2, AEx/Ex nA nC Group IIC AIS Class I,II,III, Div. 1, Groups A,B,C,D,E,F,G; Class I, Zone 0, [AEx ia]/[Ex ia] IIC T4 any mounting pos. Ta = 60°C See Doc. 9270 6 031 001 3
Certificates	ATEX (IBE), Canada / USA (UL), IECEX (IBE), SIL (exida)
Ship approval	DNV GL

Safety Data

Max. voltage U_o/V_{oc}	9.6 V
Max. current I_o/I_{sc}	10 mA
Max. power P_o	25 mW

Isolator Barriers

Switching repeater

Ex i field circuit

9270/21-17-14s Art. No. 261411



Safety Data

Max. permissible external capacitance C_o/C_a for IIC	3.6 μ F
Max. permissible external capacitance C_o/C_a for IIB	26 μ F
Max. permissible external capacitance C_o for IIA	210 μ F
Max. permissible external inductance L_o/L_a for IIC	300 mH
Max. permissible external inductance L_o/L_a for IIB	1000 mH
Max. permissible external inductance L_o for IIA	1000 mH
Internal capacitance C_i	1.1 nF
Internal inductance L_i	Negligible
Safety-related maximum voltage	253 V AC

Functional Safety

SIL	2
-----	---

Electrical Data

Number of channels	2
LFD relay	via 9193/21-11-11

Auxiliary Power

Auxiliary power	24 V DC
Auxiliary power voltage range	19.2 ... 30 V
Nominal current	35 mA
Power consumption	1 W
Power dissipation max.	1 W
Polarity reversal protection	Yes
Undervoltage monitoring	No
Operation indication	Green "PWR" LED

Galvanic Isolation

Test voltage according to standard	IEC EN 60079-11
Galvanic isolation Ex i input to output	375 V AC peak value
Galvanic isolation Ex i input to auxiliary power	375 V AC peak value
Galvanic isolation Ex i input to fault message contact	375 V AC peak value
Test voltage according to standard	EN 61010 / EN 50178
Galvanic isolation output to auxiliary power	300 V_{eff}
Galvanic isolation output to output	300 V_{eff}
Fault message contact to auxiliary power	300 V_{eff}
Galvanic isolation fault message contact to output	300 V_{eff}

Input

Input signal	In accordance with EN 60947-5-6 (NAMUR)
Input current for ON	$\geq 2,1$ mA

Isolator Barriers

Switching repeater

Ex i field circuit

9270/21-17-14s Art. No. 261411



Input

Input current for OFF	≤ 1,2 mA
Input internal resistance Ri	1000 Ω
Input for open-circuit voltage Ua	8 V

Output

Output per channel	1 NO
Output	1 NO - relay
Output min. load	5 V / 10 mA
Output max. load DC	30 V / 2 A
Output max. load AC	250 V / 2 A
Output switching capacity	500 VA
Electrical service life note	resistive load
Output mechanical service life	1 x 10 ⁷ operating cycles
Output switching frequency	20 Hz
Switch user adjustment inverting	Activated / deactivated
Switching state indication	Yellow LED "OUT"
Switch user adjustment line fault	Activated / deactivated
Indication of line fault	"LF" LED, red
Error detection wire breakage	I _E < 0.05 ... 0.35 mA
Short circuit error detection	R _E < 100 ... 360 Ω

Ambient Conditions

Ambient temperature °C	-20 °C ... +60 °C
Ambient temperature °F	-4 °F ... +158 °F
Storage temperature °C	-40 °C ... +80 °C
Storage temperature °F	-40 °F ... +176 °F
Max. relative humidity	10 to 95%
Use at the height of	< 2000 m
Electromagnetic compatibility	EN 61326-1 Use in industrial environment Immunity according to EN 61000-6-2 Interference emission to EN 61000-6-4

Mechanical Data

Degree of protection (IP)	IP30
Terminal degree of protection (IP)	IP20
Fire resistance (UL 94)	V0
Enclosure material	Polyamide
Grid dimension	12.5 mm
Width	12.5 mm
Width inches	0.49 in
Height	114.5 mm
Height inches	4.51 in
Length	112.5 mm
Length inches	4.43 in
Weight	0.17 kg
Weight	0.37 lb

Mounting / Installation

Mounting type	NS35/15, NS35/7.5 DIN rail
---------------	----------------------------

Isolator Barriers

Switching repeater

Ex i field circuit


9270/21-17-14s Art. No. 261411



Mounting / Installation


Mounting position	Any
Connection type	Screw terminal
Conductor cross-section rigid min.	0.2 mm ²
Conductor cross-section solid max.	2.5 mm ²
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section flexible max.	2.5 mm ²
Connection cross-section AWG	24 – 13

Technical Drawings – Subject to Alterations



Connection diagram 9270/21-17-14


Dimensional Drawings (All Dimensions in mm [inches]) – Subject to Alterations



I Spac Series 9260, 9265, 9270, 9275, 9276, 9282 with screw terminal

Accessories

Resistance coupling element



Connection of additional contacts in the Ex area as well, in order to enable short circuit and open circuit detection.

Art. No.

105944

We reserve the right to make alterations to the technical data, dimensions, weights, designs and products available without notice. The illustrations cannot be considered binding.