


TABLE A

PART NO	LENGTH
ZL-D0-CBL24-L	0.5m [1.6 ft]
ZL-D0-CBL24-1L	1.0m [3.3 ft]
ZL-D0-CBL24-2L	2.0m [6.6 ft]



PIN-OUT DIAGRAM

P1	P2	P1	P2
12	BLUE	1	ORANGE/BLACK
11	PINK	3	RED/BLACK
10	LIGHT BLUE	4	WHITE
9	LIGHT GREEN	2	GREEN/BLACK
8	GRAY	15	GRAY/BLACK
7	YELLOW	16	YELLOW/BLACK
6	PURPLE	7	PURPLE/WHITE
5	GREEN	9	GREEN/WHITE
4	ORANGE	10	ORANGE/WHITE
3	RED	8	RED/WHITE
2	BROWN	21	BROWN/WHITE
1	BLACK	22	BLACK/WHITE

NOTES:

- CABLE – 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT – 0.5A per conductor, 32A maximum cable current
- VOLTAGE – 240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE – 0–60°C (32–140°F)
- P1 and P2 CONNECTOR – 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025–2400
- MINIMUM BEND RADIUS – 80 mm [3.15 in]
- CONNECT P1 TO PLC, CONNECT P2 TO ZIPLINK MODULE

ZL-D0-CBL24-nL	
Rev: A	Date: 09/2010
Units: mm [inches]	
Scale: .03940	
ZIPLINK DL05/DL06 Cable	