


TABLE A

PART NO	LENGTH
ZL-D05-CBL22-P	0.5m [1.6 ft]
ZL-D05-CBL22-1P	1.0m [3.3 ft]
ZL-D05-CBL22-2P	2.0m [6.6 ft]



PIN-OUT DIAGRAM

P1	P2	P1	P2
12	BLACK RED/BLACK	4	GRAY
13	WHITE PINK	14	GRAY/BLACK
1	GREEN LIGHT GREEN	5	YELLOW
3	ORANGE	15	YELLOW/BLACK
16	PURPLE	17	RED
19	RED/WHITE	6	LIGHT BLUE
8	ORANGE/WHITE	18	BLACK/WHITE
20	GREEN/WHITE	7	BLUE
9	PURPLE/WHITE	11	GREEN/BLACK
		21	BROWN
		10	BROWN/WHITE
		22	ORANGE/BLACK

P1-2 NOT CONNECTED

NOTES:

- CABLE - 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT - 2A per conductor, 40A maximum cable current
- VOLTAGE -  
240V AC/DC rated operating voltage  
265V AC/DC maximum voltage
- OPERATING TEMPERATURE - 0-60°C (32-140°F)
- P1 CONNECTOR - 22-pin terminal block for Direct Logic 05, AutomationDirect part # D0-ACC-1
- P2 CONNECTION - 24 tinned pig-tail leads (only 20 leads are connected to P1, per cable pin-out diagram)
- MINIMUM BEND RADIUS - 65.6 mm [2.58 in]

ZL-D05-CBL22-nP	
Rev: original	Date: 10/2009
Units: mm [inches]	
Scale: none	
ZIPLINK DL05 Cable	