

DATA SHEET



Single Phase Induction Motor - Squirrel Cage

Customer : Automation Direct																			
Product line : Single-Phase	Product code : 14798864 Catalog # : 00158ES1B56C-S																		
Frame : 56HC Output : 1.5 HP (1.1 kW) Poles : 4 Frequency : 60 Hz Rated voltage : 115/208-230 V Rated current : 15.0/8.27-7.48 A L. R. Amperes : 120/66.2-59.8 A LRC : 8.0x(Code L) No load current : 7.80/3.36-3.90 A Rated speed : 1745 rpm Slip : 3.06 % Rated torque : 4.51 ft.lb Locked rotor torque : 250 % Breakdown torque : 270 % Insulation class : F Service factor : 1.15 Moment of inertia (J) : 0.1426 sq.ft.lb Design : L	Locked rotor time : 14s (cold) 8s (hot) Temperature rise : 80 K Duty cycle : Cont.(S1) Ambient temperature : -20°C to +40°C Altitude : 1000 m.a.s.l. Protection degree : IP55 Cooling method : IC411 - TEFC Mounting : F-1 Rotation ¹ : Both (CW and CCW) Noise level ² : 54.0 dB(A) Starting method : Direct On Line Approx. weight ³ : 48.2 lb																		
<table border="1"> <tr> <td>Output</td> <td>25%</td> <td>50%</td> <td>75%</td> <td>100%</td> </tr> <tr> <td>Efficiency (%)</td> <td>67.0</td> <td>69.0</td> <td>75.0</td> <td>77.0</td> </tr> <tr> <td>Power Factor</td> <td>0.42</td> <td>0.68</td> <td>0.78</td> <td>0.83</td> </tr> </table>	Output	25%	50%	75%	100%	Efficiency (%)	67.0	69.0	75.0	77.0	Power Factor	0.42	0.68	0.78	0.83	Foundation loads Max. traction : 95 lb Max. compression : 144 lb			
Output	25%	50%	75%	100%															
Efficiency (%)	67.0	69.0	75.0	77.0															
Power Factor	0.42	0.68	0.78	0.83															
<table border="1"> <tr> <td></td> <td><u>Drive end</u></td> <td><u>Non drive end</u></td> </tr> <tr> <td>Bearing type :</td> <td>6204 ZZ</td> <td>6202 ZZ</td> </tr> <tr> <td>Sealing :</td> <td>V'Ring</td> <td>Without Bearing Seal</td> </tr> <tr> <td>Lubrication interval :</td> <td>-</td> <td>-</td> </tr> <tr> <td>Lubricant amount :</td> <td>-</td> <td>-</td> </tr> <tr> <td>Lubricant type :</td> <td colspan="2">Mobil Polyrex EM</td> </tr> </table>			<u>Drive end</u>	<u>Non drive end</u>	Bearing type :	6204 ZZ	6202 ZZ	Sealing :	V'Ring	Without Bearing Seal	Lubrication interval :	-	-	Lubricant amount :	-	-	Lubricant type :	Mobil Polyrex EM	
	<u>Drive end</u>	<u>Non drive end</u>																	
Bearing type :	6204 ZZ	6202 ZZ																	
Sealing :	V'Ring	Without Bearing Seal																	
Lubrication interval :	-	-																	
Lubricant amount :	-	-																	
Lubricant type :	Mobil Polyrex EM																		
Notes																			
This revision replaces and cancel the previous one, which must be eliminated. (1) Looking the motor from the shaft end. (2) Measured at 1m and with tolerance of +3dB(A). (3) Approximate weight subject to changes after manufacturing process. (4) At 100% of full load.																			
These are average values based on tests with sinusoidal power supply, subject to the tolerances stipulated in NEMA MG-1.																			
Rev.	Changes Summary	Performed	Checked	Date															
Performed by																			
Checked by			Page	Revision															
Date	22/08/2022		1 / 2																

LOAD PERFORMANCE CURVE

Single Phase Induction Motor - Squirrel Cage



Customer : Automation Direct


Product line : Single-Phase

Product code :

14798864

Catalog # :

00158ES1B56C-S




Performance : 115/208-230 V 60 Hz 4P

Rated current : 15.0/8.27-7.48 A
 LRC : 8.0
 Rated torque : 4.51 ft.lb
 Locked rotor torque : 250 %
 Breakdown torque : 270 %
 Rated speed : 1745 rpm

Moment of inertia (J) : 0.1426 sq.ft.lb
 Duty cycle : Cont.(S1)
 Insulation class : F
 Service factor :
 Temperature rise : 80 K
 Design : L

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page 2 / 2	Revision
Checked by				
Date	22/08/2022			



Fan cover - steel plate										
Color Munsell N 1 matte black										
Painting plan 207N										
Mounting F-1/B34R(D)										
ECM	LOC	SUMMARY OF MODIFICATIONS				EXECUTED	CHECKED	RELEASED	DATE	VER
EXECUTED	HYBRISUSER	SINGLE PH. MOTOR ROLLED STEEL				PREVIEW		WEG		
CHECKED		FRAME 56HC IP55 TEFC				WDD		SHEET 1 / 1		
RELEASED		REL DT.				WMO Jaragua do Sul		Product Engineering		

1.5 HP 04 Poles 60 Hz



MADE IN MEXICO

MAT: 14798864

W01.ME01C0X0X



MODEL 00158ES1B56C-S

PH 1	Hz 60	HP 1.5
FR 56HC		KW 1.1
DUTY CONT.		V 115/208-230
ALT 1000 m.a.s.l		A 15.0/8.27-7.48
INS CL F ΔT 80K	IP55	SFA -
AMB 40°C	DES L	SF 1.15
ENCL TEFC	CODE L	PF 0.83
USABLE @ 208V SF1.00		RPM 1745
		NEMA NOM. EFF 77.0%

Electric Motor

DE 8204-ZZ	ODE 8202-ZZ	MOBIL POLYREX EM	
------------	-------------	------------------	--

REVERSE ROTATION INVERT T5 BY T8



T1-BLU
T2-WHT
T3-ORG
T4-YEL
T5-BLK
T8-RED



WARNING: Motor must be grounded in accordance with local and national electrical codes to prevent serious electrical shocks. Disconnect power source before servicing unit.



AVERTISSEMENT: Le moteur doit être mis à la terre conformément aux codes électriques locaux et nationaux afin d'éviter tout choc électrique grave. Déconnectez l'alimentation avant l'entretien de la machine.