

5361




Straight Blade Single Flush Receptacle.

Product Specifications

| | |
|----------------------------|---|
| Product Type | Receptacle. |
| Device Type | Single Flush. |
| Device Grade | Industrial. |
| Amperage | 20A |
| Voltage | 125V |
| Poles and Wires | 2 Pole, 3 Wire. |
| Wiring Style | Back & Side. |
| Color | Brown |
| NEMA # | 5-20R |
| Face | Nylon. |
| Base | Nylon. |
| Line Contacts | High Performance Brass. |
| Clamp Nut | Steel. |
| Mounting Yoke | Steel, Nickel and Brass Plated .050" (1.3). |
| Terminal Screws | Combination Brass #10-32. |
| Grounding Screw. | Combination Brass (Green) #8-32. |
| Grounding Clamp Nut | Brass. |

| | |
|--------------------------------|--|
| Circuit ID | Hot Stamp. |
| Auto Ground Clip | High Performance Brass. |
| Mounting Screws | Combination Steel Zinc-Plated. |
| Dielectric Voltage | Withstands 2000V per UL498. |
| Maximum Working Voltage | 250V AC or DC |
| Current Interrupting | Certified for current interrupting at full rated current. |
| Temperature Rise | Less than 30 deg C temperature rise at full rated current after 50 cycles overload at 150% rated current for either AC or DC applications per UL498. |
| Terminal Identification | Brass-Hot; Green-Grounding; Silver-Neutral. |
| Terminal Accommodation | #14-#10 AWG Copper Conductor Only. |
| Product Identification | Ratings are a permanent part of the device. |
| Flammability | UL 94 V2. |
| Operating Temperature | Maximum Continuous 60 deg C, Minimum -40 deg C (w/o impact). |
| UL Standard | UL Listed, File #E2258- Guide #RTRT. |
| CSA Standard | Certified to CSA Standard C22.2 No. 42M1984 (General Use Receptacles). |
| UL Listing | UL Listed, File #E2258- Guide #RTRT. |
| Federal Specification | Federal Specification WC596 (where applicable). |
| Complies with: | NEMA Standards WD-1, WD-6. |
| Overseas Approval | NOM, CE. |
| Catalog Page | Click here for catalog page |
| | |



BRYANT®