

## 71630FR




Locking Receptacle.

## Product Specifications

<b>Product Style</b>	Standard Locking.
<b>Amperage</b>	30A
<b>Device Type</b>	Flush Receptacle.
<b>Poles and Wires</b>	3 Pole, 4 Wire.
<b>Voltage</b>	3ph 480V AC
<b>Product Variation</b>	Standard.
<b>Color</b>	Black.
<b>Configuration Type</b>	L16-30
<b>Base</b>	Reinforced Thermoplastic Polyester.
<b>Face</b>	Nylon.
<b>Terminals</b>	0.40" (1.0) Copper Alloy.
<b>Terminal Clamp</b>	0.40" (1.0) Copper Alloy.
<b>Ground Contact</b>	0.40" (1.0) Copper Alloy.
<b>Ground Shunt</b>	.015" (.3) Copper Alloy.
<b>Mounting Strap</b>	.050" (1.3) Steel (Nickel-Plated).
<b>Back Plate</b>	.040" (1.0) Plated Copper Alloy.
<b>Terminal Screws</b>	#10 Bronze.
<b>Self Ground Clip</b>	Stainless Steel.
<b>Mounting Screws</b>	Plated Steel.
<b>Dielectric Voltage</b>	Withstands 3500V per UL498.

<b>Max Working Voltage</b>	600V AC or 250V DC.
<b>Current Interrupting</b>	Certified for current interrupting at full rated current.
<b>Temperature Rise</b>	Maximum 30 deg C temperature rise at full rated current after 50 cycles of overload at 150% rated current for either AC or DC applications per UL498
<b>Terminal Identification</b>	(X, Y Z Brass Hot) (G, Green, Grounding) (W, Silver, Neutral).
<b>Terminal Accommodation</b>	#14-#8 AWG solid or stranded copper wire.
<b>Product Identification</b>	Ratings and NEMA identification are permanently marked on device.
<b>Flammability</b>	UL 94 V2 Minimum.
<b>Operating Temperatures</b>	-40 deg C to 85 deg C (continuous w/o impact).
<b>UL Standard</b>	UL Listed to Standard 498 (Attachment Plug and Receptacles).
<b>CSA Standard</b>	Certified to CSA Standard C22.2 No.42M1984 (General Use Receptacles) and C22.2 No. 182.2M1987 (Industrial Locking Type, Special Use Attachment Plugs, Receptacles and Connectors) where applicable.
<b>UL Listing File</b>	UI Listed File #E2258- Guide #RTRT
<b>CSA Certification File</b>	CSA Certified File #LR16215- Guide #365-E-1.
<b>Fed Spec</b>	Federal Specifications WC596 (where applicable).
<b>Complies with:</b>	Complies with NEMA Standards WD-1, WD-6 and UL 498.
<b>Overseas Apporvals</b>	NOM, CE.
<b>Catalog Page</b>	<a href="#">Click here for catalog page</a>



**BRYANT®**