

# BR Y5262




Straight Blade Duplex Receptacle.

## Product Specifications

<b>Product Type</b>	Receptacle
<b>Device Type</b>	Duplex.
<b>Device Grade</b>	Industrial.
<b>Amperage</b>	15A
<b>Voltage</b>	125V
<b>Poles and Wires</b>	2 Pole, 3 Wire.
<b>Wiring Style</b>	Back & Side.
<b>Color</b>	Brown
<b>NEMA #</b>	5-15R
<b>Face</b>	Nylon.
<b>Base</b>	Nylon.
<b>Line Contacts</b>	High Performance Brass.
<b>Clamp Nut</b>	Steel.
<b>Mounting Yoke</b>	Steel, Nickel and Brass Plated .050" (1.3).
<b>Terminal Screws</b>	Combination Brass #10-32.
<b>Grounding Screw.</b>	Combination Brass (Green) #8-32.

<b>Grounding Clamp Nut</b>	Brass.
<b>Circuit ID</b>	Hot Stamp.
<b>Auto Ground Clip</b>	High Performance Brass.
<b>Mounting Screws</b>	Combination Steel Zinc-Plated.
<b>Dielectric Voltage</b>	Withstands 2000V per UL498.
<b>Maximum Working Voltage</b>	250V AC or DC
<b>Current Interrupting</b>	Certified for current interrupting at full rated current.
<b>Temperature Rise</b>	Less than 30 deg C temperature rise at full rated current after 50 cycles overload at 150% rated current for either AC or DC applications per UL498.
<b>Terminal Identification</b>	Brass-Hot; Green-Grounding; Silver-Neutral.
<b>Terminal Accommodation</b>	#14-#10 AWG Copper Conductor Only.
<b>Product Identification</b>	Ratings are a permanent part of the device.
<b>Flammability</b>	UL 94 V2.
<b>Operating Temperature</b>	Maximum Continuous 60 deg C, Minimum -40 deg C (w/o impact).
<b>CSA Standard</b>	Certified to CSA Standard C22.2 No. 42M1984 (General Use Receptacles).
<b>UL Listing</b>	UL Listed, File #E2258- Guide #RTRT.
<b>Federal Specification</b>	Federal Specification WC596 (where applicable).
<b>Complies with:</b>	NEMA Standards WD-1, WD-6.
<b>Overseas Approval</b>	NOM, CE.
<b>Catalog Page</b>	<a href="#">Click here for catalog page</a>



**BRYANT®**