



TABLE A

PART NO	LENGTH
ZL-CO-CBL11	0.5m [1.6 ft]
ZL-CO-CBL11-1	1.0m [3.3 ft]
ZL-CO-CBL11-2	2.0m [6.6 ft]

PIN-OUT DIAGRAM

P1	P2	P1	P2
1 — BLACK	1	7 — ORANGE/WHITE	16
1 — RED	3	7 — GREEN/WHITE	17
2 — ORANGE	4	8 — VIOLET/WHITE	18
2 — GREEN	5	8 — GRAY/BLACK	20
3 — VIOLET	6	9 — GREEN/BLACK	21
3 — YELLOW	7	9 — WHITE	22
4 — LIGHTGREEN	9	10 — RED/BLACK	23
4 — LIGHTBLUE	10	11 — ORANGE/BLACK	24
5 — PINK	11	N.C. BROWN	2
5 — BLUE	12	N.C. GRAY	8
6 — BROWN/WHITE	14	N.C. BLACK/WHITE	13
6 — RED/WHITE	15	N.C. YELLOW/BLACK	19

NOTES:

- CABLE — 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT — 2A per conductor, 40A maximum cable current
- VOLTAGE — 240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE — 0–60°C (32–140°F)
- P1 CONNECTOR — 11 position terminal block for Click PLC AutomationDirect part # C0–8TB
- P2 CONNECTOR — 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025–2400
- MINIMUM BEND RADIUS — 65.6 mm [2.58 in]

ZL-CO-CBL11-n	
Rev: original	Date: 07/2009
Units: mm [inches]	
Scale: .03937	
ZIPLINK Click PLC Cable	