


TABLE A

PART NO	LENGTH
ZL-D2-CBL19	0.5m [1.6 ft]
ZL-D2-CBL19-1	1.0m [3.3 ft]
ZL-D2-CBL19-2	2.0m [6.6 ft]



PIN-OUT DIAGRAM

P1	P2	P1	P2
11 — BROWN	2	16 — GRAY	8
11 — BROWN/WHITE	14	16 — GRAY/BLACK	20
2 — RED	3	7 — LIGHT GREEN	9
12 — RED/WHITE	15	7 — GREEN/BLACK	21
3 — ORANGE	4	8 — LIGHT BLUE	10
13 — ORANGE/WHITE	16	18 — WHITE	22
4 — GREEN	5	9 — PINK	11
14 — GREEN/WHITE	17	19 — RED BLACK	23
5 — PURPLE	6	10 — BLUE	12
15 — PURPLE/WHITE	18	20 — ORANGE/BLACK	24
6 — BLACK	1	CUT AND INSULATE	YELLOW
6 — BLACK	13	CUT AND INSULATE	YELLOW/BLACK
			19

NOTES:

- CABLE — 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT — 2A per conductor, 32A maximum cable current
- VOLTAGE — 240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE — 0–60°C (32–140°F)
- P1 CONNECTOR — 19 position terminal block, Automation Direct Part # D2-16IOCON
- P2 CONNECTOR — 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025-2400
- MINIMUM BEND RADIUS — 65.6 mm [2.58 in]

ZL-D2-CBL19-n	
Rev: A	Date: 07/2009
Units: mm [inches]	
Scale: .03940	
ZIPLINK DL205 PLC CABLE	