



- P.C.B. or plug-in mount
- AC, DC, sensitive DC or single bistable coil versions available
- 8 mm, 6 kV (1.2/50 μs) between coil and contacts
- Ambient temperature +85°C
- Sockets and accessories: see 95, 99 and 86 series



* for 400 V applications, requirements for pollution degree 2 are met.

	40.31	40.51	40.52
	<ul style="list-style-type: none"> - 1 pole, 10 A - 3.5 mm pinning - PCB / for use with 95 series sockets 	<ul style="list-style-type: none"> - 1 pole, 10 A - 5 mm pinning - PCB / for use with 95 series sockets 	<ul style="list-style-type: none"> - 2 pole, 8 A - 5 mm pinning - PCB / for use with 95 series sockets
Contact specifications			
Contact configuration	SPDT	SPDT	DPDT
Rated current/Maximum peak current A	10/20	10/20	8/15
Rated voltage/Maximum switching voltage V AC	250/400*	250/400*	250/250
Rated load in AC1 VA	2,500	2,500	2,000
Inductive rating @ p.f. 0.4 A	7	7	5.5
Single phase motor rating (@ 120/250 VAC) HP	0.3/0.6	0.3/0.6	0.2/0.4
Breaking capacity in DC1: 30/110/220V A	10/0.3/0.12	10/0.3/0.12	8/0.3/0.12
Minimum switching load mW (V/mA)	300 (5/5)	300 (5/5)	300 (5/5)
Standard contact material	AgNi (Silver Nickel)	AgNi (Silver Nickel)	AgNi (Silver Nickel)
Coil specifications			
Nominal voltage (U _N) V AC (50/60 Hz)	6 · 12 · 24 · 48 · 60 · 110 · 120 · 230 · 240		
V DC	5 · 6 · 7 · 9 · 12 · 14 · 18 · 21 · 24 · 28 · 36 · 48 · 60 · 90 · 110		
Power consumption AC/DC/sens. DC VA (50 Hz)/W	1.2/0.65/0.5	1.2/0.65/0.5	1.2/0.65/0.5
Operating range AC (50 Hz)	(0.8...1.1)U _N		
DC/sens. DC	(0.73...1.5)U _N /(0.73...1.75)U _N		
Holding voltage AC/DC	0.8 U _N /0.4 U _N		
Must drop-out voltage AC/DC	0.2 U _N /0.1 U _N		
Technical data			
Mechanical life AC/DC cycles	10,000,000/20,000,000	10,000,000/20,000,000	10,000,000/20,000,000
Electrical life at rated load AC1 cycles	200,000	200,000	100,000
Operate/release time (bounce included) ms	10/10 · (15/12 sens.)		
Insulation according to EN 61810-5	3.6 kV/3		
Insulation between coil and contacts (1.2/50μs) kV	6 (8mm)		
Dielectric strength between open contacts V AC	1,000		
Ambient temperature range °C	-40...+85		
Protection category	IP 50		
Approvals: (according to type)			

- P.C.B. or plug-in mount
- AC, DC, sensitive DC or single bistable coil versions available
- 8 mm, 6 kV (1.2/50 μs) between coil and contacts
- Ambient temperature +85°C
- Sockets and accessories: see 95, 99 and 86 series





* for 400 V applications, requirements for pollution degree 2 are met.

40.61



- 1 pole, 16 A
- 5 mm pinning
- PCB / for use with 95 series sockets



40.xx.6



- Bistable version (1 coil)
- PCB / for use with 95 series sockets

Bistable version (1 coil) types:

- 40.31.6...
- 40.51.6...
- 40.52.6...
- 40.61.6...


For wiring diagrams see page 16

Contact specifications			
Contact configuration		SPDT	
Rated current/Maximum peak current	A	16/30	
Rated voltage/Maximum switching voltage	V AC	250/400*	
Rated load in AC1	VA	4,000	
Inductive rating @ p.f. 0.4	A	11	
Single phase motor rating (@ 120/250 VAC)	HP	0.4/0.8	
Breaking capacity in DC1: 30/110/220V	A	16/0.3/0.12	
Minimum switching load	mW (V/mA)	500 (10/5)	
Standard contact material		AgCdO (Silver Cadmium Oxide)	
Coil specifications			
Nominal voltage (U _N)	V AC (50/60 Hz)	6 · 12 · 24 · 48 · 60 · 110 · 120 · 230 · 240	5 · 6 · 12 · 24 · 48 · 110
	V DC	**See below	5 · 6 · 12 · 24 · 48 · 110
Power consumption AC/DC/sens. DC	VA (50 Hz)/W	1.2/0.65/0.5	1.0/1.0/—
Operating range	AC (50 Hz)	(0.8...1.1)U _N	(0.8...1.1)U _N
	DC/sens. DC	(0.73...1.5)U _N /(0.8...1.5)U _N	(0.8...1.1)U _N /—
Holding voltage	AC/DC	0.8 U _N /0.4 U _N	—
Must drop-out voltage	AC/DC	0.2 U _N /0.1 U _N	—
Technical data			
Mechanical life AC/DC	cycles	10,000,000/20,000,000	See relays
Electrical life at rated load AC1	cycles	100,000	40.31
Operate/release time (bounce included)	ms	10/10 · (15/12 sens.)	40.51
Insulation according to EN 61810-5		3.6 kV/3	40.52
Insulation between coil and contacts (1.2/50μs)	kV	6 (8mm)	40.61
Dielectric strength between open contacts	V AC	1,000	
Ambient temperature range	°C	-40...+85	Min. impulse duration ≥ 20 ms
Protection category		IP 50	
Approvals: (according to type)			

** Nominal voltage (U_N):
 5 · 6 · 7 · 9 · 12 · 14 · 18 · 21 ·
 24 · 28 · 36 · 48 · 60 · 90 ·
 110 V DC

ORDERING INFORMATION

Example: a 40 series P.C.B. relay with DPDT contacts, with coil rated at 230 V AC.



Series

Type

- 3 = P.C.B. - 3.5 mm pinning
- 5 = P.C.B. - 5 mm pinning
- 6 = P.C.B. - 5 mm pinning

No. of poles

- 1 = SPDT
for: 40.31, 10 A
40.51, 10 A
40.61, 16 A
- 2 = DPDT
for 40.52, 8 A

Coil version

- 6 = AC/DC bistable
- 7 = Sensitive DC
- 8 = AC (50/60 Hz)
- 9 = DC

Coil voltage

see coil specifications

A: Contact material

- 0 = Standard AgNi
for: 40.31/51/52
AgCdO for 40.61
- 2 = AgCdO
- 4 = AgSnO₂
- 5 = AgNi + Au (5µm)

B: Contact circuit

- 0 = Standard
- 3 = Contact NO

D: Special applications

- 0 = Standard
- 1 = Sealed version (IP67)
- 3 = High temperature (+125°C) sealed version

C: Options

- 0 = Standard

Only combinations in the same row are possible

Preferred versions

	coil version	A	B	C	D
40.31/51	AC/DC/sens.DC	0	0	0	0
40.52	AC/DC/sens.DC	0	0	0	0
40.61	AC/DC/sens.DC	0	0	0	0

All versions

	coil version	A	B	C	D
40.31/51	AC/sens.DC	0 - 2 - 4 - 5	0 - 3	0	0 - 1
40.31/51	DC	0 - 2 - 4 - 5	0 - 3	0	0 - 1 - 3
40.52	AC/sens.DC	0 - 2 - 5	0 - 3	0	0 - 1
40.52	DC	0 - 2 - 5	0 - 3	0	0 - 1 - 3
40.61	AC/sens.DC	0 - 4	0 - 3	0	0 - 1
40.61	DC	0 - 4	0 - 3	0	0 - 1 - 3
40.31/51/52/61	bistable	0	0	0	0

TECHNICAL DATA

INSULATION

INSULATION according to EN 61810-5	insulation rated voltage	V	250	
	rated impulse withstand voltage	kV	3.6	
	pollution degree		3 (SPDT)	2 (DPDT)
	overvoltage category		III	

IMMUNITY


CONDUCTED DISTURBANCE IMMUNITY	BURST (according to EN 61000-4-4) level 4 (4kV)
	SURGE (according to EN 61000-4-5) level 3 (2kV)

OTHER DATA

VIBRATION RESISTANCE (10...55Hz): NO/NC	g/g	10/4 (SPDT)	3/3 (DPDT)
POWER LOST IN THE ENVIRONMENT	without contact current	W	
	with rated current	W	0.6
		1.2 (40.31/51)	2 (40.61/52)
RECOMMENDED DISTANCE between RELAY mounted on P.C.B.s	mm	≥5	

CONTACT SPECIFICATIONS


F 40



Electrical life vs AC1 load.

- 1** - Type 40.52 (8 A)
- 2** - Type 40.31 - 40.51 (10 A)
Type 40.61 (16 A)

H 40



Breaking capacity for DC1 load.

- 1** - Type 40.61
- 2** - Type 40.31 - 40.51
- 3** - Type 40.52
- A** - Load applied to 1 contact
- B** - Load applied to 2 contacts in series

- When switching a resistive load (DC1) having voltage and current values under the curve the expected electrical life is $\geq 100 \cdot 10^3$ cycles.
 - In case of DC13 loads the connection of a diode in parallel with the load will permit the same electrical life as for a DC1 load.
- Note:** the release time of load will be increase.

COIL SPECIFICATIONS

DC VERSION DATA (0.65 W standard)

Nominal voltage U_N V	Coil code	Operating range		Resistance R Ω	Rated coil absorption I at U_N mA
		U_{min} V	U_{max} V		
5	9.005	3.65	7.5	38	130
6	9.006	4.4	9	55	109
7	9.007	5.1	10.5	75	94
9	9.009	6.6	13.5	125	72
12	9.012	8.8	18	220	55
14	9.014	10.2	21	300	47
18	9.018	13.1	27	500	36
21	9.021	15.3	31.5	700	30
24	9.024	17.5	36	900	27
28	9.028	20.5	42	1,200	23
36	9.036	26.3	54	2,000	18
48	9.048	35	72	3,500	14
60	9.060	43.8	90	5,500	11
90	9.090	65.7	135	12,500	7.2
110	9.110	80.3	165	18,000	6.2

DC VERSION DATA (0.5 W sensitive)

Nominal voltage U_N V	Coil code	Operating range		Resistance R Ω	Rated coil absorption I at U_N mA
		U_{min}^* V	U_{max}^{**} V		
5	7.005	3.7	8.8	50	100
6	7.006	4.4	10.5	75	80
7	7.007	5.1	12.2	100	70
9	7.009	6.6	15.8	160	56
12	7.012	8.8	21	300	40
14	7.014	10.2	24.5	400	35
18	7.018	13.2	31.5	650	27.7
21	7.021	15.4	36.9	900	23.4
24	7.024	17.5	42	1,200	20
28	7.028	20.5	49	1,600	17.5
36	7.036	26.3	63	2,600	13.8
48	7.048	35	84	4,800	10
60	7.060	43.8	105	7,200	8.4
90	7.090	65.7	157	16,200	5.6
110	7.110	80.3	192	23,500	4.7


* $U_{min} = 0.8 U_N$ for 40.61 ** $U_{max} = 1.5 U_N$ for 40.61

AC VERSION DATA


Nominal voltage U_N V	Coil code	Operating range		Resistance R Ω	Rated coil absorption I at U_N (50Hz) mA
		U_{min} V	U_{max} V		
6	8.006	4.8	6.6	21	168
12	8.012	9.6	13.2	80	90
24	8.024	19.2	26.4	320	45
48	8.048	38.4	52.8	1,350	21
60	8.060	48	66	2,100	16.8
110	8.110	88	121	6,900	9.4
120	8.120	96	132	9,000	8.4
230	8.230	184	253	28,000	5
240	8.240	192	264	31,500	4.1

COIL SPECIFICATIONS


R 40 DC



R 40 sens. DC



R 40 AC



Operating range vs ambient temperature.

- 1 - Max coil voltage permitted
- 2 - Min pick-up voltage with coil at ambient temperature

BISTABLE COIL SPECIFICATIONS


AC/DC VERSION DATA (bistable)

Nominal voltage U_N V	Coil	Operating range		Resistance R Ω	Rated coil absorption I at U_N mA	DC: Release resistance** R_{DC} Ω
		U_{min} V	U_{max} V			
5	6.005	4	5.5	23	215	37
6	6.006	4.8	6.6	33	165	62
12	6.012	9.6	13.2	130	83	220
24	6.024	19.2	26.4	520	40	910
48	6.048	38.4	52.8	2,100	21	3,600
110	6.110	88	121	11,000	10	16,500


** R_{DC} = Resistance in DC, $R_{AC} = 1.3 \times R_{DC}$

Wiring Diagram for 40 Series bistable coil version

AC Operation



DC Operation



On momentary closure of the SET switch the relay is magnetised through the diode and the relay contacts transfer to the set position and remain in this position. On momentary closure of the RESET switch the relay is demagnetised through current limiting resistor (RAC) and the contacts return to the reset position.

On momentary closure of the SET switch the relay is magnetised and the relay contacts transfer to the set position and remain in this position. On momentary closure of the RESET switch the relay is demagnetised through limiting resistor (RDC) and the contacts return to the reset position.

Notes: The minimum SET or RESET impulse time is 20 ms. The maximum time can be continuous. In practice, always ensure that the SET and RESET contacts cannot be operated simultaneously.