


TABLE A

| PART NO | LENGTH |
|-----------------|---------------|
| ZL-D06-CBL24-1P | 1.0m [3.3 ft] |
| ZL-D06-CBL24-2P | 2.0m [6.6 ft] |




PIN-OUT DIAGRAM

| P1 | P2 | P1 | P2 |
|----|--------------|-----|--------------|
| 14 | BROWN | 20 | GREEN/BLACK |
| 1 | BROWN/WHITE | 7 | LIGHTGREEN |
| 15 | RED | 21 | WHITE |
| 2 | RED/WHITE | 8 | LIGHTBLUE |
| 16 | ORANGE | 22 | RED/BLACK |
| 3 | ORANGE/WHITE | 9 | PINK |
| 17 | GREEN | 23 | ORANGE/BLACK |
| 4 | GREEN/WHITE | 10 | BLUE |
| 18 | PURPLE | 24 | BLACK |
| 5 | PURPLE/WHITE | 11 | BLACK/WHITE |
| 19 | GRAY | 25 | YELLOW |
| 6 | GREY/BLACK | 26 | YELLOW/BLACK |
| | | n/c | |

12, 13, 26, and 27 NOT CONNECTED

NOTES:

- CABLE – 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT – 2A per conductor, 40A maximum cable current
- VOLTAGE –
240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE – 0–60°C (32–140°F)
- P1 CONNECTOR – 27-pin terminal block for Direct Logic 06, AutomationDirect part # DO-ACC-2
- P2 CONNECTION – 24 tinned pig-tail leads (only 20 leads are connected to P1, per cable pin-out diagram)
- MINIMUM BEND RADIUS – 65.6 mm [2.58 in]

| ZL-D06-CBL24-nP | |
|---|--------------|
| Rev: A1 | Date: 5/2013 |
| Units: mm [inches] | |
| Scale: none | |
| ZIPLINK DL06 Cable | |
|  | |