


TABLE A

PART NO	LENGTH
ZL-P2-CBL24	0.5m [1.6 ft]
ZL-P2-CBL24-1	1.0m [3.3 ft]
ZL-P2-CBL24-2	2.0m [6.6 ft]

PLC END

ZIPLINK END



PIN-OUT DIAGRAM

P1	P2	P1	P2
1	13	13	1
2	14	14	2
3	15	15	3
4	16	16	4
5	17	17	5
6	18	18	6
7	19	19	7
8	20	20	8
9	21	21	9
10	22	22	10
11	23	23	11
12	24	24	12

NOTES:

- CABLE – 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT – 0.5A per conductor, 32A maximum cable current
- VOLTAGE –
240V AC/DC rated operating voltage
265V AC/DC maximum voltage
- OPERATING TEMPERATURE – 0–60°C (32–140°F)
- P1 and P2 CONNECTOR – 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025–2400
- MINIMUM BEND RADIUS – 80 mm [3.15 in]
- CONNECT P1 TO PLC, CONNECT P2 TO ZIPLINK MODULE

ZL-P2-CBL24-n	
Rev: XB	Date: 07/2013
Units: mm [inches]	
Scale: none	
ZIPLINK Productivity 2000 PLC Cable	