


IO-Link Field I/O

IO-Link Overview

IO-Link is a standardized protocol that enables connection of intelligent devices (sensors and actuators) to an automation system.

Communication takes place between an IO-Link master and one or more IO-Link devices. IO-Link is a point-to-point communication system and is not a fieldbus. A master module has one or more ports and one device can be connected to each port.

The IO-Link master module is the interface between the controller and the IO-Link system, using EtherNet/IP or EtherCAT.



Features

- No field wiring is typically required. IO-Link devices plug into M12 ports.
- Rich sensor data can add diagnostics, history, and engineering units automatically, all delivered over one cable.
- Automatic device configuration can speed up and simplify field replacement.
- IO-Link Masters support daisy-chaining for easy installation of many devices.
- Premiere integration with Productivity PLC and BRX via EDS files

IO-Link Masters		
Part Number	Description	Price
<u>SIOL-EI8B</u>	STRIDE Basic EtherNet/IP IO-Link master, (8) IO-Link capable I/O points, up to (16) discrete I/O points, IO-Link v1.1, 8A, 1A/port, plastic housing, IP65 and IP67, -25 to 70 deg C.	\$05a48:
<u>54631</u>	Murrelektronik Premium EtherNet/IP IO-Link master, (8) IO-Link capable I/O points, up to (16) discrete I/O points, IO-Link v1.1, 16A, 2A/port, plastic housing, IP65 and IP67, -25 to 70 deg C.	\$05a49:
<u>54632</u>	Murrelektronik Premium EtherCAT IO-Link master, (8) IO-Link capable I/O points, up to (16) discrete I/O points, IO-Link v1.1, 16A, 2A/port, plastic housing, IP65 and IP67, -25 to 70 deg C.	\$,-06fdl:
<u>BNI008M</u>	Balluff EtherNet/IP IO-Link master, (8) IO-Link capable I/O points, up to (16) discrete I/O points, IO-Link v1.1.3, 9A, 2A/port, plastic housing, IP67, -5 to 70 deg C, multi-line LCD display.	\$,-06j[6:
<u>BNI00HM</u>	Balluff EtherNet/IP IO-Link master, (8) IO-Link capable I/O points, up to (16) discrete I/O points, IO-Link v1.1.3, 9A, 2A/port, die-cast zinc nickel-plated housing, IP67, -25 to 70 deg C.	\$,-06j[5:
<u>BNI006A</u>	Balluff EtherNet/IP IO-Link master, (8) IO-Link capable I/O points, up to (16) discrete I/O points, IO-Link v1.1.3, 9A, 2A/port, die-cast zinc nickel-plated housing, IP67, -5 to 70 deg C, multi-line LCD display.	\$,-06j[4:


IO-Link Hubs		
Part Number	Description	Price
<u>59507</u>	Murrelektronik IO-Link hub, up to (8) discrete I/O points, (8) 3-pin M8 ports, 24 VDC, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class A Device, 4A, 0.5A/port, IP68. Requires IO-Link master.	\$05a4a:
<u>59710</u>	Murrelektronik IO-Link hub, up to (16) discrete input points, (8) 5-pin M12 A-coded ports, 24 VDC, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class A Device, IP68. Requires IO-Link master.	\$05a4b:
<u>59712</u>	Murrelektronik IO-Link hub, up to (16) discrete I/O points, (8) 5-pin M12 A-coded ports, 24 VDC, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class B Device, 4A, 2A/port, IP68. Requires IO-Link master.	\$,06fdn:
<u>59719</u>	Murrelektronik IO-Link hub, up to (16) discrete I/O points, (8) 5-pin M12 A-coded ports, 24 VDC, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class A Device, 4A, 0.5A/port, IP68. Requires IO-Link master.	\$05a4c:
<u>59738</u>	Murrelektronik IO-Link hub, up to (16) discrete I/O points, (8) 5-pin M12 A-coded ports, 24 VDC, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class A Device, 12A, 4A/port, IP68. Requires IO-Link master.	\$,06fdo:
<u>59840</u>	Murrelektronik IO-Link hub, up to (4) analog input channel(s), (4) 5-pin M12 A-coded port(s), current/voltage, 24-bit, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class A Device, IP65, IP67 and IP68. Requires IO-Link master.	\$05zuz:
<u>59841</u>	Murrelektronik IO-Link hub, up to (4) temperature input channel(s), (4) 5-pin M12 A-coded port(s), RTD, 24-bit, IO-Link v1.1.2 (compatible with v1.1.3), IO-Link Class A Device, IP65, IP67 and IP68. Requires IO-Link master.	\$,06fdx:
<u>BNI00F4</u>	Balluff IO-Link hub, up to (16) discrete I/O points, up to (16) discrete input points, (8) 5-pin M12 A-coded ports, 24 VDC, IO-Link v1.1, IO-Link Class A Device, 4A, 0.2A/port, IP67. Requires IO-Link master.	\$,-06j[7:
<u>BNI00CP</u>	Balluff IO-Link hub, up to (16) discrete I/O points, up to (16) discrete input points, (8) 5-pin M12 A-coded ports, 24 VDC, IO-Link v1.1, IO-Link Class A Device, 9A, 2A/port, IP67. Requires IO-Link master.	\$,-06j[8:
<u>BNI00AJ</u>	Balluff temperature/analog IO-Link hub, up to (8) analog input channel(s), current/voltage/RTD/thermocouple, 16-bit, input RTD type(s): Pt100 and Pt1000, input thermocouple type(s): J, K, IO-Link v1.1, IP67. Requires IO-Link master.	\$,-06j[b:

IO-Link Signal Converters		
Part Number	Description	Price
<u>BNI00C6</u>	Balluff temperature/analog combo converter, 1-channel, current/voltage/RTD/thermocouple, 16-bit, input RTD type(s): Pt100 and Pt1000, input thermocouple type(s): J, K, IO-Link v1.1, stainless steel housing, IP65 and IP67. Requires IO-Link master.	\$,-06j[3:

BALLUFF IO-Link Analog Converter

Features

- Stainless steel designed for field mounting
- Support universal analog in or out



BN100C6

Display & Indicators

Sensor/actuator supply US/UA	Green LED
IO-Link communication indicator	Green LED

Environmental Conditions

Operating temperature	-5°C to +70°C [+23°F to +158°F]
Storage temperature	-25°C to +70°C [-13°F to +158°F]
IP rating	IP67, when threaded in

Materials

Housing material	316L stainless steel, PTFE
Gasket material	FKM 75
Housing shield	Yes

Mechanical Data

Weight (net)	Approx. 105g [3.70 oz]
Dimensions (Dia x L)	18mm dia. x 135.5 mm
Mounting part	18mm diameter mounting clamps
Drawing	PDF

Functional Safety

MTTF (40 °C)	67 years
---------------------	----------

Agency Approvals

CE	Yes
WEEE	Yes
UKCA	Yes
Ecolab	Yes

Interface	
Analog inputs	Analog, voltage/analog, current/analog, temperature (0–10V/–10–10V/0–5V/–5–5V/5–10V/4–20mA/0–20mA/Pt100/Pt1000/Thermocouple Type J/Thermocouple Type K)
Analog outputs	Analog, voltage/analog, current/analog (0–10V/–10–10V/0–5V/–5–5V/5–10V/4–20mA/0–20mA)
Resolution	≤ 16 bit adjustable
Cycle time min.	10 ms
IO-Link version	1.1
Interface	IO-Link 1.1
Process data IN	3 bytes
Process data OUT	2 bytes
Process data cycle min.	10 ms
Transfer rate	COM2 (38.4 kBaud)

Electrical Connection

IO-Link (COM 1)	(1) 4-pin M12 A-coded plug
Connection slots	(1) 5-pin M12 A-coded socket
Contact, surface protection	Nickel-plated 2 µm/gold plated 0.4 µm

Electrical Data

Configurable inputs/outputs	Yes
Current consumption without load, max.	60mA
Current sum UA, actuator	4A
Current sum US, sensor	4A
IO-Link function	Device
IO-Link ports, number	1
Operating voltage Ub	18–30.2 VDC
Rated operating voltage Ue	24 VDC

Pin Assignments

IO-Link		M12 A-coded plug			
	Pin 1	24 VDC US (controller), 260mA			
	Pin 2	24 VDC UA (outputs), 1.4 A			
	Pin 3	GND, reference potential			
	Pin 4	C/Q, IO-Link data transmission channel			
Analog Input		M12 A-coded sockets			
		V, mA Input	V, mA Output	TC	RTD
	Pin 1	24 VDC, 150mA	24 VDC, 1.4 A	n.c.	Pt-
	Pin 2	Input	Output	TC+	Pt-
	Pin 3	GND	GND	TC-	Pt+
	Pin 4	Input	Output	n.c.	Pt+
	Pin 5	n.c.			