



DW Series High Pressure Proximity Sensors



M3, M8 and M12 – DC

- High pressure resistant up to 500 bar
- IP68 rated
- Stainless steel construction with ceramic sensing face
- 10-30 VDC
- LED status indicator
- Lifetime warranty
- IO-Link v1.1 PNP models



DW-AD-621-03E-961
DW-AS-503-P12-624



DW Series High Pressure Proximity Sensors									
Part Number	Price	Size	Sensing Distance	Mounting	Output State	Logic	Connection	Wiring	Drawing Link
DW-AD-621-03E-961	\$;05ux,;	M3	0.8 mm [0.03 in]	Flush	N.O.	NPN	3-wire, pigtail, 6.5 ft [2m]	Diagram 1	PDF
DW-AD-623-03E-961	\$05uy0:			Flush	N.O.	PNP	3-wire, pigtail, 6.5 ft [2m]	Diagram 2	PDF
DW-AD-503-P8	\$05uy1:	M8	1.5 mm [0.05 in]	Flush	N.O.	PNP	3-wire, pigtail, 6.5 ft [2m]	Diagram 2	PDF
DW-AS-503-P12-630 *	\$05uy2:	M12		Flush	N.O.	PNP	3-wire, 4-pin M12 quick-disconnect	Diagram 3	PDF
DW-AS-503-P12-624 *	\$05uy3:			Flush	N.O.	PNP	3-wire, 4-pin M12 quick-disconnect	Diagram 3	PDF
DW-LS-703-P12G	\$05uy5:			Flush	N.O.	PNP	3-wire, 4-pin M12 quick-disconnect	Diagram 3	PDF

* Mounting hardware included.

Wiring Diagrams

Diagram 1

NPN Cable




Diagram 2

PNP Cable






Diagram 3

PNP Connector



Connector

M12 connector





DW Series High Pressure Proximity Sensors Specifications

DW Series High Pressure Proximity Sensors Specifications				
Sensor	DW-AD-62x-03E-961	DW-AD-503-P8	DW-Ax-50x-P12	DW-LS-703-P12G
Assured Operating Distance	0.65 mm [0.02 in]	1.22 mm [0.04 in]		
Rated Operating Distance	0.8 mm [0.03 in]	1.5 mm [0.05 in]		
Material Correction Factors	See the Material influence table			
Output Type	NPN or PNP, N.O.	PNP, N.O.		
Operating Voltage	10 to 30 VDC			
No-load Supply Current	≤ 10mA			
Operating (Load) Current	100mA	≤ 200mA		
Off-state (Leakage) Current	≤ 0.1 mA			
Voltage Drop	≤ 2.0 VDC @100mA	≤ 2.0 VDC		
Switching Frequency	≤ 8,000Hz	800Hz	600Hz	850Hz
Differential Travel (% of Nominal Distance)	≤ 10% s _r	3% S _r ≤ Hyst ≤ 15% S _r		
Repeat Accuracy	0.2 mm	≤ 0.075 mm	≤ 0.1 mm	≤ 0.06 mm
Ripple	≤ 20%			
Operating Pressure / Peak Pressure	≤ 200 bar	≤ 500 bar / ≤1000 bar		≤ 500 bar / ≤ 800 bar
Reverse Polarity Protection	Yes			
Short-Circuit Protection	Yes			
Operating Temperature	-25 to 70°C [-13 to 158°F]	-25 to 100°C [-13 to 212°F]		-25 to 85°C [-13 to 185°F]
Protection Degree (DIN 40050)	IP68, IP69K	IP68		IP68, IP69K
Indication/Switch Status	Yellow LED			
Housing Material	Stainless steel V2A	Stainless steel V4A	Stainless-steel DIN 1.4305 / AISI 303	Stainless steel V4A / 1.4435 / AISI 316L
Sensing Face Material	Ceramic	ZrO ₂ [Zirconium dioxide]	ZrO ₂ [Zirconium dioxide]	Stainless steel V4A / 1.4435 / AISI 316L
Shock/Vibration	IEC 60947-5-2 / 7.4			
Tightening Torque	N/A	12 N•m	40 N•m	50 N•m max
Weight	18g [0.63 oz]	40g [1.41 oz]	27g [0.95 oz]	137g [4.83 oz]
Connection	PUR, 3-wire, pigtail, 6.5 ft [2m]		3-wire, 4-pin M12 quick-disconnect	
IO-Link	v1.1 PNP models			
Agency Approvals	CE, cULus E239373			

Note: To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

Accessories for 3mm Sensors

Right-angle Mounting Bracket

Mounting bracket, right-angle, 316L stainless steel. Package of 2.
For use with 3mm sensors.

Accessories for 3mm Sensors				
Part Number	Price	Description	Drawing Link	Weight [lb]
OPT2037	\$--1nll:	Wenglor mounting bracket, right-angle, 316L stainless steel. Package of 2. For use with 3mm sensors.	PDF	0.02



[OPT2037](#)