

prosense® 10K-3 Thermistor Probes with Lead Wire Transition

NTC10K3-T06L06-02

Overview

- NTC 10k Thermistor Type 3
- 1/4" diameter, 316 stainless steel sheath to protect against harsh environments
- 6", 12", or 18" probe length
- 4 point crimp and sleeve transition to PVC cable
- 6-foot cable with 2 inches of 24AWG wire pre-stripped 1/4 inch and tinned
- Made in the USA



10K-3 Thermistor Probes with Lead Wire Transition									
Part Number	Pcs/Pkg	Wt (lb)	Price	Drawing Link	Type	Probe Diameter (O.D.)	Probe Length	Temperature Sensing Range	Mounting
<u>NTC10K3-T06L06-02</u>	1	0.11	\$,6alc:	<u>PDF</u>	10K-AN Type 3 Thermistor	1/4"	6"	-40 to 125° C (-40 to 257° F)	ProSense compression fitting (see accessories purchased separately)
<u>NTC10K3-T12L06-02</u>		0.16	\$,6ald:	<u>PDF</u>			12"		
<u>NTC10K3-T18L06-02</u>		0.20	\$,6ale:	<u>PDF</u>			18"		


Technical Specifications	
Sensing Element	Epoxy Coated NTC Thermistor
No-Load Resistance	10kΩ at 25°C
Accuracy	± 0.2°C from 0°C to 70°C
Probe	ø1/4", 316 stainless steel sheath
Minimum Installation Depth	3" (76 mm)
Sensing Element Response Time	Approximately 1 second*
Wiring	72 inches of PVC cable with 2 inches of 24AWG wire stripped 1/4 inch and tinned

* The sensing element has an approximate response time of 1 second in a well stirred liquid bath. Different constructions will have different thermal responses.



Note: Check the chemical compatibility of the sensor's wetted parts with the medium to be measured.

Wiring Information



- No polarity

prosense® 10K-3 Thermistor Probes with Lead Wire Transition - Accessories

Accessories

Part No.	Description	Pcs/Pkg	Price
<u>BCF14-125N</u>	Compression fitting, brass, for 1/4 inch diameter temperature probes, 1/8 inch NPT male thread	1	\$ekq:
<u>BCF14-25N</u>	Compression fitting, brass, for 1/4 inch diameter temperature probes, 1/4 inch NPT male thread	1	\$eks:
<u>BCF14-50N</u>	Compression fitting, brass, for 1/4 inch diameter temperature probes, 1/2 inch NPT male thread	1	\$,ekt:
<u>CF14-125N</u>	Compression fitting, 316 stainless steel, for 1/4 inch diameter temperature probes, 1/8 inch NPT male thread	1	\$,ek]:
<u>CF14-25N</u>	Compression fitting, 316 stainless steel, for 1/4 inch diameter temperature probes, 1/4 inch NPT male thread	1	\$,ek[:
<u>CF14-50N</u>	Compression fitting, 316 stainless steel, for 1/4 inch diameter temperature probes, 1/2 inch NPT male thread	1	\$0ek_:
<u>CFTF-14</u>	Teflon™ ferrule for brass or stainless steel compression fittings and 1/4 diameter temperature probes	5	\$,ea!:


See end of section for full listing of accessories and dimension information.

* Working pressure of compression fitting should not exceed 500 psi. However, we recommend any pressure application use a thermowell.

[CFTF-14](#)



[CF14-50N](#)



[CF14-25N](#)



[CF14-125N](#)



Stainless Steel Compression Fittings

[BCF14-50N](#)



[BCF14-25N](#)



[BCF14-125N](#)



Brass Compression Fittings