

# prosense® RTD Threaded Bolt Sensors



**RTD1-N38P14-01**

## Overview

- Typically used to measure the temperature of the nozzle of an injection molding machine without being in direct contact with the molten plastic.
- The small size of this sensor makes it ideal for other general areas of use such as mounting in bearing housings, sealing bars, heat plates, and other limited space applications
- 100 ohm platinum RTD 3-wire element
- Class A accuracy
- 1/4-28 UNF threaded stainless steel rotating bolt allows for easy installation
- 6-foot lead wires with stainless steel overbraid
- Made in the USA

RTD Threaded Bolt Sensors						
Part Number	Pcs/Pkg	Wt (lb)	Price	Type	Bolt	Temperature Sensing Range
<b>RTD1-N38P14-01</b>	1	0.25	\$54k9:	PT 100, 3-wire	1/4-28 x 3/8" SS - Rotating Bolt	-40 to 316°C (-40 to 600°F)


Technical Specifications	
<b>Sensing Element</b>	Single 100Ω platinum (Pt 100), 3-wire; TCR = 0.00385 Ω/Ω/°C
<b>Initial Accuracy</b>	Class A $\pm[0.15 + 0.002  t ]$ °C
<b>Response Time</b>	7 seconds, 63% of a 25 to 77°C step change (ASTM E1137)
<b>Wiring</b>	6 foot stranded 24 AWG wire leads with stripped ends, Kapton insulation and stainless steel overbraid




*Note: Check the chemical compatibility of the sensor's wetted parts with the medium to be measured.*

## Dimensions

inches [mm]



## Wiring Information



## Accessories

Part No.	Description	Pcs/Pkg	Price
<b>RTD-SP</b>	RTD 3-pin connector, standard round pin plug, maximum continuous temperature 400°F (200°C), white body, copper pins, 14 AWG maximum (2.0 mm) wire size	1	\$42x:
<b>RTD-SJ</b>	RTD 3-pin connector, standard round pin jack, maximum continuous temperature 400°F (200°C), white body, copper pins, 14 AWG maximum (2.0 mm) wire size	1	\$042v:
<b>WCB-S</b>	Wire / cable clamp bracket for use with standard thermocouple and RTD connectors	4	\$05hp:

*Note: Full listing of accessories and dimension information available at the end of this section. RTD extension lead wire available at [www.automationdirect.com](http://www.automationdirect.com)*