

# SoliTherm® Thermoelectric Coolers



## Applications

Thermoelectric elements utilize the Peltier Effect to create a temperature difference between the internal and ambient heat sinks, making internal air cooler while dissipating heat into the external environment. Fans assist the convective heat transfer from the heat sinks, which are optimized for maximum flow.

The Seifert SoliTherm® Peltier thermoelectric coolers can be mounted in nearly every position (except roof mounting) because they don't have a compressor or any moving parts aside from the fans. Depending on the application, condensation management may need to be considered. Seifert SoliTherm thermoelectric coolers are available as recessed with the internal heat sink and fan inside the enclosure and the ambient components on the outside. But, frames are available for external mounting. These thermoelectric coolers are resistant to extreme ambient conditions and can operate effectively even in environments that are dusty and oily. They comply with European standards IEC/TC 62610-1 and IEC/TC 62610-3, and can be used for both indoor and outdoor applications.

## Construction

- Recessed mounting (flush-mounting kit sold separately)
- Cooling capacities from 100 to 680 BTU/H [30W to 200W]
- Operating Temperature Range: -4°F to 149°F [20°C to 65°C]
- AISI 304 stainless steel housing
- Condensate tray and drain sold separately
- Mounting nut torque: 3.3 lb-ft [4.5 Nm]
- Connection: Terminal block
- 24 VDC units require thermostat for set-point control

## Agency Approvals


- CE, RoHS
- UL Recognized File number: SA32278
- NEMA 4X
- IP 66



SoliTherm® Thermoelectric Cooler General Specifications							
Part Number	Nominal Power / Max (W)	Cooling Capacity	Operating Voltage	Inrush Current (A)	Max Current (A)	Recommended Fuse Size (A)	Integral Thermostat
<a href="#">3035303</a>	44 - 52	100 BTU/H [30W]	24 VDC	4.0	2.2	5	No
<a href="#">3050303</a>	58 - 60	170 BTU/H [50W]		3.7	2.5	4	
<a href="#">3102303</a>	115 - 118	340 BTU/H [100W]		7.4	4.9	8	
<a href="#">3152303</a>	170 - 180	510 BTU/H [150W]		11	7.5	10	
<a href="#">3200303</a>	260 - 280	680 BTU/H [200W]		17	11.6	16	
<a href="#">6105313</a>	125 - 139	340 BTU/H [100W]	120 VAC	1.6	1.2	2	Yes
<a href="#">6105323</a>			230 VAC	0.8	0.6	1	

Notes: Power and Cooling Capacity values are for 95°F [35°C] internal and ambient temperatures. Refer to Performance Graphs for values corresponding to other conditions.  
Fuses are Class T Time Delay.

## Airflow Example



THERMOELECTRIC COOLING PRINCIPLE

# SoliTherm® Thermoelectric Coolers




SoliTherm Thermoelectric Coolers					
Part Number	Price	Dimensions HxWxD	Cutout Dimensions	Weight (lb)	Drawing Link
<a href="#">3035303</a>	\$,-05i3t	6.04 x 4.33 x 5.07 [110 x 154 x 129]	4.80 x 3.23 [122 x 82]	4	<a href="#">PDF</a>
<a href="#">3050303</a>	\$,-04jn1	8.11 x 6.06 x 5.31 [206 x 154 x 135]	6.69 x 4.72 [170 x 120]	7	<a href="#">PDF</a>
<a href="#">3102303</a>	\$,-004jn2	7.87 x 11.97 x 5.43 [200 x 304 x 138]	10.24 x 6.30 [260 x 160]	13	<a href="#">PDF</a>
<a href="#">3152303</a>	\$,-004jn3	15.75 x 7.09 x 6.73 [400 x 180 x 171]	14.61 x 6.10 [371 x 155]	20	<a href="#">PDF</a>
<a href="#">3200303</a>	\$,-004jn4	15.75 x 7.09 x 6.73 [400 x 180 x 171]	14.61 x 6.10 [371 x 155]	22	<a href="#">PDF</a>
<a href="#">6105313</a>	\$,-0062#j	11.02 x 13.78 x 6.5 [280 x 350 x 164]	12.68 x 9.92 [322 x 252]	21	<a href="#">PDF</a>
<a href="#">6105323</a>	\$,-0062#k				<a href="#">PDF</a>


Note: Dimensions in inches [millimeters].




[3035303](#)  
24VDC



[3050303](#)  
24VDC



[3102303](#)  
24VDC




# SoliTherm® Thermoelectric Coolers




## Performance Graphs




**3152303**  
24VDC



**3200303**  
24VDC



**6105313 and 6105323**  
120 VAC 230 VAC



# SoliTherm® Thermoelectric Coolers



## External Mounting Kit



1012305

This kit is for external mounting of SoliTherm Thermoelectric Coolers. Add these kits when there isn't space in the enclosure for the internal heat sink and fan.

### Features

- AISI 304 stainless steel
- Hardware included

SoliTherm Thermoelectric Cooler External Mounting Kit		
Part Number	Price	For Use With
<b>1011305</b>	\$-05i3o:	3035303
<b>1012305</b>	\$-04jn6:	3050303
<b>1013305</b>	\$-4jn7:	3102303
<b>1014305</b>	\$-04jn8:	3152303 3200303
<b>1015305</b>	\$-04jn9:	6105313 - 6105323

## Condensate Drain Kit



1001303

As with a conventional air conditioner, cooling air with a thermoelectric cooler may produce condensation. Consider adding condensation management in humid environments.

This kit contains a condensate tray and drain for use with SoliTherm Thermoelectric Coolers.

Mounts to cooler using existing mounting bolts for enclosure.

### Features

- Stainless steel AISI 304
- Hardware included

SoliTherm Thermoelectric Cooler Condensate Drain Kit		
Part Number	Price	For Use With
<b>1001303</b>	\$-04jna:	3035303 3050303
<b>1003303</b>	\$-04jnb:	3102303
<b>1002303</b>	\$-04jnc:	3152303 3200303
<b>1004303</b>	\$-04jnd:	6105313 - 6105323