


# STEGOJET Compact Fans



019250-00



Range of Rotation

## Applications

The STEGOJET is a compact, powerful built-in fan. It is designed for precise cooling of heat sources and for maximum rotation range with an air output in almost any direction. The dual clip system (two clips at a 90° angle) allows four different positions on a DIN rail, while the hinge in the housing can be moved at a 40° angle. Additionally, the airflow at the air outlet can be directed at a 45° angle and the air duct can be turned 360°.

## Features

- Prevents heat pockets
- Wide voltage range
- Compact design
- Quick connection
- Panel or DIN rail mounting





## StegoJet Fan Specifications

<b>Axial Fan, Ball Bearing</b>	Service life 40,000h at 140°F (60°C) and 90% RH
<b>Power Consumption</b>	4W
<b>Connection</b>	2-pole dual cage clamp for solid wire – 14AWG (2.5 mm <sup>2</sup> ) stranded wire (with wire end ferrule) – 16AWG (1.5 mm <sup>2</sup> )
<b>Housing</b>	Plastic, UL 94V-0, black
<b>Mounting</b>	Clip for 35mm DIN rail, EN 60715 or M5 screws and washers (not included) – torque 2 N·m max.
<b>Mounting Position</b>	Variable
<b>Operating/Storage Temperature</b>	+14° to +140°F (-10° to +60°C) / -22° to +158°F (-30° to 70°C)
<b>Operating/Storage Humidity</b>	Max. 90% RH (non-condensing)
<b>Protection Class</b>	II (double insulated)
<b>Protection Type</b>	IP20
<b>Approvals</b>	CE, UL Recognized File No. E234324, RoHS compliant

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at [www.automationdirect.com](http://www.automationdirect.com)

## Dimensions



Part Number	Price	Description	Operating Voltage	Air Flow, Free Blowing	Weight (approx.)
<b>019250-00</b>	\$;-00,zj:	DIN rail mounting	100-240V AC, 50/60 Hz (min. 90VAC, max. 265VAC)	16.2 cfm (27.6 m <sup>3</sup> /h)	7oz (198g)
<b>019250-01</b>	\$;00,zk:	Panel mounting			