



Audible Signal Devices

Wall-mount Signal Horns

Features

- Wall mounting
- Continuous tone
- 148mm diameter

570 Series Signal Horns Specifications		
Part Number	57005255	57005267
Price	\$00?a1:	\$00?a2:
Drawing Link	PDF	PDF
Description	Signal Horn	
Voltage	24VDC	115VAC
Current Consumption	350mA	200mA
Tone Frequency	150Hz	100Hz (supply frequency)
Maximum Volume	108dB @ 1m	
Tone Type	Continuous	
Life Duration	> 250h	
Operating Temperature	-20 to 60°C [-4 to 140°F]	
Protection	IP55	
Weight	880g [31.04 oz]	860g [30.34 oz]
Housing Material	ABS/PC	
Connection	Screwable con max. 2.5 mm² single wire, 18-14 AWG	
Agency Approvals	CE, RoHS	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.





Audible Signal Devices

Wall-mount Signal Horns

Features

- Corrosion-resistant aluminum housing, salt water proof
- Wall mounting
- Continuous tone
- 132mm diameter



571 Series Signal Horns Specifications		
Part Number	57105255	57105267
Price	\$00?a3:	\$00?a4:
Drawing Link	PDF	PDF
Description	Signal Horn	
Voltage	24VDC	115VAC
Current Consumption	350mA	200mA
Tone Frequency	150Hz	100Hz (supply frequency)
Maximum Volume	108dB @ 1m	
Tone Type	Continuous	
Life Duration	> 250h	
Operating Temperature	-20 to 60°C [-4 to 140°F]	
Protection	IP55	
Weight	880g [31.04 oz]	860g [30.34 oz]
Housing Material	Aluminum	
Connection	Screwable con max. 2.5 mm ² single wire, 18-14 AWG	
Agency Approvals	CE, RoHS	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



Features

- Modern electro-mechanical design
- Wall mounting
- Continuous tone
- 178mm diameter



573 Series Signal Horns Specifications		
Part Number	57300055	57300067
Price	\$00?a5:	\$00?a6:
Drawing Link	PDF	PDF
Description	Signal Horn	
Voltage	24VDC	115VAC
Current Consumption	350mA	200mA
Tone Frequency	150Hz	100Hz (supply frequency)
Maximum Volume	105dB @ 1m	
Tone Type	Continuous	
Life Duration	> 250h	
Operating Temperature	-30 to 50°C [-22 to 122°F]	
Protection	IP65	
Weight	1200g [42.33 oz]	1150g [40.57 oz]
Housing Material	Polycarbonate/ABS-blend	
Connection	Screwable con max. 2.5 mm ² single wire, 18-14 AWG	
Agency Approvals	CE, RoHS	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.