


Product Overview

Looking for a common sense way to buy industrial controls?

It's time to try AutomationDirect

VOTED #1
Best in SERVICE
7 YEARS
 2001-2002-2003-2004
 2005-2006-2007



BUY DIRECT AND SAVE

Thousands of large and small companies alike have turned to AutomationDirect as their direct supplier of industrial automation products for electrical control systems. We currently offer PLCs, operator interfaces, AC drives, motors, stepper and servo systems, sensors, motor controls, pilot devices, connection systems, enclosures and more. We're so sure you'll be happy with the value, we offer a 30-day money back guarantee on almost every product that we stock.

BEST PRICES EVERY DAY

Our direct business model allows us to offer high-quality products with minimal overhead. We pass the savings on to you with our low everyday prices, which are typically **well below the list prices** of most traditional automation manufacturers. (See Web site or catalog for documented price comparisons).

VOTED #1 IN CUSTOMER SERVICE

Our tech service department is staffed by field service veterans at our headquarters just north of Atlanta, GA. Independent surveys completed by the readers of Control Design magazine placed us at the top of the list (in at least one product category) seven years in a row in their Readers' Choice Awards. Other independent surveys by magazines such as Control and Control Engineering have echoed the results.

SAME-DAY SHIPPING

At AUTOMATIONDIRECT, the majority of our products are stocked for same-day shipping, when you place your order by 6 p.m. ET (except for motors 12 p.m., enclosures 4 p.m., Fed Ex 5 p.m.). Already one of the most automated warehouses in the industry, we constantly assess and improve our logistics to maintain our high standard for efficiencies and order accuracy of 99.98%.

SATISFIED CUSTOMERS

It is important for us to get feedback in order to serve our customers better, so we send out satisfaction surveys for many of the sales and technical support calls that we take.

At: www.automationdirect.com/you_talk you can see what our current customers are saying about us.

Call 1-800-633-0405 or go to www.automationdirect.com to get our FREE catalog or browse the online store. Both are complete with pricing, specifications, competitive comparisons and more.

PLC Products ...

Family	I/O Count (In/Out)	Form Factor	Power Options	CPU Options	Base Module Slots	CPU Communications Ports	Ethernet Available	High Speed Counting	Pulse Output	Analog	Additional Bases	Remote I/O	Product Photo
DL05	8 - 24 6 - 24	Brick (Integrated I/O) plus one option slot	AC or DC	1	1	2	Yes	5kHz (Integrated I/O) or 100kHz (H0-CTRIO) module	7kHz (Integrated I/O) or 25kHz (H0-CTRIO) module	Current, Voltage, RTD, Thermocouple	No	No	
DL105	8 8	Brick (Integrated I/O)	AC or DC	1	0	1	No	5kHz (Integrated I/O) or 100kHz (H0-CTRIO) module	7kHz (Integrated I/O) or 25kHz (H0-CTRIO) module	None	No	No	
DL06	20 - 84 16 - 80	Brick (Integrated I/O) plus four option slots	AC or DC	1	4	2	Yes	5kHz (Integrated I/O) or 100kHz (H0-CTRIO) module	7kHz (Integrated I/O) or 100kHz (H0-CTRIO) module	Current, Voltage, RTD, Thermocouple	No	No	
DL205	4 - 8,000 4 - 8,000	Modular Base	AC or DC	6	2-8	1-2	Yes	5kHz (D2-CTRINT) module or 100kHz (H2-CTRIO) module	5kHz (D2-CTRINT) module or 25kHz (H2-CTRIO) module	Current, Voltage, RTD, Thermocouple	Yes	Yes	
DL305	8 - 320 8 - 320	Modular Base	AC or DC	3	5-10	1-2	No	No	No	Current, Voltage, Thermocouple	Yes	Yes	
DL405	8 - 3,584 8 - 3,584	Modular Base	AC or DC	3	4-8	1-3	Yes	100kHz	25kHz	Current, Voltage, RTD, Thermocouple	Yes	Yes	

... PLC PRODUCTS

<p>ZipLink PLC Wiring System</p>	<ul style="list-style-type: none"> • Plug-in termination • Fuse, relay, and communications breakout terminals and cables 	
<p>Terminator I/O</p>	<ul style="list-style-type: none"> • Field termination I/O, AC & DC supplied, up to 16 modules per node • Ethernet 10/100 Mbit (TCP/IP, Modbus TCP, IPX) • DeviceNet / Profibus / Modbus RTU • Koyo Serial Remote I/O • Analog, thermocouple, RTD, AC, DC, relay output modules, high-speed counter, high-speed pulse output 	


PC BASED HMI/CONTROL/CONNECTIVITY SOFTWARE

<p>KEPDirect PLC & EBC OPC/DDE Server</p>	<ul style="list-style-type: none"> • PLC OPC/DDE server • Ethernet I/O OPC/DDE server 	
<p>DataNet OPC Software ———></p> <p>DataWorx Software ———></p> <p>DataLynx Software ———></p>	<p>Uses OPC technology to display data from an industrial device (such as a PLC) on any Web browser; dynamic color monitoring gives instant access from any computer on the Web</p> <p>Access industrial data over Ethernet networks with Report-by-Exception technology; log your data to a comma or tab delimited file and archive to a directory for management</p> <p>Poll your remote, Modbus enabled device over phone lines using off-the-shelf modems, no SCADA system or third-party software required</p>	
<p>Think & Do Live! PC Control Software</p>	<ul style="list-style-type: none"> • Flowchart logic • Integrated HMI • OPC client and server • Productivity analysis tools • SQL interface • Integrated motion and vision control • Common tag database • 64 PID loops • Multi-dimensional arrays • Ethernet and field bus I/O drivers 	
<p>LookoutDirect HMI/SCADA Software</p>	<ul style="list-style-type: none"> • PC-based HMI/SCADA software • High-speed event driven processing • Bumpless runtime editing • Real-time and historical trending • Easy-to-configure datalogging • Advanced security capabilities • Local and distributed alarming • Supports most popular PLCs • OPC client/server • Integrated graphics library • Browse and select networking 	

OPERATOR INTERFACES ...

<p>C-more PLC Touchscreens</p>	<ul style="list-style-type: none"> • Vivid TFT panels with 65,536 colors (6, 8, 10, 12 and 15-inch models) • Cost-conscious STN panels with grayscale or 256 colors (6-inch models) • Analog touch overlay • 10MB project memory on 6 to 10-inch units; 40MB project space on 12 and 15-inch units • Serial RS232, RS422/485 and Ethernet 10/100BaseT communications • 4,000 built-in symbols and 10 typefaces with hundreds of font sizes • PID faceplate, trending, alarming and recipe abilities • Built-in FTP server, e-mail client and Web server 	
<p>C-more Micro-Graphic Operator Panels</p>	<ul style="list-style-type: none"> • Text/graphical panels with 3-inch screen, and 5 function keys with LED indicators • Touch or non-touch models; regular and high-contrast screen models • Optional snap-on keypads • 768 Kb project memory 	

... OPERATOR INTERFACES

<p>Atlas™ Industrial/Touchscreen Monitors</p>	<ul style="list-style-type: none"> • Heavy duty industrial monitors from 15" to 19" • Resistive touchscreens (with or without) • UL and CE 	
<p>Optimate Text Panels</p>	<ul style="list-style-type: none"> • Text display • Annunciator panels • Serial Drivers - <i>Direct</i>LOGIC, Allen Bradley 	

DRIVES/MOTORS/MOTOR CONTROLS/MOTION ...

<p>GS and DURApulse Series AC Drives</p>	<ul style="list-style-type: none"> • Variable frequency drives from 0.25 to 100 HP • 115, 230, 460 and 575 volt versions • Volts/Hz • Sensorless vector control available 	
<p>Hitachi AC Drives</p>	<ul style="list-style-type: none"> • Flux vector variable frequency drives from 0.25 to 30 HP • 230 and 460 volt versions 	
<p>Motor Controls and Contactors</p>	<ul style="list-style-type: none"> • Full line of Fuji Electric IEC rated contactors, overloads, manual motor starters and accessories up to 300 HP • Cutler-Hammer Freedom Series IEC contactors and starters 	
<p>IronHorse™ General Purpose AC Motors</p>	<ul style="list-style-type: none"> • 56C frame rolled steel, from 0.33 to 2 hp, 115/208-230V • T-frame cast iron, from 1 to 300 hp, 208-230/460V • Motor slide bases 	
<p>Marathon® Inverter Duty Motors</p>	<ul style="list-style-type: none"> • Marathon MAX series inverter and vector duty motors from 0.25 to 100 HP • Available with encoder feedback options • 230, 460 and 575 volt models available • microMax® (1/4 - 10HP) • BlackMax® (1/4 - 30HP) • BlueChip XRI® (40 - 100HP) - Premium Efficiency • BlueMax® 2000 (40 - 100HP) 	
<p>SureStep Stepper Systems</p>	<ul style="list-style-type: none"> • Microstepping drive to 10,000 steps per revolution • Open loop stepping • Motors, drives and power supplies available • Holding torque from 83 Oz/In to 434 Oz/In 	

... DRIVES/MOTORS/MOTOR CONTROLS/MOTION

SureServo™ Drives & Motors

- AC Servo systems ranging from 100W to 3kW and 230V single/3 phase
- Standard cable sets are available from 10-100 ft.
- 3 Tuning Modes: Manual, adaptive auto-tune, and adaptive easy-tune modes
- Control modes include position, speed, and torque
- Drives have on board indexer & built-in RS-232/422/485 Modbus communications



PANEL BUILDING PRODUCTS

Hubbell-Wiegmann Enclosures

- Carbon steel
- Stainless steel
- Non-metallic
- Control, operator and disconnect enclosures
- NEMA 1, 3R, 4, 4X, 4/12, and 12 ratings
- Full line of accessories



Pilot Devices

- 22 mm metal pilot devices
- Cutler-Hammer 22 mm and 30 mm pilot devices & stacklights
- Includes pushbuttons, indicators, selector switches, toggle switches and accessories

Foot Switches

- Single and double foot switches



DINnector Terminal Blocks

- Single, double, and triple level terminal blocks and fuse holders in a variety of colors
- Screw terminal or screwless clamp

Hookup Wire

- 10 to 18 gauge MTW, 4 to 14 gauge THHN, 16 to 18 gauge TFFN
- All in a variety of colors



Wire Duct and Flexible Tubing

- Standard or thin-finger rigid wire duct
- Flexible duct also available
- Spiral wrap - 1/2 to 4 inch diameter, natural or white
- I-Flex liquid-tight tubing



POWER PRODUCTS ...

MCCBs

(Molded Case Circuit Breakers)

- UL489 Listed
- G, F, K and L frame sizes
- Rotary handle or flex shaft for external access
- 15 to 600 amp range



Disconnects

- Ferraz non-fusible, handles up to 800A loads
- Ferraz fusible, handles up to 200A loads

Load Switches

- High breaking capacity (AC 22A - AC 23A)
- Double break contacts

Supplementary Protectors

- Current limiting design provides fast short circuit interruption
- Thermal magnetic overcurrent protection
- 1, 2 and 3-pole models



Fuses

- Branch circuit rated for 600 VAC with compact dimensions
- Fast-acting or time-delay designs
- Metal, glass and ceramic models available

Fuse Holders & Fuse Blocks

- Multiple pole configurations with finger-safe protection
- Optional 'open-fuse' indication



POWER PRODUCTS

DC Power Supplies

- 12 and 24 volt DC switching power supplies
- 20 to 600 watt capacities
- Metal or plastic enclosures
- DIN rail or panel mountable

DC-DC Converters

- 4 models, with input ranges of 9.5 to 18 VDC and 18 to 75 VDC;
- 5, 12 and 24V adjustable output ranges

Control Transformers

- Hammond Imperator Series**
- 50VA to 1kVA
 - 50/60 Hz, 600V



SENSORS/ENCODERS

Presence Sensors

- Inductive
- Photoelectric
- Capacitive
- Ultrasonic
- Fiber optic
- Light screens



Limit Switches

- Heavy duty IEC
- Double-Insulated (PBT)

Encoders

- Light, medium, and heavy duty
- 6 mm/8 mm/10 mm shafts
- Incremental and absolute, solid and hollow shafts



Process and Instrumentation

- AcuAMP current switches and transducers
- ProSense pressure switches and transmitters



CONTROL COMPONENTS

Process Controls

- SOLO and other process controllers, from simple on/off control to full PID
- Signal conditioners for mA, voltage, RTD, and thermocouples

Relays

- General purpose industrial relays in cube, card and solid state models
- Timer Relays (Digital, 1/16 DIN, mini-DIN)



COMMUNICATION PRODUCTS

Communication Products

- Serial and Ethernet radio modems
- Standard telephone modems
- RS-232 to RS-422/485 converters
- Industrial Ethernet switches
- USB to RS-232 converter



www.automationdirect.com

Call 1-800-633-0405 or go to www.automationdirect.com to get our FREE catalog or browse the online store. Both are complete with pricing, specifications, competitive comparisons and more.