



Nickel-Plated Brass Push-to-Connect Fittings

Part No. [UL532-B](#)

NITRA pneumatic push-to-connect union elbow fittings with nickel-plated brass body and stainless steel tube gripping claws. For use with flexible tubing. Five fittings per package.

- Performs well in harsh duty or washdown applications
- Working Pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)

NITRA™ Nickel-Plated Brass Union Elbow					
Imperial Tube					
Part No.	Size	Price	Drawing Link	Qty. per pack	Weight (lb)
UL532-B	(1) 5/32in (4mm) push-to-connect to (1) 5/32in (4mm) push-to-connect	\$602b:	PDF	5	0.15
UL14-B	(1) 1/4in push-to-connect to (1) 1/4in push-to-connect	\$602d:	PDF	5	0.17
UL38-B	(1) 3/8in push-to-connect to (1) 3/8in push-to-connect	\$602f:	PDF	5	0.37
Metric Tube					
UL6M-B	(1) 6mm push-to-connect to (1) 6mm push-to-connect	\$602c:	PDF	5	0.18
UL8M-B	(1) 5/16in (8mm) push-to-connect to (1) 5/16in (8mm) push-to-connect	\$602e:	PDF	5	0.23

Part No. [UT532-B](#)

NITRA pneumatic push-to-connect union T fittings with nickel plated brass body and stainless steel tube gripping claws. For use with flexible tubing. Five fittings per package.

- Performs well in harsh duty or washdown applications
- Working Pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)

NITRA™ Nickel-Plated Brass Union T					
Imperial Tube					
Part No.	Size	Price	Drawing Link	Qty. per pack	Weight (lb)
UT532-B		\$602g:	PDF	5	0.14
UT14-B		\$602i:	PDF	5	0.24
UT38-B		\$602k:	PDF	5	0.5
Metric Tube					
UT6M-B		\$602h:	PDF	5	0.25
UT8M-B		\$602j:	PDF	5	0.31




Nickel-Plated Brass Push-to-Connect Fittings


NITRA nickel-plated brass push-to-connect fittings are an excellent choice for many industrial applications. They have an attractive, easily maintained finish and have a higher pressure and temperature rating when compared to resin fittings.

Features

- Large selection of fitting configurations
- Inch and metric sizes available
- Hybrid Inch to metric conversion fittings available
- NPT, BSPT (R) and BSPP (G) threads available
- Nickel-plated brass bodies, threads and release rings
- Threaded elbow and tee bodies can be rotated after installation
- For use with air and water
- Working pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)



Ideal for washdown and harsh environments



Fitting Cut-away Diagram