




# VDCT Series DC Voltage Transducers



## Applications

- Detect below normal or “brown out” voltage conditions; protect against possible motor overheating.
- Monitor over voltage conditions associated with regenerative voltage to help in diagnosing/avoiding motor drive issues.
- Detect voltage conditions which may cause stress in or damage to soft starter components (SCRs).

## Features

- **Accurate Output:** Two ranges available for your application, up to 50VDC
- **Standard 4-20 mA Output:** Industry standard output makes use with existing controllers, data loggers and SCADA equipment easy and reliable.
- **Input/Output Isolation:** Input and output circuitry electrically isolated for improved safety of use.
- **Compact DIN rail Mount Enclosure:** Space saving 35mm wide enclosure makes installation quick and easy.

The VDCT series DC voltage transducers are high-performance transducers for sensing voltage in DC powered installations. Applicable on circuits up to 50VDC, the VDCT series models provide a fully isolated, 4-20 mA output proportional to rated nominal voltage in DC circuits. Housed in a slim, compact, easy-to-install DIN rail mounted enclosure, the VDCT series comes in two different nominal voltage ranges.

## Agency Approvals



VDCT Series DC Voltage Transducers				
Part Number	Description	Pcs/Pkg	Wt (lb)	Price
VDCT015-42-24	Single-phase DC voltage transducer, 0-15 VDC input range, 4-20 mA output (sinking)	1	0.25	\$135.00
VDCT050-42-24	Single-phase DC voltage transducer, 0-50 VDC input range, 4-20 mA output (sinking)	1	0.25	\$135.00

VDCT Series Specifications	
<b>Power Supply</b>	24 VAC/DC External Power (20-45 VDC), <2VA Use Class 2 power supply
<b>Input</b>	15V (for monitoring 12VDC) and 50V (for monitoring 24, 36, 48 VDC), not to exceed 600VDC
<b>Output</b>	4-20mA proportional; capped at 24mA max
<b>Response Time</b>	250ms (to 90% value)
<b>Accuracy</b>	<1%
<b>Linearity</b>	<0.5%
<b>Output Loading</b>	500Ω maximum
<b>Isolation Voltage</b>	2500 Volts per UL
<b>Frequency Range</b>	DC
<b>Operating Temperature</b>	-4 to 122°F (-20 to 50°C) (surrounding sensor)
<b>Case</b>	UL94V-0 Flammability Rating
<b>Environmental</b>	Operating temperature: -4 to 122°F (-20 to 50°C)
	Relative humidity: 0-95% RH, Non-condensing
	Pollution Degree 2
	Altitude to 2000 meters
<b>Agency Approvals</b>	UL/cUL (E222847), CE

\* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at [www.AutomationDirect.com](http://www.AutomationDirect.com)

Company Information

Drives

Soft Starters

Motors

Power Transmission

Motion: Servos and Steppers

Motor Controls

Sensors: Proximity

Sensors: Photoelectric

Sensors: Limit Switches

Sensors: Encoders

Sensors: Current

Sensors: Pressure

Sensors: Temperature

Sensors: Level

Sensors: Flow

Pushbuttons and Lights

Stacklights

Signal Devices

Process

Relays and Timers

Pneumatics: Air Prep

Pneumatics: Directional Control Valves

Pneumatics: Cylinders

Pneumatics: Tubing

Pneumatics: Air Fittings


Appendix Book 2

Terms and Conditions




# VDCT Series DC Voltage Transducers

## Connection



## Dimensions

Inches [mm]



### VDCT Series

See our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete Engineering drawings.