


ASO Safety Solutions 25mm x 30mm SENTIR Edges and End Caps



1502-2110



1502-2112

M8 Connector



Use pins 1 and 3 for continuity.



1804-2205



1804-2195



1804-0565



2002-0230



9501-0160

The SENTIR edge safety contact edges of ASO Safety Solutions are pressure-sensitive sensors applied to ensure the safety of closing edges at possible crushing or shearing points which are prone to accidents. They may be installed near automatic gates, machines and other facilities for handling equipment or moving stage elements in order to protect individuals from bodily harm or machinery from damage.

Features

- Optimized material properties guarantee fast switching results
- 4 edge lengths available that can be easily cut to fit any application
- Can wire in 2 or 4-wire circuits
- Requires aluminum mounting rail (included with 2ft and 5ft edges) and offered in varying lengths
- Reference example connection drawings for easy product selection

ASO Safety Contact Edges - 30mm					
Part Number	Price	Profile	Length	End Caps	Aluminum Mounting Rail
1502-2110	\$36.00	25 x 30 mm [0.787 x 1.18 in]	2ft [0.610 m]	End caps not included; choose from table below	Included
1502-2111	\$80.00	25 x 30 mm [0.787 x 1.18 in]	5ft [1.52 m]		Included
1502-2112	\$200.00	25 x 30 mm [0.787 x 1.18 in]	20ft [6.10 m]		Not included
1502-2600	\$590.00	25 x 30 mm [0.787 x 1.18 in]	82ft [25.00 m]		Not included

ASO Safety Contact Edge End Caps - 30mm			
Part Number	Price	Description	Connection
1804-2205	\$17.00	End cap for 25 x 30 mm safety contact edges	3-pin female M8 connector; 1.65 ft [0.5 m] cable length
1804-2195	\$17.00	End cap for 25 x 30 mm safety contact edges	3-pin male M8 connector; 1.65 ft [0.5 m] cable length
1804-0565	\$10.25	Terminating resistor end cap for 25 x 30 mm safety contact edges, 8.2 k ohm	NA

ASO Safety Contact Edge Mounting Rails				
Part Number	Price	Description	Material	Contents
2002-0230	\$80.00	Contact edge mounting rail	Aluminum	Package of 4 rails, each 5ft [1.52 m] length
2002-0231	\$14.00	Contact edge mounting rail	Aluminum	1 rail, 2ft [609.6 mm] length


ASO Safety Solutions Industrial Shears				
Part Number	Price	Description	Use With	Contents
9501-0160	\$65.00	Stainless steel industrial shears	Safety contact edges	1 shear

ASO Safety Solutions 25mm x 30mm SENTIR Edges and End Caps

Selection


Use the following Example Connections drawings to help you select the correct components for your system.

Example Connections - 30mm edges and end caps




Example Connections for a 2-wire Safety Relay

Single Edge Connection



Multiple Edge Connection




Note 1: **1502-2110** 2' Edge (mounting rail included)
1502-2111 5' Edge (mounting rail included)
1502-2112 20' (cut to length)
1502-2600 82' (cut to length)

Note 2: **2002-0231** 2' mounting rail
2002-0230 5' mounting rails (4 pack)


ASO Safety Solutions 25mm x 30mm SENTIR Edges and End Caps

Example Connections - 30mm edges and end caps




Example Connections for a 4-wire Safety Relay

Single Edge Connection



Multiple Edge Connection




Note 1: **1502-2110** 2' Edge (mounting rail included)
1502-2111 5' Edge (mounting rail included)
1502-2112 20' (cut to length)
1502-2600 82' (cut to length)

Note 2: **2002-0231** 2' mounting rail
2002-0230 5' mounting rails (4 pack)

ASO Safety Solutions 25mm x 30mm SENTIR Edges and End Caps


SENTIR 25mm x 30mm Edges	
	General Specifications
Material	TPE
Material Hardness	68 Shore A
Weight (per meter)	440g [5.5 oz] per meter
Protection Class (Enclosure)	IP65
Switching Cycles	>30,000 [UL 325]
Switching Angle	2 x 45°
Actuation Resistance	≤ 500 Ohms
Actuation Force	35N
Mechanical Life	10,000 cycles
Electrical Capacity	24VDC, 10mA
Max. Temperature Range	-25° to +75°C [-13° to +167°F]
Operating Temperature	-10° to +50°C [+14° to +122°F]
Max. Series Connection	5 contact edges or 100m [328.08 ft] based on the ASO safety relay 1114-0210
Inactive End Region with Higher Forces	30mm [1.18 in]
Connection Cables	LIY11Y 2 x 0.34 mm ²
Cable Material	PUR matte black
Agency Approvals	UL Recognized file E341185, CE

Dimensions mm [in]




Safety Contact Edges - 30mm 1502-2XXX

PART INFORMATION			
PART NO.	W	H	LENGTH
1502-2110			609.6 mm [2] ft
1502-2111	25.0 [0.98]	30.0 [1.18]	1524.0 mm [5] ft
1502-2112			6096.0 mm [20] ft
1502-2600			24993.6 mm [82] ft



Safety Contact Edge Mounting Rails 2002-0230



Safety Contact Edge Mounting Rails 2002-0231

Safety Products



Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application. AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.