

DINnectors® Accessories

Jumpers

Multi-pole jumper bars for DINnector terminal blocks




DN-12JL14B-A

Multi-pole Jumper Bars								
Part Number	Qty	Price	Number of Poles	Rating		Tightening Torque	Insulation Color	For Use With Terminal Block Series
				(V)	(A)			
Screw-down Connection								
DN-2J6	100	\$05cy:	2	600	65	0.5 Nm [4.4 Lb-In]	—	DN-T6
DN-3J6	100	\$;005cl:	3	600	65		—	
DN-4J6	100	\$005d1:	4	600	65		—	
DN-55J6	1	\$05d2:	55	600	65		—	
DN-24J8	5	\$0ed#:	24	600	50	0.6 Nm [5.3 lb-in]	Green	DN-T8
Push-in Connection								
DN-2J2Y	100	\$05cv:	2	600	25	—	Orange	DN-T12-A
DN-2J2YMN	25	\$07uh:	2	600	25		Orange	DN-EMX
DN-3J2Y	100	\$05c_:	3	600	25		Orange	DN-Q12-A
DN-3J2YMN	25	\$07uk:	3	600	25		Orange	DN-QEMX
DN-24J2Y	5	\$07og:	24	600	25		Orange	DN-QKBD12-A
DN-2J4Y	100	\$05cx:	2	600	25		Yellow	DN-T10-A
DN-2J4YMN	25	\$-07ui:	2	600	25		Yellow	
DN-3J4Y	100	\$05c#:	3	600	25		Yellow	
DN-3J4YMN	25	\$-07ul:	3	600	25		Yellow	
DN-24J4Y	5	\$07oh:	24	600	25		Yellow	DN-TL-A
DN-2JL14-A	100	\$05cz:	2	300	20		Red	
DN-2JL14-AMN	25	\$-07uj:	2	300	20		Red	
DN-2JL14B-A	100	\$;05cj:	2	300	20		Blue	
DN-2JL14B-AMN	25	\$;05cj:	2	300	20		Blue	
DN-3JL14-A	100	\$005c?:	3	300	20		Red	
DN-3JL14-AMN	25	\$07un:	3	300	20		Red	
DN-3JL14B-A	100	\$;005c,:	3	300	20		Blue	
DN-3JL14B-AMN	25	\$05d0:	3	300	20		Blue	
DN-12JL14-A	10	\$;05ct:	12	300	20		Red	
DN-12JL14B-A	10	\$05cu:	12	300	20		Blue	DN-FE4
DN-12JFE	10	\$;-07l,:	12	300	25		Blue	
DN-2J6Y	100	\$-07oi:	2	600	30		Green	
DN-2J6YMN	25	\$-07oj:	2	600	30		Green	
DN-3J6Y	100	\$07ok:	3	600	30		Green	DN-Q8-A
DN-3J6YMN	25	\$05d3:	3	600	30		Green	
DN-12J6Y	10	\$;07of:	12	600	30		Green	DN-Q8-A


Dimensions

mm [inches]


DN-24J8




DN-xJ2Y / DN-xJ2YMN




DN-xJ4Y / DN-xJ4YMN




DN-xJL14 / DN-xJL14x-AMN, DN-xJ14x-A



DN-12JFE



DN-xJ6Y / DN-xJ6YMN




DINnectors® Accessories

Modifying a [DN-24J8](#) jumper bar to the required number of poles


1) Place the insulating part into the jumper bar and insert screws, based on number of poles required.
(For instance, in the following example, 5 poles are required). Click into place.



2) Using a cutting tool, cut the insulating part at the edge of the jumper bar (see below).




3) Hold the metal jumper bar and insulating jumper with two hands, placing fingers to the left and right of the pole you wish to cut, repeatedly flexing up and down (1 or 2 times should be sufficient) until the jumper bar and insulating jumper break in two.



4) Remove the small remaining piece of jumper (see below). This is important to ensure appropriate insulation distance in the case of contiguously applied jumpers in sequence. This step also facilitates the placement of a separator terminal if the bridge is positioned as the last terminal of a group.



5) The jumpers now are ready to be screwed onto [DN-T8](#) series terminal blocks.



Jumper Cutting Tools

Jumper cutting tools maintain protective covering.

Jumper Cutting Tools			
Part Number	Description	Qty	Price
DN-J2CUT	DINnector jumper cutting tool, for use with DN-2J2Y, DN-3J2Y and DN-24J2Y jumpers.	1	\$;04,k:
DN-J4CUT	DINnector jumper cutting tool, for use with DN-2J4Y, DN-3J4Y and DN-24J4Y jumpers.	1	\$;04,n:
DN-J6CUT	DINnector jumper cutting tool, for use with DN-12J6Y jumpers.	1	\$;004,p:
DN-JL14CUT	DINnector jumper cutting tool, for use with DN-12JL 14-A and DN-12JL 14B-A jumpers.	1	\$007uo:
DN-JXCUT	DINnector jumper cutting tool, for use with DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE and DN-JFEDIE dies.	1	\$;04,s:
DN-JFECUT	DINnector jumper cutting tool, for use with DN-12JFE jumpers.	1	\$;004,h:
DN-JKIT	DINnector cutting tool kit for DN series jumpers. Includes (1) DN-JXCUT cutting tool, (5) dies (DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE, and DN-JFEDIE).	1	\$00ebx:
DN-TOOL2	DINnector tool kit, for use with DN series terminal blocks, includes (1) spring opening tool for DN-Q series screwless terminal blocks and (1) jumper removal tool for J2, J4, J6, and JL14 jumpers.	1	\$0eby:



DN-J2CUT



DN-J4CUT



DN-JKIT



DN-TOOL2


Replacement Dies		
Part Number	Description	Price
DN-J2DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J2CUT or DN-JXCUT.	\$;-004,l:
DN-J4DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J4CUT or DN-JXCUT.	\$;004,o:
DN-JFEDIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-JFECUT or DN-JXCUT.	\$;-004,i:
DN-J6DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J6CUT or DN-JXCUT.	\$;004,q:
DN-JL14DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-JL14CUT or DN-JXCUT.	\$;-004,j:

DINnectors® Accessories

Terminal Plugs



DN-xxPLUG / DN-xxPLUGMN



Accessories – Terminal Plugs							
Plugs* Part Number	Qty	Price	Plugs* Part Number	Qty	Price	Number of Poles	Length mm [in]
DN-2PLUG	200	\$006a9:	DN-2PLUGMN	10	\$7n3:	2	10.2 [0.40]
DN-3PLUG	200	\$006aa:	DN-3PLUGMN	10	\$07n4:	3	15.2 [0.60]
DN-4PLUG	100	\$006ab:	DN-4PLUGMN	10	\$07n5:	4	20.3 [0.80]
DN-5PLUG	100	\$006ac:	DN-5PLUGMN	10	\$07n6:	5	25.4 [1.00]
DN-6PLUG	100	\$006ad:	DN-6PLUGMN	10	\$07n7:	6	30.5 [1.20]
DN-7PLUG	50	\$006ae:	DN-7PLUGMN	5	\$07n8:	7	35.6 [1.40]
DN-8PLUG	50	\$006af:	DN-8PLUGMN	5	\$07n9:	8	40.6 [1.60]
DN-9PLUG	50	\$006ag:	DN-9PLUGMN	5	\$07na:	9	45.7 [1.80]
DN-10PLUG	50	\$00675:	DN-10PLUGMN	5	\$07n0:	10	50.8 [2.00]
DN-11PLUG	50	\$00676:	DN-11PLUGMN	5	\$07n1:	11	55.9 [2.20]
DN-12PLUG	50	\$00677:	DN-12PLUGMN	5	\$07n2:	12	61.0 [2.40]
Terminal Plugs Ratings							
Voltage/Current		300V, 12A					
Wire Gauge		14–22 AWG, CU only					
Torque		Tightening Torque: 0.51 N·m [4.5 lb-in]					
Usage Temperature		Ambient air temperature: -20 to 105°C [-4 to 221°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]					
Agency Approvals		UL file #: E179129					


Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

* DN-xxPLUGs fit all DN-EMXxx & DN-QEMXxx plug-in terminal blocks

Disconnect Blade



**DN-DIS-BLADE
DN-DIS-BMN**







Disconnect Blade			
Part Number	Description	Qty	Price
DN-DIS-BLADE	Terminal block disconnect blade for DN-FE2, DN-FE4, DN-DIS2 and DN-DIS4	50	\$07z9:
DN-DIS-BMN		10	\$05cs:

End Brackets



End Brackets		
Part Number	Description	Price
DN-EB15	DINnecter snap-on end bracket, 7mm wide. Package of 100. For use with 15mm DIN rail.	\$007ze:
DN-EB15MN	DINnecter snap-on end bracket, 7mm wide. Package of 20. For use with 15mm DIN rail.	\$07zf:
DN-EB35	DINnecter screw-down end bracket, 9mm wide. Package of 50. For use with 35mm DIN rail.	\$07zg:
DN-EB35MN	DINnecter screw-down end bracket, 9mm wide. Package of 20. For use with 35mm DIN rail.	\$07zj:
DN-EB35-A	DINnecter screw-down end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail.	\$07zh:
DN-EB35-A-10	DINnecter screw-down end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail.	\$07zi:
DN-QEB35	DINnecter snap-on end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail.	\$07zk:
DN-QEB35-10	DINnecter snap-on end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail.	\$07zl:



For more information on accessories, see the "DINnectors Accessories" section of this section.

 DINnectors Accessories

End Covers

Certain end covers can be used with multiple terminal block parts to cover and insulate the open side, or to put more space between adjacent blocks.

DINnectors End Covers		
Part Number	Description	Price
<u>DN-EC1210</u>	DINnector terminal block end cover, gray. Package of 100. For use with DN-T12 or DN-T10 series terminal blocks.	\$;0et2:
<u>DN-EC1210MN</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-T12 or DN-T10 series terminal blocks.	\$;0et3:
<u>DN-EC86</u>	DINnector terminal block end cover, gray. Package of 100. For use with DN-T8 or DN-T6 series terminal blocks.	\$;0et7:
<u>DN-EC86MN</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-T8 or DN-T6 series terminal blocks.	\$;0et8:
<u>DN-EC4</u>	DINnector terminal block end cover, gray. Package of 50. For use with DN-T4 series terminal blocks.	\$;0et6:
<u>DN-EC4MN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-T4 series terminal blocks.	\$7zp:
<u>DN-EC1/0</u>	DINnector terminal block end cover, gray. Package of 50. For use with DN-T1/0 series terminal blocks.	\$;0et1:
<u>DN-EC1/0MN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-T1/0 series terminal blocks.	\$7zo:
<u>DN-DEC10</u>	DINnector terminal block end cover, gray. Package of 50. For use with DN-D10-A series terminal blocks.	\$;0et0:
<u>DN-DEC10MN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-D10-A series terminal blocks.	\$7zn:
<u>DN-EC14</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14 series terminal blocks.	\$;0et4:
<u>DN-EC14S</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14S series terminal blocks.	\$;0et5:
<u>DN-ECM10</u>	DINnector terminal block end cover, gray. Package of 100. For use with DN-M10-A series terminal blocks.	\$;0eta:
<u>DN-ECM10MN</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-M10-A series terminal blocks.	\$;0etb:
<u>DN-ECKBD</u>	DINnector terminal block end cover, gray. Package of 100. For use with DN-KBD12 series terminal blocks.	\$;0et9:
<u>DN-ECKBDMN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-KBD12 series terminal blocks.	\$7zq:
<u>DN-EMXM1EC1</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block leftside.	\$;0ete:
<u>DN-EMXM1EC2</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block rightside.	\$;;0etf:
<u>DN-EMXDVEC1</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block leftside.	\$;0etc:
<u>DN-EMXDVEC2</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block rightside.	\$;0etd:
<u>DN-FESEP</u>	DINnector terminal block end cover, gray. Package of 50. For use with DN-FE and DN-DIS series terminal blocks.	\$07us:
<u>DN-FESEP-10</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-FE and DN-DIS series terminal blocks.	\$;7ut:
<u>DN-QEC12</u>	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q12-A or DN-QG12 series terminal blocks.	\$07o4:
<u>DN-QEC12MN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q12-A or DN-QG12 series terminal blocks.	\$;etg:
<u>DN-QEC10</u>	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q10-A or DN-QG10 series terminal blocks.	\$07o2:
<u>DN-QEC10MN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q10-A or DN-QG10 series terminal blocks.	\$7o3:
<u>DN-QEC8</u>	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q8-A or DN-QG8 series terminal blocks.	\$07o6:
<u>DN-QEC8MN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q8-A or DN-QG8 series terminal blocks.	\$7o7:
<u>DN-QEC12-1-2</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-1-2-A series terminal blocks.	\$07nx:
<u>DN-QEC12-2-2</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-2-2-A series terminal blocks.	\$07o5:
<u>DN-QDEC12</u>	DINnector terminal block end cover, gray. Package of 25. For use with DN-QD12 series terminal blocks.	\$07o1:

Spacers

Spacers are used to put more space between adjacent blocks.

DINnectors Spacers			
Part Number	Description	Qty	Price
<u>DN-S1210</u>	Spacer for DN-T12-A and DN-T10-A series terminal blocks	100	\$07uu:
<u>DN-S1210MN</u>		25	\$07uv:
<u>DN-S86</u>	Spacer for DN-T8 and DN-T6 series terminal blocks	100	\$07ux:
<u>DN-S86MN</u>		25	\$05sc:
<u>DN-EMXM1SPA1</u>	Spacer for DN-EMXM1 and DN-QEMXM1 single-level plug-in terminal blocks	25	\$07uq:
<u>DN-EMXDVSPA1</u>	Spacer for DN-EMXDV and DN-QEMXDV double-level plug-in terminal blocks	25	\$07up:
<u>DN-FESPA</u>	Spacer for DN-FE sockets and DN-DIS disconnects	50	\$05sa:
<u>DN-FESPA-10</u>		10	\$5sb:

Top Covers








DINnectors Top Covers				
Part Number	Description	For Use With	Qty	Price
<u>DN-C12</u>	Top cover, clear, printed electrical symbol.	<u>DN-T12-A</u>	100	\$;07uj:
<u>DN-C12MN</u>			25	\$;07uj:
<u>DN-C10</u>	Top cover, clear, printed electrical symbol.	<u>DN-T10-A</u>	100	\$07uy:
<u>DN-C10MN</u>			25	\$07uz:
<u>DN-C86</u>	Top cover, clear, printed electrical symbol.	<u>DN-T8</u> <u>DN-T6</u>	100	\$07u_:
<u>DN-C86MN</u>			25	\$07u#:
<u>DN-DC10</u>	Top cover, clear, printed electrical symbol.	DN-D10	100	\$07xy:
<u>DN-DC10MN</u>			25	\$07xz:
<u>DN-MC10</u>	Top cover, clear, printed electrical symbol.	DN-M10	100	\$;07x[:
<u>DN-MC10MN</u>			25	\$07x_:

 DINnectors Accessories

DINnector End Covers and Spacers Dimensions









Part Number		Length mm[in]	Height mm [in]	Thickness mm [in]
<u>DN-EC1210</u>	<u>DN-EC1210MN</u>	44 [1.73]	35 [1.38]	1.5 [0.06]
<u>DN-S1210</u>	<u>DN-S1210MN</u>	55 [2.17]	44 [1.73]	
<u>DN-EC86</u>	<u>DN-EC86MN</u>	50 [1.97]	43 [1.69]	
<u>DN-S86</u>	<u>DN-S86MN</u>	55 [2.17]	49 [1.93]	
<u>DN-EC4</u>	<u>DN-EC4MN</u>	56 [2.21]	48 [1.89]	
<u>DN-EC1/0</u>	<u>DN-EC1/0MN</u>	62 [2.44]	60 [2.36]	
<u>DN-DEC10</u>	<u>DN-DEC10MN</u>	72 [2.80]	49 [1.93]	
<u>DN-EC14</u>	—	78 [3.08]	55 [2.17]	
<u>DN-EC14S</u>	—	55 [2.17]	50 [1.97]	
<u>DN-ECM10</u>	<u>DN-ECM10MN</u>	32 [1.26]	27 [1.06]	
<u>DN-ECKBD</u>	<u>DN-ECKBDMN</u>	52 [2.05]	34.5 [1.36]	
<u>DN-EMXM1EC1</u>	<u>DN-EMXM1EC2</u>	as shown on next page		1.5 [0.06]
<u>DN-EMXDVEC1</u>	<u>DN-EMXDVEC2</u>			
<u>DN-EMXDVSPA1</u>	<u>DN-EMXM1SPA1</u>			
<u>DN-FESPA</u>	<u>DN-FESPA-10</u>			
<u>DN-FESEP</u>	<u>DN-FESEP-10</u>			
<u>DN-QEC12</u>	<u>DN-QEC12MN</u>	50 [1.97]	23 [0.9]	
<u>DN-QEC10</u>	<u>DN-QEC10MN</u>	57.4 [2.26]	33.6 [1.32]	
<u>DN-QEC8</u>	<u>DN-QEC8MN</u>	63 [2.48]	38.5 [1.52]	
<u>DN-QEC12-1-2</u>	—	68.5 [2.70]	28.5 [1.12]	
<u>DN-QEC12-2-2</u>	—	87.5 [3.44]	28.5 [1.12]	
<u>DN-QDEC12</u>	—	98 [3.86]	37 [1.46]	

**DN-EC1210 (MN), DN-EC86 (MN), DN-EC4 (MN),
DN-EC1/0 (MN), DN-ECKBD (MN), DN-S1210 (MN),
DN-S86 (MN)**



DINnectors Accessories

Dimensional Drawings

DN-EMXM1EC1**DN-EMXM1EC2****DN-EMXDVSPA1****DN-EMXM1SPA1****DN-EMXDVEC1****DN-EMXDVEC2****DN-FESEP,
DN-FESEP-10****DN-FESPA, DN-FESPA-10**

 DINnectors® Accessories

Marking Tags Cross Reference Charts - Screwless


DINector Marking Tags Cross Reference - Screwless				
<i>Block Type</i>	<i>DN-QL</i>	<i>DN-LA</i>	<i>DN-LT</i>	<i>DN-EMLBL</i>
<i>DN-Q12</i>	X	–	–	–
<i>DN-Q10</i>	X	–	–	–
<i>DN-Q8</i>	X	–	–	–
<i>DN-QD12</i>	X	–	–	–
<i>DN-Q12-1-2</i>	X	–	–	–
<i>DN-Q12-1-2L</i>	X	–	–	–
<i>DN-Q12-1-2D</i>	X	–	–	–
<i>DN-QKBD</i>	X	–	–	–
<i>DN-Q12-2-2</i>	X	–	–	–
<i>DN-Q12-2-2L</i>	X	–	–	–
<i>DN-Q12-2-2D</i>	X	–	–	–
<i>DN-QEMXM1</i>	–	X	X	X
<i>DN-QEMXDV</i>	–	X	X	X
<i>DN-QG12</i>	X	–	–	–
<i>DN-QG10</i>	X	–	–	–
<i>DN-QG8</i>	X	–	–	–
<i>DN-QG12-1-2</i>	X	–	–	–
<i>DN-QG12-2-2</i>	X	–	–	–

Marking Tags

Marking Tags DN-L Series

Part Number	Marking Sequence	Qty	Price
<u>DN-L50</u>	1-50	500	\$07vp:
<u>DN-L100</u>	51-100	500	\$07vg:
<u>DN-L150</u>	101-150	500	\$07vh:
<u>DN-L200</u>	151-200	500	\$-07vi:
<u>DN-L250</u>	201-250	500	\$-07vj:
<u>DN-L300</u>	251-300	500	\$07vk:
<u>DN-L350</u>	301-350	500	\$-07vl:
<u>DN-L400</u>	351-400	500	\$07vn:
<u>DN-L450</u>	401-450	500	\$07vo:
<u>DN-LB</u>	Blank	500	\$07vq:
<u>DN-LS</u>	L1, L2, L3, L, N, GND, +, -, COM, COM*	500	\$07vs:

Dimensions




- The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500.
- The DN-L tags fit all DINnectors 6mm wide and wider.
- There will be a gap between tags on blocks wider than 6mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LA Series

Part Number	Marking Sequence	Qty	Price
<u>DN-LA100</u>	1-100	500	\$;07u!:
<u>DN-LA200</u>	101-200	500	\$07u?:
<u>DN-LA300</u>	201-300	500	\$;07u,::
<u>DN-LA400</u>	301-400	500	\$07v0:
<u>DN-LAB</u>	Blank Tags	500	\$07v1:
<u>DN-LAS</u>	L1, L2, L3, L, N, GND, +, -, COM, COM*	500	\$07v2:

Dimensions




- The marking sequence of 100 tags (i.e. 1-100) is printed five times in each package of 500.
- The DN-LA tags fit all DINnectors 5mm wide and wider. There will be a gap between tags on blocks wider than 5mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LAT Series

Part Number	Marking Sequence	Qty	Price
<u>DN-LAT100-A</u>	1-100	500	\$07v4:
<u>DN-LAT200-A</u>	101-200	500	\$07v6:
<u>DN-LAT300-A</u>	201-300	500	\$07v8:
<u>DN-LAT400-A</u>	301-400	500	\$07va:
<u>DN-LAT500-A</u>	401-500	500	\$07vb:
<u>DN-LAT600-A</u>	501-600	500	\$07vc:
<u>DN-LATB-A</u>	Blank Tags	500	\$07vd:
<u>DN-LATS-A</u>	L1, L2, L3, L, N, +, -, COM, COM*	500	\$;07vf:

Dimensions




- The marking sequence of 500 tags (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-QL Series

Part Number	Marking Sequence	Qty	Price
<u>DN-QL100</u>	1-100	500	\$059o:
<u>DN-QL200</u>	101-200	500	\$059p:
<u>DN-QL300</u>	201-300	500	\$059q:
<u>DN-QL400</u>	301-400	500	\$059s:
<u>DN-QL500</u>	401-500	500	\$;059t:
<u>DN-QLB</u>	Blank Tags	500	\$059u:
<u>DN-QLS</u>	L1, L2, L3, L, N, +, -, COM, COM*	500	\$059v:

Dimensions




- The marking sequence of 500 (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

DINnectors® Accessories


Marking Tags continued

Marking Tags DN-LT Series			
Part Number	Marking Sequence	Qty	Price
DN-LT15	1-5	100	\$07vv:
DN-LT60	6-0	100	\$07v_:
DN-LT1	1	100	\$07vu:
DN-LT2	2	100	\$07vx:
DN-LT3	3	100	\$07vy:
DN-LT4	4	100	\$07vz:
DN-LT5	5	100	\$07v[:
DN-LT6	6	100	\$07v[:
DN-LT7	7	100	\$07v#:
DN-LT8	8	100	\$07v!:
DN-LT9	9	100	\$07v?:
DN-LT0	0	100	\$07vt:
DN-LTBLNK	Unprinted	100	\$07x2:
DN-LTA	A	100	\$07v,:
DN-LTB	B	100	\$07x1:
DN-LTC	C	100	\$07x3:
DN-LTD	D	100	\$07x4:
DN-LTE	E	100	\$07x6:
DN-LTF	F	100	\$07x7:
DN-LTG	G	100	\$07x8:
DN-LTH	H	100	\$07xa:
DN-LTI	I	100	\$07xb:
DN-LTJ	J	100	\$07xc:
DN-LTK	K	100	\$07xd:
DN-LTL	L	100	\$07xe:
DN-LTM	M	100	\$07xf:
DN-LTN	N	100	\$07xg:
-	-	-	-
DN-LTP	P	100	\$07xi:
DN-LTQ	Q	100	\$07xk:
DN-LTR	R	100	\$07xl:
DN-LTS	S	100	\$07xn:
DN-LTT	T	100	\$07xo:
DN-LTU	U	100	\$07xp:
DN-LTV	V	100	\$07xq:
DN-LTW	W	100	\$07xs:
DN-LTX	X	100	\$07xt:
DN-LTY	Y	100	\$07xu:
DN-LTZ	Z	100	\$07xv:
DN-LTGND	⊕	100	\$07x9:
DN-LTPOS	+	100	\$07xj:
DN-LTNEG	-	100	\$07xh:
DN-LTAC	~	100	\$07x0:
DN-LTDC	=	100	\$07x5:




- These marking tags allow the flexibility of creating custom marking sequences on site.
- The DN-M series supports a maximum of three digits (tags), while other DINnectors support up to four digits (tags).
- Material: Thermoplastic with heat embossed black print.

DN-MTA marking tag adapter



DN-MTA dimensions



Part Number	Description	Qty	Price
DN-MTA	Marking tag adapter holds up to six DN-LT tags	50	\$07xx:

Note: [DN-MTA](#) adapter does not fit [DN-T12-A](#) terminal blocks.

DINnectors® Accessories

Terminal Marking Accessories

**DN-EMLBL1****DN-EMLBL2****DN-EMLBL3**

Part Number	Description	For Use With	Qty	Price
DN-EMLBL1	Blank labels	DN-EMPEG1 pin protectors for DN-xEMXxx plug-in terminal blocks	100	\$059k:
DN-EMLBL2	Labels printed 1 – 12		100	\$-059l:
DN-EMLBL3	Labels printed 13 – 24		100	\$059n:

Marking Pen – for terminal and wire marking tags

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- Low odor ink

Part Number	Description	Qty	Price
DN-MP	Staedtler-Mars marking pen, for use with blank marking tags. Permanent Ink, fine tip.	1	\$,86]:

**Marking pen**

Wire Marking Accessories

**DN-WMTAG1 wire tags &
DN-WM-x wire tag holders**

Part Number	Description	For Use With	Qty	Price
DN-WMTAG1	Wire tag – blank	all DN-WM-x wire tag holders	525	\$059x:
DN-WM-1	Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire	DN-WMTAG1	200	\$0edg:
DN-WM-2	Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16–11 AWG wire		200	\$0edh:
DN-WM-3	Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire		100	\$-edi:
DN-WM-4	Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire		100	\$-edj: