





Signal Devices

Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201	\$04c2:	PDF	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202	\$0eag:	PDF	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503	\$0enk:	PDF	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
97581507	\$-0enl:	PDF	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
97581508	\$0enn:	PDF	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
97581522	\$4e6:	PDF	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
96000001	\$05h8:	PDF	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901	\$;0eaf:	PDF	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
97520902	\$;-4i,:	PDF	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8 to 17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
97582603	\$;:04[[:	PDF	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
97582605	\$05o0:	PDF	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ ABS blend	62g [2.19 oz]





Signal Devices

Visual 98mm Base Mount Beacons

Features

- Choose from permanent incandescent, permanent LED, flashing Xenon, EVS (Enhanced Visibility System) flashing LED, and rotating models
- Base mount installation
- 98mm diameter
- Light-intensive Xenon flash in flash models
- Bulb not included with 826 incandescent models
- 25W bulb included with 827 incandescent models
- Various mounting accessories available
- 2-year warranty



Visual 98mm Base Mount Beacons 826, 827, and 828 Series Selection Chart

Part Number	Price	Color	Drawing link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
74mm Base Mount													
82610000	\$0czu:	Red	PDF	Incandescent Permanent Light 98mm	12-240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (bulb sold separately)	-				180 [6.35]		
82620000	\$0czv:	Green	PDF										
82630000	\$0czx:	Yellow	PDF										
82640000	\$0czy:	Clear	PDF										
82650000	\$0czz:	Blue	PDF										
82710075	\$;00czj:	Red	PDF	Incandescent Blinking Light (1.5 Hz blinking frequency, 5Ws flash energy) 98mm	24V AC/DC	max. 3.0 A		-4 to 122°F [-20 to 50°C] IP65 when mounted	Up to 5,000h	Polycarbonate cap Polycarbonate/ABS base	207 [7.30]	Terminal screws Max 2.5 mm ² AWG 16-14 Cable diameter 5-8 mm	cULus file E164155, CE, RoHS
82720075	\$00cz:	Green	PDF										
82730075	Retired	Yellow	PDF										
82740075	\$;00cz:	Clear	PDF										
82750075	\$;00cj1:	Blue	PDF										
82710077	Retired	Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	115V AC/DC	max. 500mA	≤ 3.0 A						
82720077	\$00cz#:	Green	PDF										
82730077	\$00cz?:	Yellow	PDF										
82740077	\$;00cj0:	Clear	PDF										
82750077	\$;00cj2:	Blue	PDF										
82810055	\$;00cj3:	Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	24VDC	300mA							
82820055	\$;00cj5:	Green	PDF										
82830055	Retired	Yellow	PDF										
82840055	\$;00cj9:	Clear	PDF										
82850055	\$;00cjb:	Blue	PDF										
82810067	Retired	Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	115VAC	65mA 50-60 Hz			4,000,000 flashes				
82820067	\$;00cj6:	Green	PDF										
82830067	\$;00cj8:	Yellow	PDF										
82840067	\$;00cja:	Clear	PDF										
82850067	\$;00cjc:	Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bulbs



[95582635](#)

Bulbs						
Part Number	Price	Description	Wattage	Voltage	For Use With	Life Duration
95582635	\$ec7:	Bulb for incandescent light BA15d bayonet socket	15W	24V AC/DC	826xxxxx	up to 5,000h
95582637	\$ec8:			115VAC		
95582638	\$ec9:			230VAC		
95582735	\$;?b:	Bulb for blinking incandescent light B15d bayonet socket	25W	24V AC/DC	827xxxxx	up to 2,000h
95582737	\$?c0:			115VAC		
95588524	\$0?c1:		Halogen bulb G6.35	12V	885xxx78	
95588525	\$0?c2:			24V	885xxx75	



[95582735](#)



[95588524](#)