

Save 50% today

on NEMA enclosures



CHECK OUT OUR PRICES

Enclosures	AutomationDirect Hubbell/Wiegmann Price/Part Number	VS.	Hoffman Price/Part Number
NEMA 1 wall mount 24 x 24 x 08"	\$138.50 N1C242408LP		\$319.20 A-24N24BLP
NEMA 12 wall mount 20 x 16 x 08"	\$186.50 N12201608		\$413.60 A-201608LP
NEMA 12 DISCONNECT wall mount (24" x 25-3/8" x 8")	\$325.00 SDN12242508		\$622.60 A24SA2608LP
NEMA 4 wall mount 20 x 20 x 06"	\$241.75 N4202006		\$536.70 A-20H20ALP
NEMA 4X wall mount 20 x 20 x 06"	\$577.00 SSN4202006		\$1,412.00 A-20H2006SSLP
NEMA 4/12 wall mount 36 x 24 x 08"	\$239.25 N412362408C		\$537.60 C-SD36248
3-hole 30 mm NEMA 12 pushbutton enclosure	\$41.25 PB3		\$94.12 E-3PB

*All prices are U.S. published prices. AutomationDirect prices from April 2008 Price List. Hoffman prices are taken from Hoffman Price List dated March 3, 2008. Prices may vary by dealer. Many other part numbers are available from all vendors.



AUTOMATIONDIRECT offers over 1,600 enclosures from Hubbell/Wiegmann across **NEMA 1, 3S, 3R, 4, 4X, 6P, 12 and 4/12, and 13 ratings**. Choose from a full line of **metallic enclosures** and operator consoles; our **non-metallic** line is designed for harsh outdoor environments requiring **NEMA 3R or 4X ratings**. A full line of accessories, including subpanels, locks and latches, and floor stand kits, is also available.

Also get great prices on steel and stainless steel flanged enclosures for mounting **disconnects from all the major manufacturers**, including the Ferraz Shawmut line sold by AutomationDirect.

30-day money-back guarantee
Order with the assurance of our unconditional 30-day money-back guarantee on enclosures.

ALSO AVAILABLE


Wire



Terminal Blocks



Rigid or Flexible Wire Duct
Water Tight Tubing



For more information on our Enclosure products, visit:
www.automationdirect.com/enclosures

ORDER BY PHONE



ORDER ONLINE



**BEST INDUSTRIAL
AUTOMATION DISTRIBUTOR**

IEA Best Brand 2007

AUTOMATIONDIRECT.com

www.automationdirect.com | 1-800-633-0405