

Build your control system for less!

with our everyday low prices on high-quality components

From cable to wire duct ...

NEW! 300V UL **Instrumentation Cable** is dual listed as UL 2250 Type ITC (Instrumentation Tray Cables) and UL 13 Type PLTC (Power Limited Tray Cables).

- 18 gauge
- 1, 2, 4 or 8 twisted pairs
- Overall shielded or individually shielded with overall shield
- Available in 100, 250 or 1000 ft reels

NEW!

Flexible **multi-conductor control cable** is suitable for wet and dry locations, and is resistant to sunlight, oil and moisture penetration.

- Conductor sizes from 18 to 10 gauge
- 3 to 41 unshielded conductors
- Available in 100, 250, 500 or 1000 ft reels
- UL and CSA approved, RoHS compliant

Heavy-duty **multi-wire connectors** quickly and reliably connect wiring in applications such as machinery, robots, and control and signal circuits.

- Build custom connectors from components
- 3 to 144-pole configurations
- 3A to 32B sizes
- Bulkhead or surface mount housings with standard or automatic covers

Multi-Conductor Control Cable

100-foot reels start at: **\$50.00**
(V40166-100)

Instrumentation Cable

100-foot reels start at: **\$32.00**
(PLTC3-18-1S-100)

Wire Duct

starting at: **\$12.00**
(single piece) or **\$184.00**
(20-piece pack)

Multi-Wire Connectors

All components sold separately

Keep your wiring in order with Iboco rigid or flexible **wire duct** in a choice of styles and colors.

- Standard or thin finger slotted styles, and solid duct for special applications
- Standard duct in gray, blue and black
- Sold per 2-meter piece for convenience or in cost-saving multi-packs

Research, price, buy at:
www.automationdirect.com/wiring-solutions

Also Available

Enclosures



Wiring Devices



Terminal Blocks



Tools



Cat5e Cables



Field Wireable Connectors



Cable Ties & Accessories



Order Today, Ships Today!

*See our Web site for details and restrictions. © Copyright 2014 AutomationDirect, Cumming, GA USA. All rights reserved.



AUTOMATIONDIRECT.com
1-800-633-0405 the #1 value in automation